

Key Features

- Industry Highest Cell Capacity & High Energy
- High voltage response, stable during most of the lifetime of the application
- Reliable Performance
- Child-Safe Markings & Retail Packaging
- Wide operating temperature range (-30°C / +70°C)
- Low self-discharge with long operating life (<1% after 1 year of storage at +20 °C)
- Excellent resistance to corrosion
- Designed to meet all major quality, safety and environment standards:
 - Safety: IEC 60086-4
 - Transport: UN 38.3
 - REACH compliance
 - Quality: ISO 9001, Duracell World Class Continuous Program

Electrical characteristics

Nominal capacity (15k Ohm Cont., 2.0 V cut-off)	255 mAh
Minimum Open circuit voltage (OCV)	3.0 V
Standard Continuous Discharge Current	0.4 mA
Maximum Continuous Discharge Current	3 mA
Maximum Pulse Discharge Current at 1 sec	50 mA
Nominal Energy	745 mWh
AC Impedance @ 1kHz	11 Ohm

Physical characteristics

Typical weight	2.8 g (0.098 oz)
Li metal content	approx. 0.072 g

Operating conditions

Operating temperature range	-30°C to 70°C (-22°F to 158°F)
Storage Temperature	5°C to 30°C (41°F to 86°F)
Storage Humidity	<70%

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.


DURACELL®
BATTERIES

Berkshire Corporate Park
Bethel, CT. 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
www.duracell.com


Typical applications

- Medical devices
- Security devices
- Fitness devices
- Watches
- Calculators
- Wireless sensors
- Toys
- Key-Fobs & Trackers

IEC Rated Capacity
15K Ohm Continuous to 2V




Continuous Discharge




IEC Key Fob
10 mA 5s/m, 24hd to 1.8V, RT



Temperature Discharge
5000 Ohm Continuous to 1.8V



Pulse Discharge Impedance
20mA 1s/14s to 1.8V




DURACELL®
BATTERIES

Berkshire Corporate Park
Bethel, CT. 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.

Pulse Load Capability (5 sec load)



IEC 60086-4

Test	Test designation	Observation
A	Altitude	Pass
B	Thermal cycling	Pass
C	Vibration	Pass
D	Shock	Pass
E	External short circuit	Pass
F	Impact	Pass
G	Crush	Pass
H	Forced discharge	Pass
I	Abnormal charging	Pass
J	Free fall	Pass
K	Thermal Abuse	Pass

Warning

Fire, explosion and burn hazard

Do not recharge, short circuit, crush, disassemble, heat above 100 °C (212 °F), incinerate, or expose contents to water

Warning! Keep batteries away from children!

Always keep your batteries away from children to prevent swallowing. If ingestion does occur, however, be aware that initial symptoms may be similar to other childhood illnesses such as coughing, drooling and discomfort.

Battery ingestion hotline (1-800-498-8666)

Storage

The storage area should be clean, cool (preferably not exceeding +30 °C), dry and ventilated

Cavity Contact Design Recommendation

Duracell's latest safety innovation added to our CR2032 lithium coin batteries is a bitter coating on the front face of the cell. If a child puts a CR2032 lithium coin battery in their mouth, the bitter coating will immediately react with saliva to release a bitter taste which helps discourage swallowing. Duracell recommends device designers and manufacturers avoid placing contacts within 3.2 mm of the perimeter of the positive terminal as shown in Figure 1.



DURACELL®
BATTERIES

Berkshire Corporate Park
Bethel, CT. 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
www.duracell.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Duracell:

[CR2032-1-72](#) [CR2032-2-72](#) [CR2032-36](#) [CR2032-600](#)