


- Industry Standard PLCC4 Footprint
- ♦ 3 Super Bright Chips in One Low Profile Package
- High Luminous Intensity
- Wide Viewing Angle
- High Power Efficiency



Bivar SMTL4 Super Bright Tri-Color LED combines three chips in a single package and is offered in an industry standard PLCC4 footprint. The SMTL4 LED has a water clear lens for high luminous intensity and wide viewing angle making them ideal for outdoor illumination applications where higher ambient lighting conditions exist. The flexible three chip design allows for a wide variety of lighting options where the chips can be individually driven or mixed to create different color combinations. The robust package is ideal for harsh working environments and can be clustered in LED arrays for high luminous applications. Low power consumption and excellent long life reliability are suitable for battery powered equipment. Bivar SMTL4 LED is packaged in standard tape and reels for pick and place assemblies.

Part Number	Material	Emitted Color	Luminous Intensity Typ. mcd	Lens Color	Viewing Angle	
	AlGaInP	Red	180		120°	
SMTL4-SRYB	GaAsP	Yellow	180	Water Clear		
	InGaN	Blue	285			

### **Outline Dimensions**











### **Absolute Maximum Ratings**

 $T_A = 25$ °C unless otherwise noted

Power Dissipation	Red, Yellow - 78 mW Blue - 100 mW	
Continuous Forward Current	Red, Yellow - 30 mA Blue - 25mA	
Peak Forward Current <sup>1</sup>	100 mA	
Reverse Voltage	5 V	
Derating Linear From 25°C	0.4 mA/°C	
Operating Temperature Range	-40 ~ +85°C	
Storage Temperature Range	-40 ~ +85°C	
Soldering Temperature <sup>2</sup>	260°C	

Notes: 1. 10% Duty Cycle, Pulse Width ≤ 0.1 msec.

2. Solder time less than 5 seconds at temperature extreme.

Handling: Reflow soldering must not be performed more than twice. Hand soldering must not be performed

more than once.

Sensitive to static electricity or surge voltage. Proper handling required to avoid ESD damage and impair LED reliability

### **Electrical Characteristics**

T<sub>A</sub> = 25°C & I<sub>F</sub> = 20 mA unless otherwise noted


Emitting Color	Forward Voltage (V)		Recommend Forward Current (mA)	Reverse Current (µA) V <sub>R</sub> =5V	Dominant Wavelength (nm) <sup>2</sup>		Luminous Intensity (mcd) <sup>3</sup>		Viewing Angle gle 2 Θ ½ (deg)			
	MIN	TYP	MAX	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	TYP
Red	1.6	1.9	2.4	20	10	624	631	634	115	180	225	
Yellow	1.6	1.9	2.4	20	10	585	591	594	115	180	225	120
Blue	2.9	3.2	3.5	20	10	464	469	471	180	285	360	

Notes: 1. Tolerance of Forward Voltage: ±0.05V.

Tolerance of Dominant Wavelength: -1nm of MIN & +1nm of MAX.
Tolerance of Luminous Intensity: ±15%.

### **Directivity Radiation**

T<sub>A</sub> = 25°C unless otherwise noted





### Typical Electrical / Optical Characteristics Curves

T<sub>A</sub> = 25°C unless otherwise noted

Relative Spectrum Emission I $_{\rm rel}$  = f (I), T $_{\rm A}$  = 25°C , I $_{\rm F}$  = 20 mA V(I) = Standard eye response curve





Fig.1 Relative Luminous Intensity vs. Wavelength

Relative Luminous Intensity  $I_V/I_V$  (20 mA) = f ( $I_F$ )  $T_A$  = 25°C Ambient Temperature vs. Allowable Forward Current



 $\label{eq:Fig.2} \textbf{Fig.2 Relative Luminous Intensity vs. Forward Current}$ 






Fig.3 Forward Current vs. Ambient Temperature






Forward Voltage (V)

Fig.4 Forward Current vs. Forward Voltage

Bivar reserves the right to make changes at any time without notice




### **Recommended Soldering Conditions**




### **Tape and Reel Dimensions**

Note: 2000 pcs/Reel



Bivar reserves the right to make changes at any time without notice





#### **Outline Drawings Notes:**


- 1. All dimensions are in inches [millimeters].
- 2. Standard tolerance unless otherwise noted: X.XXX ± 0.010"

X.X ± 0.1"

### **Packaging and Labeling Plan**

Note: 1 Reel / Bag

Sealed ESD and Moisture Barrier Bag



Part No.	XXXX-XXX-XXX
Prod. No.	XXXX-XXX-XXX
PO No.	xxxx
Lot No.	XXXXXXXX
Q'ty:	X.XXX PCS
Q.C.	XXX BIN
Date:	2008.XX.XX

Internal Quality Control Label

### Bivar. Inc.

MSL4

4 Thomas, Irvine, CA 92618-2593 LOT: XXX.XXXXXXXX



Part: XXXX-XXX

Quantity: XXXX

**RoHS** Compliant

Bivar Standard Packaging Label

### **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

SMTL4-SRYB