

REV.	DESCRIPTION	DATE	APPROVED
D	Engineering Update w/o Changes	02/24/04	M. C.
E	Tolerance Update.	09/28/06	M. C.
F	Updated Material.	10/28/08	T. Y.
G	Added Ordering Information.	06/06/11	T. Y.



SERIES	"H" DIMENSION	I.D.	O.D.
901	.030-1.250 (.76-31.8)	.028 (.71)	.085 (2.2)
902	.030-1.250 (.76-31.8)	.032 (.81)	.125 (3.2)
903	.030-1.250 (.76-31.8)	.047 (1.2)	.156 (4.0)
904	.030-1.250 (.76-31.8)	.063 (1.6)	.187 (4.7)
905	.030-1.250 (.76-31.8)	.147 (3.7)	.250 (6.4)
906	.030-1.250 (.76-31.8)	.085 (2.2)	.148 (3.8)
907	.030-1.250 (.76-31.8)	.105 (2.7)	.167 (4.2)
908	.030-1.250 (.76-31.8)	.125 (3.2)	.187 (4.7)
910	.030-1.250 (.76-31.8)	.091 (2.3)	.250 (6.4)
911	.030-1.250 (.76-31.8)	.125 (3.2)	.250 (6.4)
912	.030-1.250 (.76-31.8)	.171 (4.3)	.250 (6.4)
913	.030-1.250 (.76-31.8)	.091 (2.3)	.187 (4.7)
937	.030-1.250 (.76-31.8)	.090 (2.3)	.125 (3.2)
938	.030-1.250 (.76-31.8)	.032 (.81)	.085 (2.2)
939	.030-1.250 (.76-31.8)	.047 (1.2)	.125 (3.2)
940	.030-1.250 (.76-31.8)	.063 (1.6)	.156 (4.0)
941	.030-1.250 (.76-31.8)	.135 (3.4)	.230 (5.8)

ORDERING INFORMATION:

9XX-XXX

SERIES — LENGTH
 INCHES, MULTIPLES OF .005"
 .030" = 030
 .100" = 100
 1.250" = 1.250
 WHOLE MILLIMETERS
 2mm = 2MM
 5mm = 5MM

3. TOLERANCE "H" DIMENSION:

0.030 - 0.500 (1.0 - 12.7mm)±0.005(0.1mm)
 0.505 - 0.750 (12.8 - 19.1mm)±0.008(0.2mm)
 0.755 - 1.250 (19.2 - 31.8mm)±0.015(0.4mm)

2. MATERIAL: NYLON 6, ULTRAMID 8270 HS, NATURAL. BIVAR MATERIAL CODE 01-NL-WE.

ALLIED CHEMICAL POLYAMID NYLON 6 WITH CLARIANT CNY02655 WHITE NYLON CONCENTRATE.

1. GENERAL SPECIFICATIONS: BIVAR EXTRUDED PRODUCT SPECIFICATION BV00-E103.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ±.1	X° ± 1°		
.XX ±.01		 TITLE: NYLON TUBE SPACERS	
.XXX ±.005			
DESIGNED: Michael Chen	DATE: 01/13/03	PART NO: 9XX-XXX	REVISION: G
CHECKED: D. Green	DATE: 01/13/03	CAGE CODE : 32559	SHEET # 1 OF 1
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

<u>939-125</u>	<u>903-315</u>	<u>903-320</u>	<u>903-330</u>	<u>911-175</u>	<u>939-170</u>	<u>904-300</u>	<u>905-350</u>	<u>906-160</u>	<u>901-030</u>	<u>901-035</u>	<u>901-040</u>
<u>901-045</u>	<u>901-050</u>	<u>901-055</u>	<u>901-060</u>	<u>901-065</u>	<u>901-070</u>	<u>901-075</u>	<u>901-080</u>	<u>901-085</u>	<u>901-090</u>	<u>901-095</u>	<u>901-100</u>
<u>901-105</u>	<u>901-110</u>	<u>901-115</u>	<u>901-120</u>	<u>901-125</u>	<u>901-130</u>	<u>901-135</u>	<u>901-140</u>	<u>901-145</u>	<u>901-150</u>	<u>901-155</u>	<u>901-160</u>
<u>901-170</u>	<u>901-175</u>	<u>901-180</u>	<u>901-185</u>	<u>901-190</u>	<u>901-195</u>	<u>901-200</u>	<u>901-205</u>	<u>901-210</u>	<u>901-215</u>	<u>901-220</u>	<u>901-225</u>
<u>901-230</u>	<u>901-235</u>	<u>901-240</u>	<u>901-245</u>	<u>901-250</u>	<u>901-255</u>	<u>901-260</u>	<u>901-265</u>	<u>901-270</u>	<u>901-275</u>	<u>901-285</u>	<u>901-290</u>
<u>901-305</u>	<u>901-310</u>	<u>901-315</u>	<u>901-320</u>	<u>901-325</u>	<u>901-330</u>	<u>901-335</u>	<u>901-355</u>	<u>901-360</u>	<u>901-365</u>	<u>901-370</u>	<u>901-375</u>
<u>901-380</u>	<u>901-385</u>	<u>901-390</u>	<u>901-395</u>	<u>901-405</u>	<u>901-410</u>	<u>901-415</u>	<u>901-420</u>	<u>901-425</u>	<u>901-430</u>	<u>901-435</u>	<u>901-440</u>
<u>901-445</u>	<u>901-450</u>	<u>901-455</u>	<u>901-460</u>	<u>901-465</u>	<u>901-470</u>	<u>901-475</u>	<u>901-480</u>	<u>901-485</u>	<u>901-490</u>	<u>901-495</u>	<u>901-505</u>
<u>901-515</u>	<u>901-520</u>	<u>901-525</u>	<u>901-530</u>								