



SEI-110-02-GF-S-E-TR

SEI-120-02-GF-S

SIBF-10-F-S-AD

SIBF-25-F-S-AD

SIBF-05-F-S-AD

(1.00 mm) .0394" (SEI) (1.27 mm) .050" (SIBF)

SEI, SIBF SERIES

ONE-PIECE INTERFACE

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SEI or see www.samtec.com?SIBF

Insulator Material:
SEI = Liquid Crystal Polymer
SIBF = Black Liquid Crystal Polymer

Contact Material:
Phosphor Bronze

Plating:
SEI = Au over
50 μ" (1.27 μm) Ni
SIBF = Au or Sn over
50 μ" (1.27 μm) Ni

Current Rating:
SEI = 2.3 A per pin
(1 pin powered)
SIBF = 2.5 A per pin
(1 pin powered)

Operating Temp Range:
-55 °C to +125 °C

Mating Force:
SEI = 50 g (0.49 N) per contact

Voltage Rating:
SEI = 250 VAC
SIBF = 155 VAC

Cycles:
SEI = 100 min

Contact Deflection:
SEI = (0.46 mm) .018" nominal

RoHS Compliant:
Yes

PROCESSING



Lead-Free Solderable:
Yes

SMT Lead Coplanarity (SEI):
(0.10 mm) .004" max (05-25)
(0.15 mm) .006" max (30)*
*(.004" stencil solution may be available; contact ipg@samtec.com)

SMT Lead Coplanarity (SIBF):
(0.10 mm) .004" max (05-20)
(0.15 mm) .006" max (25)*
*(.004" stencil solution may be available; contact ipg@samtec.com)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SEI-110-02-G-S-AB](#) [SEI-120-02-G-S-AB](#) [SEI-115-02-G-S-AB](#) [SEI-110-02-GF-S-AB](#) [SEI-120-02-GF-S-M-AB](#) [SEI-105-02-G-S-AB](#) [SEI-125-02-GF-S-E-AB-TR](#) [SEI-120-02-GF-S-E-AB](#) [SEI-120-02-GF-S-E-AB-TR](#) [SEI-105-02-GF-S-SEI-105-02-GF-S-TR](#) [SEI-105-02-G-S-M](#) [SEI-105-02-G-S](#) [SEI-120-02-G-S-M-AT](#) [SEI-125-02-GF-S-AB](#) [SEI-120-02-G-S-AT](#) [SEI-130-02-GF-S-AT-TR](#) [SEI-130-02-GF-S-M](#) [SEI-110-02-G-S-M-AB](#) [SEI-120-02-GF-S](#) [SEI-120-02-G-S-M-AB](#) [SEI-110-02-GF-S-AB-TR](#) [SEI-110-02-GF-S-E-AT](#) [SEI-116-02-G-S](#) [SEI-120-02-G-S-E-AB](#) [SEI-125-02-GF-S-M](#) [SEI-107-02-GF-S](#) [SEI-120-02-G-S-TR](#) [SEI-110-02-GF-S-M-AT](#) [SEI-120-02-G-S-AB-TR](#) [SEI-116-02-GF-S-AT](#) [SEI-118-02-G-S-AT](#) [SEI-125-02-G-S](#) [SEI-130-02-G-S-M-AT](#) [SEI-110-02-GF-S-AT](#) [SEI-120-02-G-S-E](#) [SEI-120-02-G-S-M](#) [SEI-115-02-GF-S-E-AB](#) [SEI-115-02-GF-S-E-AT](#) [SEI-115-02-G-S-M-AT](#) [SEI-124-02-GF-S-M](#) [SEI-114-02-GF-S](#) [SEI-125-02-G-S-AB](#) [SEI-110-02-G-S-AT](#) [SEI-120-02-G-S](#) [SEI-112-02-GF-S-AB](#) [SEI-115-02-GF-S-AB](#) [SEI-120-02-GF-S-AB](#) [SEI-125-02-G-S-M](#) [SEI-110-02-G-S](#) [SEI-130-02-GF-S-AT](#) [SEI-130-02-G-S-E-AB](#) [SEI-105-02-G-S-M-AB](#) [SEI-106-02-GF-S](#) [SEI-110-02-G-S-AB-TR](#) [SEI-110-02-G-S-E-AB](#) [SEI-125-02-G-S-E-AT](#) [SEI-110-02-GF-S-M](#) [SEI-115-02-G-S-TR](#) [SEI-116-02-G-S-AB](#) [SEI-130-02-GF-S](#) [SEI-130-02-GF-S-AB](#) [SEI-125-02-G-S-AT-TR](#) [SEI-130-02-GF-S-E-AT](#) [SEI-130-02-G-S-E](#) [SEI-105-02-GF-S-AB](#) [SEI-105-02-GF-S-AT](#) [SEI-130-02-G-S-AT](#) [SEI-110-02-GF-S](#) [SEI-115-02-G-S-M](#) [SEI-120-02-GF-S-M-AT](#) [SEI-125-02-G-S-AT](#) [SEI-130-02-GF-S-E-AB-TR](#) [SEI-110-02-GF-S-E-AB](#) [SEI-115-02-G-S-M-AB-TR](#) [SEI-120-02-GF-S-AB-TR](#) [SEI-125-02-G-S-E-AB](#) [SEI-110-02-G-S-E-AT](#) [SEI-115-02-GF-S](#) [SEI-125-02-GF-S-M-AB](#) [SEI-125-02-G-S-E](#) [SEI-130-02-GF-S-E](#) [SEI-130-02-G-S-E-AT](#) [SEI-115-02-G-S](#) [SEI-115-02-G-S-AB-TR](#) [SEI-115-02-G-S-AT](#) [SEI-120-02-G-S-E-AT](#) [SEI-125-02-GF-S-AT](#) [SEI-130-02-GF-S-E-AT-TR](#) [SEI-130-02-GF-S-M-AB](#) [SEI-130-02-G-S-AB](#) [SEI-125-02-GF-S-M-AT](#) [SEI-130-02-GF-S-E-AB](#) [SEI-130-02-G-S-E-AT-TR](#) [SEI-106-02-GF-S-AT](#) [SEI-111-02-G-S](#) [SEI-115-02-G-S-E](#) [SEI-120-02-GF-S-M](#) [SEI-130-02-G-S-M](#) [SEI-108-02-GF-S-AT](#)