

RUGGED TIGER EYE™ SYSTEMS

(1.27 mm) .050" PITCH

MAX
3.7
A m p s

8
G b p s

FEATURES & BENEFITS


- Screw down, locking clip, friction latching and weld tab ruggedizing options
- Shrouded, polarized and keyed
- Surface mount or through-hole tails
- High-density, four row design (FOLC/MOLC Series)
- Discrete wire assemblies available in single or double row, 28 and 30 AWG PVC or *Teflon™ Fluoropolymer (See pages 238-239). Contact asp@samtec.com for custom solutions.
- Cable components (ISDF/CC03) and tooling available: samtec.com/tooling
- Severe Environment Testing qualified (SFM/TFM); aligns with MIL-DTL-55302. Visit samtec.com/set

*Teflon™ is a trademark of The Chemours Company FC, LLC used under license by Samtec.


KEY SPECIFICATIONS

SERIES	STACK HEIGHTS	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	VOLTAGE RATING	MAX. CYCLES	LEAD-FREE SOLDERABLE
SFM/TFM	6 to 12 mm	Black LCP	BeCu (SFM) Phosphor Bronze (TFM)	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	3.7A per pin (2 pins powered)	275 VAC	10,000 with 30 μ" (0.76 μm) Au	Yes
SFC/TFC	6 to 12 mm	Black LCP	Phosphor Bronze	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	3.1 A per pin (2 pins powered)	350 VAC	(Call Samtec for E.L.P.™ plating option)	Yes

**TIGER™
EYE**
CONTACT









IDC cable assemblies with rugged strain relief (FFSD/FFMD, FFTP/FMTP)





Locking for increased unmating force (SFML/TFML)

(1.27 mm) .050" PITCH • COST-EFFECTIVE HEADER/SOCKET

SFC	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	OPTIONS		
		04, 05, 10, 15, 20, 25, 30, 35, 40, 45, 50 (Standard sizes)	-T1 = Through-hole Tiger Eye™ LITE -T2 = Surface Mount Tiger Eye™ LITE	-F = Gold flash on contact, Matte Tin on tail -L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail		-A = Alignment Pin -K = (4.00 mm) .157" DIA Polyimide film Pick & Place Pad -TR = Tape & Reel (-T2 only) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-T2 only)		
SFC Board Mates: TFC Cable Mates: TFSD, TFSDT								
								
							-T1	-T2

SFC
Board Mates:
TFC
Cable Mates:
TFSD, TFSDT

View complete specifications at: samtec.com?SFC

TFC	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	OPTIONS																														
		03, 04, 06, 08 (Lead Style -01 & -02 only) 05, 07, 10, 15, 20, 25, 30, 35, 40, 45, 50 (Standard sizes)	-X1 = Through-hole -X2 = Surface Mount	-F = Gold flash on post, Matte Tin on tail -L = 15 μ" (0.38 μm) Gold on post, Matte Tin on tail		-RA = Right-angle (-01 only) -A = Alignment Pin -LC = Locking Clip (Manual Placement required) (not available with -RA) -K = (6.75 mm) .266" DIA Polyimide film Pick & Place Pad (not available with -RA) -P = Plastic Pick & Place Pad (5 positions min.) (not available with -RA) -TR = Tape & Reel (-X2 only) (not available with -RA) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-X2 only) (not available with -RA)																														
TFC Board Mates: SFC Cable Mates: SFSD, SFSDT		 																																		
		<table><tr><th>SMT LEAD STYLE</th><th>A</th><th>B</th></tr><tr><td>-02</td><td>(5.72) .225</td><td>(3.38) .133</td></tr><tr><td>-12</td><td>(7.49) .295</td><td></td></tr><tr><td>-22</td><td>(9.27) .365</td><td>(3.30) .130</td></tr><tr><td>-32</td><td>(11.18) .440</td><td></td></tr></table> <table><tr><th>TH LEAD STYLE</th><th>A</th><th>B</th></tr><tr><td>-01</td><td>(5.59) .220</td><td>(3.38) .133</td></tr><tr><td>-11</td><td>(7.37) .290</td><td></td></tr><tr><td>-21</td><td>(9.14) .360</td><td>(3.30) .130</td></tr><tr><td>-31</td><td>(11.05) .435</td><td></td></tr></table>					SMT LEAD STYLE	A	B	-02	(5.72) .225	(3.38) .133	-12	(7.49) .295		-22	(9.27) .365	(3.30) .130	-32	(11.18) .440		TH LEAD STYLE	A	B	-01	(5.59) .220	(3.38) .133	-11	(7.37) .290		-21	(9.14) .360	(3.30) .130	-31	(11.05) .435	
SMT LEAD STYLE	A	B																																		
-02	(5.72) .225	(3.38) .133																																		
-12	(7.49) .295																																			
-22	(9.27) .365	(3.30) .130																																		
-32	(11.18) .440																																			
TH LEAD STYLE	A	B																																		
-01	(5.59) .220	(3.38) .133																																		
-11	(7.37) .290																																			
-21	(9.14) .360	(3.30) .130																																		
-31	(11.05) .435																																			
Note:																																				

Note:
Some lengths, styles and
options are non-standard,
non-returnable.

View complete specifications at: samtec.com?TFC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SFC-140-T2-L-D-A](#) [SFC-105-T2-L-D-A](#) [SFC-110-T1-F-D-A](#) [SFC-150-T2-L-D-A](#) [SFC-125-T2-F-D-A](#) [SFC-120-T2-L-D-K-TR](#) [SFC-110-T2-L-D-A](#) [SFC-125-T2-L-D-A](#) [SFC-110-T2-F-D-A-K-TR](#) [SFC-115-T2-L-D-A-K-TR](#) [SFC-115-T2-F-D-SFC-115-T1-F-D](#) [SFC-120-T2-L-D-A-K-TR](#) [SFC-110-T2-F-D-A](#) [SFC-110-T2-L-D](#) [SFC-120-T2-F-D-A-K-TR](#) [SFC-150-T2-F-D-A](#) [SFC-150-T2-F-D-A-K-TR](#) [SFC-110-T2-L-D-A-K-TR](#) [SFC-130-T2-F-D-A](#) [SFC-135-T2-L-D-A](#) [SFC-130-T2-L-D-A](#) [SFC-120-T2-F-D-A](#) [SFC-115-T2-F-D-K-TR](#) [SFC-115-T2-F-D-A](#) [SFC-140-T2-F-D-A](#) [SFC-110-T2-F-D-K-TR](#) [SFC-125-T2-L-D-A-K-TR](#) [SFC-145-T2-F-D-A](#) [SFC-115-T2-L-D](#) [SFC-110-T1-L-D](#) [SFC-105-T2-F-D](#) [SFC-120-T2-L-D-A-K](#) [SFC-115-T2-L-D-A-K](#) [SFC-120-T2-L-D-A](#) [SFC-110-T1-F-D](#) [SFC-105-T2-F-D-A](#) [SFC-115-T2-L-D-A](#) [SFC-110-T2-F-D](#) [SFC-125-T2-F-D-A-K-TR](#) [SFC-120-T1-F-D](#) [SFC-105-T2-LM-D-A-K-TR](#) [SFC-105-T2-F-D-K-TR](#) [SFC-110-T2-L-D-K-TR](#) [SFC-110-T1-L-D-A](#) [SFC-107-T2-F-D](#) [SFC-105-T1-L-D](#) [SFC-115-T2-F-D-A-K-TR](#) [SFC-105-T2-L-D-A-K-TR](#) [SFC-105-T2-LM-D](#) [SFC-125-T1-L-D-A](#) [SFC-140-T1-F-D](#) [SFC-110-T2-L-D-A-K](#) [SFC-120-T2-F-D](#) [SFC-130-T1-L-D](#) [SFC-130-T2-L-D-A-K-TR](#) [SFC-150-T1-L-D-A](#) [SFC-150-T2-F-D](#) [SFC-125-T1-L-D](#) [SFC-120-T2-L-D](#) [SFC-115-T1-F-D-A](#) [SFC-125-T1-F-D](#) [SFC-130-T1-F-D](#) [SFC-115-T1-L-D-A](#) [SFC-145-T2-L-D-A](#) [SFC-105-T1-F-D](#) [SFC-115-T1-L-D](#) [SFC-125-T2-F-D](#) [SFC-150-T1-F-D-A](#) [SFC-110-T2-F-D-A-K](#) [SFC-130-T2-F-D-A-K-TR](#) [SFC-140-T2-L-D-A-K-TR](#) [SFC-150-T2-LM-D-A](#) [SFC-105-T1-L-D-A](#) [SFC-120-T1-F-D-A](#) [SFC-110-T2-L-D-K](#) [SFC-115-T2-F-D-A-K](#) [SFC-120-T2-F-D-A-K](#) [SFC-135-T2-F-D-A-K-TR](#) [SFC-120-T2-F-D-K-TR](#) [SFC-107-T1-L-D](#) [SFC-140-T2-F-D-A-K-TR](#) [SFC-115-T2-F-D-K](#) [SFC-110-T2-F-D-K](#) [SFC-110-T2-L-D-LC](#) [SFC-105-T2-L-D-K](#) [SFC-125-T2-L-D-K](#) [SFC-106-T2-L-D-K](#) [SFC-104-T2-F-D](#) [SFC-104-T2-L-D-A](#) [SFC-123-T2-L-D-A-K-TR](#) [SFC-123-T2-L-D-A-K](#) [SFC-103-T2-F-D-A](#) [SFC-102-T2-L-D-A](#)