




REV.	DESCRIPTION	DATE	APPROVED
E	Engineering Release.	04/29/14	M. C.



PART NO.	A ±.032 (.8)	B ±.016 (.4)	C ±.008 (.2)
UDD-200-D	2.0 (50.8)	1.0 (25.4)	-
UDD-250-D	2.5 (63.5)	1.5 (38.1)	-
UDD-300-D	3.0 (76.2)	2.0 (50.8)	-
UDD-350-D	3.5 (88.9)	2.5 (63.5)	-
UDD-400-D	4.0 (101.6)	3.0 (76.2)	-
UDD-450-D	4.5 (114.3)	3.5 (88.9)	-
UDD-500-D	5.0 (127.0)	4.0 (101.6)	-
UDD-550-D	5.5 (139.7)	4.5 (114.3)	-
UDD-600-D	6.0 (152.4)	5.0 (127.0)	-
UDD-650-D	6.5 (165.1)	5.5 (139.7)	-
UDD-700-D	7.0 (177.8)	6.0 (152.4)	-
UDD-750-D	7.5 (190.5)	6.5 (165.1)	-
UDD-800-D	8.0 (203.2)	7.0 (177.8)	-
UDD-850-D	8.5 (215.9)	7.5 (190.5)	3.75 (95.3)
UDD-900-D	9.0 (228.6)	8.0 (203.2)	4.00 (101.6)
UDD-950-D	9.5 (241.3)	8.5 (215.9)	4.25 (108.0)
UDD-1000-D	10.0 (254.0)	9.0 (228.6)	4.50 (114.3)
UDD-1050-D	10.5 (266.7)	9.5 (241.3)	4.75 (120.7)
UDD-1100-D	11.0 (279.4)	10.0 (254.0)	5.00 (127.0)



NOTE:

4. MATERIAL: NYLON 66, 15% GLASS FILLED, BLACK, 94V-0
3. INTEGRATED STATIC DISSIPATIVE CLIPS PROVIDE SURFACE RESISTIVITY OF 10^6 TO 10^9 OHMS.
2. RECOMMENDED CARD THICKNESS .062" - .079" [1.6mm - 2.0mm]
1. RECOMMENDED PANEL THICKNESS 0.047" - 0.090" (1.2mm - 2.3mm)

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u>	<u>ANGULAR</u>	TITLE: UNIVERSAL CARD GUIDE W/ STATIC DISSIPATIVE CLIP	
.X ±.1	X° ± 1°		
.XX ±.02			
.XXX ±.010			
DESIGNED: Ty Yin	DATE: 11/26/13	PART NO: UDD-XXX-D	REVISION E
CHECKED: B. Oliver	DATE: 11/26/13	CAGE CODE : 32559	SHEET # 1 OF 1
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[UDD-200-D](#) [UDD-250-D](#) [UDD-300-D](#) [UDD-350-D](#) [UDD-400-D](#) [UDD-450-D](#) [UDD-500-D](#) [UDD-550-D](#) [UDD-600-D](#)
[UDD-650-D](#) [UDD-700-D](#) [UDD-750-D](#) [UDD-800-D](#) [UDD-850-D](#) [UDD-900-D](#) [UDD-950-D](#) [UDD-1000-D](#) [UDD-1050-D](#)
[UDD-1100-D](#)