


ONE-PIECE INTERFACES

(2.54 mm) .100" PITCH • SIB/SIR1 SERIES



SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer
Contact Material:
Phosphor Bronze
Plating:
Au or Sn over
50 μ " (1.27 μ m) Ni
Current Rating:
2.6 A per pin
(1 pin powered)
Operating Temp Range:
-55 °C to +125 °C

SIB

- 1

NO. OF
POSITIONS

- 02

PLATING
OPTION

- S

OPTION


02 thru 30
(Per Row)

-F
= Gold flash
on contact,
Matte Tin on tail

-LC
= Locking
Clip
(Manual
placement
required)

PROCESSING



Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.10 mm) .004" max (02-19)
(0.15 mm) .005" max (20-30)*
*(.004" stencil solution
may be available; contact
ipg@samtec.com)



Notes:

The SIB Series
is intended for vertical
mating only.

Some lengths, styles and
options are non-standard,
non-returnable.



-LC

SPECIFICATIONS

Insulator Material:
Black LCP
Contact Material:
Phosphor Bronze
Weld Tab:
Phosphor Bronze
Plating:
Au or Sn over
50 μ " (1.27 μ m) Ni
Current Rating:
2.8 A per pin
(1 pin powered)

SIR1

-

NO. OF
POSITIONS

-

PLATING
OPTION

- S

-

OPTION

-03, -05, -10, -15
(Per Row)

-L
= 10 μ " (0.25 μ m)
Gold on contact,
Matte Tin on tail

-S
= 30 μ " (0.76 μ m)
Gold on contact,
Matte Tin on tail

-A
= Alignment Pin




-K
= (4.00 mm) .157"
DIA Polyimide
Film Pick &
Place Pad

-TR
= Tape & Reel

-FR
= Full Reel
Tape & Reel
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)

PROCESSING

Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.10 mm) .004" max



Note:

Some lengths, styles and
options are non-standard,
non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[SIB-105-02-F-S-LC](#) [SIB-116-02-F-S-LC](#) [SIB-106-02-F-S](#) [SIB-102-02-F-S-LC](#) [SIB-105-02-F-S](#) [SIB-106-02-F-S-LC](#)
[SIB-112-02-F-S-LC](#) [SIB-104-02-F-S](#) [SIB-102-02-F-S](#) [SIB-104-02-F-S-LC](#) [SIB-107-02-F-S-LC](#) [SIB-108-02-F-S](#) [SIB-](#)
[110-02-F-S](#) [SIB-107-02-F-S](#) [SIB-111-02-F-S-LC](#) [SIB-108-02-F-S-LC](#) [SIB-110-02-F-S-LC](#) [SIB-103-02-F-S-LC](#) [SIB-](#)
[125-02-F-S-LC](#) [SIB-114-02-F-S](#) [SIB-113-02-F-S-LC](#) [SIB-115-02-F-S](#) [SIB-120-02-F-S](#) [SIB-115-02-F-S-LC](#) [SIB-118-](#)
[02-F-S-LC](#) [SIB-130-02-F-S](#) [SIB-114-02-F-S-LC](#) [SIB-116-02-F-S](#) [SIB-124-02-F-S-LC](#) [SIB-125-02-F-S](#) [SIB-122-02-F-S](#)
[SIB-126-02-F-S-LC](#) [SIB-117-02-F-S-LC](#) [SIB-122-02-F-S-LC](#) [SIB-126-02-F-S](#) [SIB-109-02-F-S](#) [SIB-117-02-F-S](#) [SIB-](#)
[121-02-F-S-LC](#) [SIB-127-02-F-S](#) [SIB-118-02-F-S](#) [SIB-111-02-F-S](#) [SIB-121-02-F-S](#) [SIB-124-02-F-S](#) [SIB-123-02-F-S-](#)
[LC](#) [SIB-119-02-F-S](#) [SIB-128-02-F-S](#) [SIB-128-02-F-S-LC](#) [SIB-129-02-F-S-LC](#) [SIB-103-02-F-S](#) [SIB-119-02-F-S-LC](#)
[SIB-130-02-F-S-LC](#) [SIB-109-02-F-S-LC](#) [SIB-112-02-F-S](#) [SIB-113-02-F-S](#) [SIB-123-02-F-S](#) [SIB-127-02-F-S-LC](#) [SIB-](#)
[120-02-F-S-LC](#)