


REV.	DESCRIPTION	DATE	APPROVED
F	Engineering Release	04/09/14	J. C.
G	Engineering Update w/o Changes	08/09/16	J. C.

For Use With:
Wire Harness: BIVAR L2CON-24
or
Housing : LEOCO 2530S020000
Terminal : LEOCO 2533TPB0000



LED POLARITY





Table 1: Assembly Configurations

Part Number	LED P/N	Color	Dominant Wavelength (nm) / CCT (K)		Typical Luminous Flux (lm)	Cree P/N Reference
			Min.	Max.		
L22-MLRGBW	BDL-1483	Red	620	630	45.7	XMLCTW-A0-0000-00C3ABB02
		Green	520	535	87.4	
		Blue	450	465	13.9	
		Cool White	5700	8000	100	

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u>	<u>ANGULAR</u>	 	
.X ± .1	X° ± 1°		
.XX ± .02			
.XXX ± .010			
DESIGNED: B. Oliver	DATE: 07/22/13	PART NO: L22-MLRGBW	REVISION: G
CHECKED: J. Chiang	DATE: 07/22/13	CAGE CODE : 32559	SHEET # 1 OF 1
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[L22-MLRGBW](#)