



ITEM	QTY	PART NUMBER	PART DESCRIPTION
1	1	LTM-XXX	Molded, Self-Retaining LED Mount
2	1	5XX-F	T-1 3/4 (5mm) Flanged LED, See Pages 2 & 3

REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	09/30/03	M. C.
B	LED Data Update	07/28/10	T. Y.
C	Engineering Update w/o Changes	06/25/16	J. C.

PART NO.	H	PART NO.	H	PART NO.	H
LTM-120	.120(3.1)	LTM-300	.300(7.6)	LTM-490	.490(12.5)
LTM-130	.130(3.3)	LTM-310	.310(7.9)	LTM-500	.500(12.7)
LTM-140	.140(3.6)	LTM-320	.320(8.1)	LTM-520	.520(13.2)
LTM-150	.150(3.8)	LTM-330	.330(8.4)	LTM-550	.550(14.0)
LTM-160	.160(4.1)	LTM-340	.340(8.6)	LTM-570	.570(14.5)
LTM-170	.170(4.3)	LTM-350	.350(8.9)	LTM-600	.600(15.2)
LTM-180	.180(4.6)	LTM-360	.360(9.1)	LTM-620	.620(15.8)
LTM-190	.190(4.8)	LTM-370	.370(9.4)	LTM-650	.650(16.5)
LTM-200	.200(5.1)	LTM-380	.380(9.7)	LTM-670	.670(17.0)
LTM-210	.210(5.3)	LTM-390	.390(9.9)	LTM-700	.700(17.8)
LTM-220	.220(5.6)	LTM-400	.400(10.2)	LTM-720	.720(18.3)
LTM-230	.230(5.8)	LTM-410	.410(10.4)	LTM-750	.750(19.1)
LTM-240	.240(6.1)	LTM-420	.420(10.7)	LTM-770	.770(19.6)
LTM-250	.250(6.4)	LTM-430	.430(10.9)	LTM-800	.800(20.3)
LTM-260	.260(6.6)	LTM-440	.440(11.2)	LTM-820	.820(20.8)
LTM-270	.270(6.9)	LTM-450	.450(11.4)	LTM-850	.850(21.6)
LTM-280	.280(7.1)	LTM-460	.460(11.7)	LTM-870	.870(22.1)
LTM-290	.290(7.4)	LTM-480	.480(12.2)	LTM-900	.900(22.9)




EXAMPLE:
LTM5005GD
 LED Color & Lens Appearance.
 Omit -F when ordering.
 LTM Height "H"
 Series



ABSOLUTE MAXIMUM RATINGS (Ta = 25°C)

REVERSE VOLTAGE	5V
REVERSE CURRENT (VR=5V)	100μA
OPERATING TEMPERATURE RANGE	-25°C ~ 85°C
STORAGE TEMPERATURE	-30°C ~ 100°C
LEAD SOLDERING TEMPERATURE (1/16" FROM BODY)	260°C for 5 Seconds

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR[®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974			
<u>DECIMALS</u>	<u>ANGULAR</u>				
.X ± .1	X° ± 1°				
.XX ± .02					
.XXX ± .010		TITLE: MOLDED, SELF-RETAINING T-1 3/4 (5mm) LED MOUNT ASSEMBLY			
DESIGNED:	DATE:			PART NO:	REVISION:
D. Green	09/30/03			LTMXXX5XX	C
CHECKED:	DATE:	CAGE CODE : 32559		SHEET # 1 OF 3	
M. Chen	09/30/03	CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		

LED Assy. No.	Peak Wave Length λp(nm)	Emitted Color	Lens Appearance	Electro-Optical Data			Viewing Angle 2 θ ½ (Deg)	LED P/N
				Vf (V)		Iv (mcd)		
				TYP	MAX	TYP		
STANDARD				Data @ 20mA				
LTMXXX5AC	605	AMBER	WATER CLEAR	2.0	2.8	40	35	5AC-F
LTMXXX5AD	605	AMBER	DIFFUSED	2.0	2.8	25	40	5AD-F
LTMXXX5AT	605	AMBER	TINTED	2.0	2.8	40	35	5AT-F
LTMXXX5BWC	430	BLUE	WATER CLEAR	4.0	4.5	30	25	5BWC-F
LTMXXX5BWD	430	BLUE	DIFFUSED	4.0	4.5	15	40	5BWD-F
LTMXXX5BWT	430	BLUE	TINTED	4.0	4.5	30	25	5BWT-F
LTMXXX5GC	568	GREEN	WATER CLEAR	2.1	2.8	40	35	5GC-F
LTMXXX5GD	568	GREEN	DIFFUSED	2.1	2.8	25	40	5GD-F
LTMXXX5GT	568	GREEN	TINTED	2.1	2.8	40	35	5GT-F
LTMXXX5HC	625	HE RED	WATER CLEAR	2.0	2.8	50	35	5HC-F
LTMXXX5HD	625	HE RED	DIFFUSED	2.0	2.8	40	40	5HD-F
LTMXXX5HT	625	HE RED	TINTED	2.0	2.8	50	35	5HT-F
LTMXXX5PGC	555	PURE GREEN	WATER CLEAR	2.2	2.8	10	35	5PGC-F
LTMXXX5PGD	555	PURE GREEN	DIFFUSED	2.2	2.8	10	40	5PGD-F
LTMXXX5PGT	555	PURE GREEN	TINTED	2.2	2.8	10	35	5PGT-F
LTMXXX5RC	700	RED	WATER CLEAR	2.1	2.8	2	35	5RC-F
LTMXXX5RD	700	RED	DIFFUSED	2.1	2.8	1.5	40	5RD-F
LTMXXX5RT	700	RED	TINTED	2.1	2.8	2	35	5RT-F
LTMXXX5YC	590	YELLOW	WATER CLEAR	2.0	2.8	40	35	5YC-F
LTMXXX5YD	590	YELLOW	DIFFUSED	2.0	2.8	25	40	5YD-F
LTMXXX5YT	590	YELLOW	TINTED	2.0	2.8	40	35	5YT-F

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL.: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
DESIGNED: D. Green	DATE: 09/30/03	 TITLE: MOLDED, SELF-RETAINING T-1 3/4 (5mm) LED MOUNT ASSEMBLY	
		PART NO: LTMXXX5XX	REVISION: C
CHECKED: M. Chen	DATE: 09/30/03	CAGE CODE : 32559	SHEET # 2 OF 3
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		

LED Assy. No.	Peak Wave Length λp(nm)	Emitted Color	Lens Appearance	Electro-Optical Data			Viewing Angle 2 θ ½ (Deg)	LED P/N
				Vf (V)		Iv (mcd)		
				TYP	MAX	TYP		
LOW CURRENT				Data @ 2mA				
LTMXXX5ADL	605	AMBER	DIFFUSED	2.0	2.6	4	40	5ADL-F
LTMXXX5BWDL	430	BLUE	DIFFUSED	3.8	4.2	4	40	5BWDL-F
LTMXXX5GDL	568	GREEN	DIFFUSED	2.1	2.6	4	40	5GDL-F
LTMXXX5HDL	625	HE RED	DIFFUSED	2.0	2.6	5	40	5HDL-F
LTMXXX5PGDL	555	PURE GREEN	DIFFUSED	2.1	2.6	1	40	5PGDL-F
LTMXXX5SRDL	645	RED	DIFFUSED	1.7	2.3	6	40	5SRDL-F
LTMXXX5YDL	590	YELLOW	DIFFUSED	2.0	2.6	4	40	5YDL-F

LED Assy. No.	Peak Wave Length λp(nm)	Emitted Color	Lens Appearance	Electro-Optical Data			Viewing Angle 2 θ ½ (Deg)	LED P/N
				Vf (V)		Iv (mcd)		
				TYP	MAX	TYP		
5 VOLT				Data @ 5V				
LTMXXX5AD5V	605	AMBER	DIFFUSED	-	5.0	25	40	5AD5V-F
LTMXXX5BWD5V	430	BLUE	DIFFUSED	-	5.0	15	40	5BWD5V-F
LTMXXX5GD5V	568	GREEN	DIFFUSED	-	5.0	25	40	5GD5V-F
LTMXXX5HD5V	625	HE RED	DIFFUSED	-	5.0	30	40	5HD5V-F
LTMXXX5RD5V	700	RED	DIFFUSED	-	5.0	1.5	40	5RD5V-F
LTMXXX5YD5V	590	YELLOW	DIFFUSED	-	5.0	25	40	5YD5V-F

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL.: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
		TITLE: MOLDED, SELF-RETAINING T-1 3/4 (5mm) LED MOUNT ASSEMBLY	
DESIGNED: D. Green	DATE: 09/30/03	PART NO: LTMXXX5XX	REVISION: C
CHECKED: M. Chen	DATE: 09/30/03	CAGE CODE : 32559	SHEET # 3 OF 3
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[LTM1205HC](#) [LTM1505GC](#) [LTM1205GC](#) [LTM1405HC](#) [LTM3205SRDL](#) [LTM3205YDL](#) [LTM1505HC](#) [LTM1405GC](#)
[LTM1605GC](#) [LTM1605HC](#) [LTM3205GDL](#)