






ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	ORFLP1	1mm Flexible Light Pipe ORCA Adapter
2	1	RXXXXX-4-0045	4.6mm Dome 4-Pin Super Flux ORCA LED, 45°

REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release.	04/06/09	T. Y.
B	Updated LED Optical Characteristics.	08/29/15	J. C.



NOTE: SEE PAGE 2 FOR POLARITY



ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

REVERSE VOLTAGE	_____	5V
REVERSE CURRENT	_____	10uA
OPERATING TEMPERATURE RANGE	_____	-25°C ~ +80°C
STORAGE TEMPERATURE	_____	-30°C ~ +80°C
LEAD SOLDERING TEMPERATURE(1/16" FROM BODY)	_____	260°C FOR 5 SECONDS

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR® 4 THOMAS, IRVINE, CA. 92618 TEL.: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .2	X° ± 1°		
.XX ± .02			
.XXX ± .010			
DESIGNED: Raffy Paje	DATE: 04/06/09	TITLE: 1mm FLEXIBLE LIGHT PIPE ORCA ADAPTER W/ LED	
CHECKED: F. Jensen	DATE: 04/06/09	PART NO: ORFLP1-XXX	REVISION: B
		CAGE CODE : 32559	SHEET # 1 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		

Assy P/N	LED P/N	Emitted Color	Dominant Length λd(nm) / CCT (K)	Lens Appearance	Absolute Max. Ratings			Vf (V)			Iv (mcd)		Viewing Angle 2 θ½ (Deg)	POLARITY DIAGRAM
			Pd (mW)		If (mA)	Peak If (mA)								
			MIN - MAX		MIN	TYP	MAX	MIN	TYP					
SINGLE COLOR LED ASSEMBLIES (20mA)														
ORFLP1-BLU	R20BLU-4-0045	BLUE	465 - 475	WATER CLEAR	220	50	100	2.7	3.2	3.6	5000	8000	45	FIG. A
ORFLP1-GRN	R20GRN-4-0045	GREEN	517 - 527		220	50	100	2.7	3.2	3.6	15000	25000	45	FIG. A
ORFLP1-WHT	R20WHT-4-0045	WHITE	6000K		220	50	100	2.7	3.2	3.6	10000	16000	45	FIG. A
SINGLE COLOR LED ASSEMBLIES (50mA)														
ORFLP1-RED	R50RED-4-0045	RED	620 - 635	WATER CLEAR	140	80	160	1.8	2.4	2.6	12000	18000	45	FIG. A
ORFLP1-YLW	R50YLW-4-0045	YELLOW	588 - 596		140	80	160	1.8	2.4	2.6	12000	18000	45	FIG. A
BI-COLOR LED ASSEMBLIES (50mA)														
ORFLP1-RG	R50RG2-4-0045	RED	617 - 630	WATER CLEAR	150	80	160	1.8	2.4	2.6	3000	4000	45	FIG. B
		GREEN	515 - 525		220	80	150	3.0	3.4	3.8	6000	10000		
ORFLP1-RB	R50RB2-4-0045	RED	617 - 630	WATER CLEAR	150	80	160	1.8	2.4	2.6	3000	4000	45	FIG. C
		BLUE	460 - 470		220	80	150	3.0	3.4	3.8	1000	3000		
ORFLP1-BG	R50BG2-4-0045	BLUE	460 - 470	WATER CLEAR	220	80	150	3.0	3.4	3.8	1000	3000	45	FIG. D
		GREEN	515 - 525		220	80	150	3.0	3.4	3.8	6000	10000		
ORFLP1-RGB	R50RGB-4-0045	RED	617 - 630	WATER CLEAR	150	80	160	1.8	2.4	2.6	3000	4000	45	FIG. E
		GREEN	515 - 525		220	80	150	3.0	3.4	3.8	6000	10000		
		BLUE	460 - 470		220	80	150	3.0	3.4	3.8	1000	3000		




FIG. A




FIG. B




FIG. C




FIG. D




FIG. E

NOTES:

1. INDIVIDUAL LED P/N DATA AVAILABLE @ WWW.BIVAR.COM.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) DECIMALS ANGULAR		 4 THOMAS, IRVINE, CA. 92618 TEL.: (949) 951-8808 FAX: (949) 951-3974	
DESIGNED: Raffy Paje	DATE: 04/06/09		
CHECKED: F. Jensen	DATE: 04/06/09	TITLE: 1mm FLEXIBLE LIGHT PIPE ORCA ADAPTER W/ LED PART NO: ORFLP1-XXX REVISION: B CAGE CODE : 32559 SHEET # 2 OF 2 CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[ORFLP1-GRN](#) [ORFLP1-YLW](#) [ORFLP1-BLU](#) [ORFLP1-RED](#) [ORFLP1-RG](#) [ORFLP1-RGB](#) [ORFLP1-WHT](#) [ORFLP1-BG](#) [ORFLP1-RB](#) [OR1-1.5-RGB-F7P-2](#) [OR1-1.5-RGB-F7P-4](#) [OR1-1.5-RGB-F7P-5](#) [OR1-1.5-RGB-F7P-6](#) [OR1-1.5-RGB-F7P-9](#) [OR1-10.0-GRN-F4P-2](#) [OR1-10.0-GRN-F4P-4](#) [OR1-10.0-GRN-F4P-5](#) [OR1-10.0-GRN-F4P-6](#) [OR1-10.0-GRN-F4P-9](#) [OR1-10.0-RED-F4P-2](#) [OR1-10.0-RED-F4P-4](#) [OR1-10.0-RED-F4P-5](#) [OR1-10.0-RED-F4P-6](#) [OR1-10.0-RED-F4P-9](#) [OR1-24.0-RG-F4P-2](#) [OR1-24.0-RG-F4P-4](#) [OR1-24.0-RG-F4P-5](#) [OR1-24.0-RG-F4P-6](#) [OR1-24.0-RG-F4P-9](#) [OR1-36.0-RG-F4P-2](#) [OR1-36.0-RG-F4P-4](#) [OR1-36.0-RG-F4P-5](#) [OR1-36.0-RG-F4P-6](#) [OR1-36.0-RG-F4P-9](#) [OR1-6.0-RGB-F7P-2](#) [OR1-6.0-RGB-F7P-4](#) [OR1-6.0-RGB-F7P-5](#) [OR1-6.0-RGB-F7P-6](#) [OR1-6.0-RGB-F7P-9](#) [OR1-8.0-BLU-F4P-2](#) [OR1-8.0-BLU-F4P-4](#) [OR1-8.0-BLU-F4P-5](#) [OR1-8.0-BLU-F4P-6](#) [OR1-8.0-BLU-F4P-9](#) [OR1-8.0-RED-F4P-2](#) [OR1-8.0-RED-F4P-4](#) [OR1-8.0-RED-F4P-5](#) [OR1-8.0-RED-F4P-6](#) [OR1-8.0-RED-F4P-9](#)