



T1M-07-F-SV-L



T1M-10-GF-DV

T1M-05-F-SH-L



T1M-10-GF-DH



(1.00 mm) .0394"

T1M SERIES

DISCRETE WIRE COMPONENTS

Mates with:
S1SS(T), S1SD(T)

SPECIFICATIONS

For complete specifications see www.samtec.com?T1M

Insulator Material:

Natural LCP

Terminal Material:

Phosphor Bronze

Weld Tab:

Phosphor Bronze

Plating:

Au or Sn over

50 μ " (1.27 μ m) Ni

Operating Temp Range

(S1SX(T)/T1M):

-10 °C to +85 °C (PVC)

-40 °C to +125 °C (Teflon®

cable with -GF plated contact)

Current Rating

(S1SX (28 AWG)/T1M):

3.3 A per pin (1 pin powered)

Voltage Rating:

250 VAC/353 VDC

RoHS Compliant:


Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




FILE NO. E111594



OTHER SOLUTIONS

- Without latch
- Other sizes



Note:
Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[T1M-16-F-SV-L](#)