

TCS08-08-D-02.00-01-N-R

(2.00 mm) .0787"

TCS08 SERIES

TIGER EYE™ IDC SOCKET CABLE

Mates with:

TMM, TMMH, STMM,
MMT, TW, MTMM, EHT,
ETMM (-SR), ZSTMM

SPECIFICATIONS

For complete specifications
see www.samtec.com/TCS08

Insulator Material:

Black Glass Filled Polyester

Contact:

BeCu

Plating:

Au or Sn over 50 μ" (1.27 μm) Ni

Wire:

28 AWG 7/36 Stranded,

Tinned, Copper with

Gray PVC Insulator

Current Rating (TCS08/STMM):

2.8 A per pin

(2 pins powered)

Operating Temp Range:

-40 °C to +105 °C

Lead Size Accepted:

(0.48 mm) .019" to

(0.53 mm) .021"

Insertion Depth:

(2.87 mm) .113" to

(3.17 mm) .125"

RoHS Compliant:

Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



FILE NO. E111594

ALSO AVAILABLE (MOQ Required)





- Other sizes
- Other platings

POLARIZING KEY



Specify PK-01-07 for polarizing key
(Available in wheels of six each).

Also polarizes SMM
Series socket strips.



Note:
TCS08 Series assemblies are
non-standard, non-returnable.




Specify "XX" as position
number. Same position
will be polarized on
both ends.




Breakout starts with Number 1
lead indicated by brown wire or
red stripe. Shown on top side.







EJECTOR HEADERS & LOCKING CLIPS



See TMM Series.



See EHT Series.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TCSD-25-D-04.00-01-N](#)