### 4-Pin Super Flux White LED Lamp Orca R Series (5mm Dome)

### BIVVR

#### R20WHT-5-0080


- **RoHS Compliant**
- Low Profile Dome Lens
- Automatic Insertion Compatible Tubular Packaging
- **Automatic Placement Compatible**
- **High Intensity Output**
- **High Power Efficiency**



Bivar R20WHT-5-0080 comes with low profile package design incorporating higher forward current to maximize intensity while minimizing the number of LEDs required to achieve uniform and enhanced light distribution. Low power consumption with quick response time means savings in electricity.

Bivar R20WHT-5-0080 can be coupled with reflectors or lenses for optimal light distribution needs. Typical applications are automotive exterior lighting, decorative interior or exterior lighting, specialty stage lighting, and electronic signage.

Part Number	Material	Emitted Color	Intensity Typ. mcd	Lens Color	Viewing Angle	
R20WHT-5-0080	InGaN/Sapphire	White	6000	Water Clear	80°	



#### **Outline Drawings Notes:**

- 1. All dimensions are in inches [millimeters].
  2. Standard tolerance: ±0.010" unless otherwise noted.
  3. Tolerance of overall epoxy outline: ±0.020" unless otherwise noted.
  4. Epoxy meniscus may extend to 0.060" max.







# 4-Pin Super Flux White LED Lamp R20WHT-5-0080



#### **Absolute Maximum Ratings**

 $T_A = 25$ °C unless otherwise noted

Power Dissipation	220 mW
Forward Current ( DC )	50 mA
Peak Forward Current <sup>1</sup>	100 mA
Electrostatic Discharge ( Class1 )	2000 V
Reverse Voltage	5 V
Operating Temperature Range	-25 ~ +80°C
Storage Temperature Range	-30 ~ +80°C
Lead Soldering Temperature ( 3 mm from the base of the epoxy bulb ) <sup>2</sup>	260°C

#### **Electrical Characteristics**

 $T_A = 25$ °C &  $I_F = 20$  mA unless otherwise noted


Emitting Color	Forward Voltage (V) <sup>1</sup>		Recommend Forward Current (mA)	Reverse Current (µA) V <sub>R</sub> =5V	Chromaticity Coordinates (XY) <sup>2</sup> / CCT (Kelvin)	Luminous Intensity (mcd) <sup>3</sup>		Viewing Angle 2 Θ ½ (deg)	
	MIN	TYP	MAX	TYP	MAX	TYP	MIN	TYP	TYP
White	2.7	3.2	3.6	20	10	X=0.31 , Y=0.33 6000K	3000	6000	80

Notes: 1. Tolerance of Forward Voltage: ±0.05V.

- 2. Tolerance of Chromaticity Coordinates: ±0.02.
- 3. Tolerance of Luminous Intensity: ±15%.

#### **Directivity Radiation**

 $T_A = 25^{\circ}C$  unless otherwise noted



Relative Luminous Intensity vs. Radiation Angle

Notes: 1. 10% Duty Cycle, Pulse Width ≤ 0.1 msec.

<sup>2.</sup> Solder time less than 5 seconds at temperature extreme.

# 4-Pin Super Flux White LED Lamp R20WHT-5-0080



#### Typical Electrical / Optical Characteristics Curves

 $T_A = 25$ °C unless otherwise noted




Fig.1 Forward Current vs. Forward Voltage




Fig.2 Relative Luminous Intensity vs. Forward Current





Fig. 3 Reverse Current vs. Reverse Voltage



Half Width = △ 35nm

Fig.4 Relative Luminous Intensity vs. Wavelength




Fig.5 Relative Luminous Intensity vs. Ambient Temperature





Fig.6 Maximun Forward Current vs. Ambient Temperature

# 4-Pin Super Flux White LED Lamp R20WHT-5-0080




#### Recommended Soldering Conditions



Recommended Lead Free Wave Soldering Profile				
Preheat Temperature: 100°C Max.	Peak Temperature: 260°C Max.			
Preheat Time: 20 ~ 50 Seconds	Solder Time Above 217°C: 5 Seconds Max.			
Note: Turn off top heater at preheat to prevent the lamp body directly exposed to the heat source.				

#### **Packaging and Labeling Plan**

Bivar Orca R series Super Flux LEDs are packaged in tubes, each of which contains 60 LEDs; and each tube contains a rubber stopper at each end.



### **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

**BIVAR**:

R20WHT-5-0080