



NOTES:

1. ALLOWABLE FLEXIBLE LIGHT PIPE CUT LENGTH AVAILABLE IN INCREMENTS OF 0.05".
2. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 1.22" [31mm].
3. COMPONENTS SHIPPED NON-ASSEMBLED.
4. SEE SHEET 2 FOR DETAILED ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SPLASH GUARD.



PART NUMBER CONFIGURATOR

SEE SHEET 2 & 3 FOR ORDERING INFORMATION

SZ4-X.XX-XX-F5PX **-X**

LENGTH (L)
(SEE TABLE 1)




LED INFO
(SEE TABLE 4)

LENS APPEARANCE
(SEE TABLE 2)

CABLE COLOR
(SEE TABLE 3)

IP RATING

IP OPTION	CODE
NONE	(BLANK)
IP54	54



CUSTOMER USE DRAWING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	 TITLE: FLP ASSEMBLY WITH SURFACE MOUNT ADAPTER, SMD LED, LC2	
.XX ± .02			
.XXX ± .010		DRAWING NO: SZ4-X.XX-XX-F5PX-X	
DESIGNED: K. BARON	DATE: 08/21/19	REVISION: A	
REVISED: N/A	DATE: N/A	SHEET SIZE	A
CHECKED: A. VALDEZ	DATE: 08/21/19	SCALE: 2:1	CAGE CODE: 32559
		SHEET # 1 OF 3	
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			


TABLE 1 - LENGTH	
LENGTH (L)*	TOLERANCE
1.00" - 16.00"	±0.05"
16.05" - 40.00"	±0.15"
40.05" - 80.00"	±0.30"
80.05" - 3,940.00"	±0.5%

*AVAILABLE IN 0.05" INCREMENTS

TABLE 2 - LENS	
ORDER CODE	LENS APPEARANCE
(BLANK)	CLEAR
D	DIFFUSED
S	SMOKED
BE	TINTED BLUE
GN	TINTED GREEN
RD	TINTED RED
YW	TINTED YELLOW

TABLE 3 - CABLE	
ORDER CODE	CABLE COLOR
(BLANK)	BLACK
2	RED
4	YELLOW
5	GREEN
6	BLUE
9	WHITE

ASSEMBLY SAMPLE PART NUMBER



ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SPLASH GUARD:

- CLEAN PANEL SURFACE AROUND MOUNTING HOLE WITH ALCOHOL
- PEEL LINER OFF TOP OF THE SPLASH GUARD WHILE KEEPING SPLASH GUARD ON PLASTIC ROLL
- APPLY SPLASH GUARD TO PANEL HOLE AS CENTERED AS POSSIBLE AND PEEL PLASTIC LINER SLOWLY AWAY
- INSERT LIGHT PIPE INTO PANEL UNTIL SPLASH GUARD MATERIAL IS COMPRESSED BETWEEN LENS AND PANEL
- HOLD FOR A FEW SECONDS TO ENSURE ENTIRE SPLASH GUARD ADHERES TO PANEL AND LENS FLANGE SURFACE

CUSTOMER USE DRAWING

		BIVAR[®]	
CAGE CODE:	32559	DRAWING NO: SZ4-X.XX-XX-F5PX-X	REVISION: A
SHEET SIZE:	A	SCALE: 2:1	SHEET # 2 OF 3
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			





TABLE 4 - LED INFORMATION

Order Code XX	Emitted Color	Peak Wave L.	Electro-Optical Data @20mA, 25°C				Polarity Diagram
		λ _p [nm]	V _f [V]			I _v [mcd]	
		Chroma	MIN	TYP	MAX	TYP	
		TYP					
R130	Red	640	1.7	2.0	2.5	130	FIGURE A
R480	Red	630	1.7	2.0	2.5	480	FIGURE B
A220	Amber	610	1.7	2.0	2.5	220	
O170	Orange	590	1.7	2.0	2.5	170	
Y50	Yellow	570	1.7	2.0	2.5	50	
G850	Green	520	2.8	3.2	3.7	850	
B150	Blue	465	2.8	3.2	3.7	150	
W305	White	X = 0.308 Y = 0.305	2.8	3.0	3.7	1750	
OY	Orange	590	1.7	2.0	2.5	190	FIGURE C
	Yellow	572	1.7	2.0	2.5	60	
RY	Red	640	1.7	2.0	2.5	110	FIGURE D
	Yellow	572	1.7	2.0	2.5	55	
RG	Red	640	1.7	2.0	2.5	200	FIGURE E
	Green	520	2.8	3.2	3.7	810	
RW	Red	630	1.7	2.0	2.5	130	FIGURE F
	White	X = 0.28 Y = 0.29	2.8	3.2	3.7	520	
RB	Red	650	1.7	2.0	2.5	80	FIGURE G
	Blue	465	2.8	3.2	3.7	150	
RGB	Red	643	1.7	2.0	2.5	95	FIGURE H
	Green	515	2.8	3.3	3.7	730	
	Blue	460	2.8	3.3	3.7	120	

Note: 10% Duty Cycle, Pulse Width ≤ 0.1 msec for Peak If.




FIG. A

FIG. B

FIG. C




FIG. D




FIG. E




FIG. F




FIG. G




FIG. H

CUSTOMER USE DRAWING

BIVAR

CAGE CODE:	32559	DRAWING NO:	SZ4-X.XX-XX-F5PX-X	REVISION:	A
SHEET SIZE:	A	SCALE:	2:1	SHEET #	3 OF 3
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[SZ4-6.00-O170-F5PRD-2](#) [SZ4-6.00-O170-F5PRD-4](#) [SZ4-6.00-O170-F5PRD-5](#) [SZ4-6.00-R130-F5PGN54-5](#) [SZ4-6.00-R130-F5PGN54-6](#) [SZ4-6.00-R130-F5PGN54-9](#) [SZ4-6.00-R130-F5PGN-6](#) [SZ4-6.00-R130-F5PGN-9](#) [SZ4-6.00-R130-F5PRD](#) [SZ4-6.00-R130-F5PRD-2](#) [SZ4-6.00-R130-F5PRD-4](#) [SZ4-6.00-R130-F5PRD-5](#) [SZ4-6.00-R130-F5PRD54](#) [SZ4-6.00-R130-F5PRD54-2](#) [SZ4-6.00-R130-F5PRD54-4](#) [SZ4-6.00-R130-F5PRD54-5](#) [SZ4-6.00-R130-F5PRD54-6](#) [SZ4-6.00-R130-F5PRD54-9](#) [SZ4-6.00-R130-F5PRD-6](#) [SZ4-6.00-R130-F5PRD-9](#) [SZ4-6.00-O170-F5PBE54-5](#) [SZ4-6.00-O170-F5PBE54-6](#) [SZ4-6.00-O170-F5PBE54-9](#) [SZ4-6.00-O170-F5PBE-6](#) [SZ4-6.00-O170-F5PBE-9](#) [SZ4-6.00-O170-F5PD](#) [SZ4-6.00-O170-F5PD-2](#) [SZ4-6.00-R130-F5PS54-9](#) [SZ4-6.00-R130-F5PS-6](#) [SZ4-6.00-R130-F5PS-9](#) [SZ4-6.00-R130-F5PYW](#) [SZ4-6.00-R130-F5PYW-2](#) [SZ4-6.00-R130-F5PYW-4](#) [SZ4-6.00-R130-F5PYW-5](#) [SZ4-6.00-R130-F5PYW54](#) [SZ4-6.00-R130-F5PYW54-2](#) [SZ4-6.00-R130-F5PYW54-4](#) [SZ4-6.00-R130-F5PYW54-5](#) [SZ4-6.00-R130-F5PYW54-6](#) [SZ4-6.00-R130-F5PYW54-9](#) [SZ4-6.00-R130-F5PYW-6](#) [SZ4-6.00-R130-F5PYW-9](#) [SZ4-6.00-R480-F5P](#) [SZ4-6.00-G850-F5PRD](#) [SZ4-6.00-G850-F5PRD-2](#) [SZ4-6.00-G850-F5PRD-4](#) [SZ4-6.00-G850-F5PRD-5](#) [SZ4-6.00-G850-F5PRD54](#) [SZ4-6.00-G850-F5PRD54-2](#) [SZ4-6.00-G850-F5PRD54-4](#) [SZ4-6.00-G850-F5PRD54-5](#) [SZ4-6.00-G850-F5PRD54-6](#) [SZ4-6.00-G850-F5PRD54-9](#) [SZ4-6.00-R480-F5P-9](#) [SZ4-6.00-R480-F5PBE](#) [SZ4-6.00-R480-F5PBE-2](#) [SZ4-6.00-R480-F5PBE-4](#) [SZ4-6.00-R480-F5PBE-5](#) [SZ4-6.00-R480-F5PBE54](#) [SZ4-6.00-R480-F5PBE54-2](#) [SZ4-6.00-R480-F5PBE54-4](#) [SZ4-6.00-R480-F5PBE54-5](#) [SZ4-6.00-R480-F5PBE54-6](#) [SZ4-6.00-R480-F5PBE54-9](#) [SZ4-6.00-R480-F5PBE-6](#) [SZ4-6.00-R480-F5PBE-9](#) [SZ4-6.00-O170-F5PS-9](#) [SZ4-6.00-O170-F5PYW](#) [SZ4-6.00-O170-F5PYW-2](#) [SZ4-6.00-O170-F5PYW-4](#) [SZ4-6.00-O170-F5PYW-5](#) [SZ4-6.00-O170-F5PYW54](#) [SZ4-6.00-O170-F5PYW54-2](#) [SZ4-6.00-R480-F5PGN-2](#) [SZ4-6.00-R480-F5PGN-4](#) [SZ4-6.00-R480-F5PGN-5](#) [SZ4-6.00-R480-F5PGN54](#) [SZ4-6.00-R480-F5PGN54-2](#) [SZ4-6.00-R480-F5PGN54-4](#) [SZ4-6.00-R480-F5PGN54-5](#) [SZ4-6.00-R480-F5PGN54-6](#) [SZ4-6.00-R480-F5PGN54-9](#) [SZ4-6.00-R480-F5PGN-6](#) [SZ4-6.00-R480-F5PGN-9](#) [SZ4-6.00-R480-F5PRD](#) [SZ4-6.00-R480-F5PRD-2](#) [SZ4-6.00-R480-F5PRD-4](#) [SZ4-6.00-R480-F5PRD-5](#) [SZ4-6.00-R480-F5PRD54](#) [SZ4-6.00-R130-F5PD54-4](#) [SZ4-6.00-R130-F5PD54-5](#) [SZ4-6.00-R130-F5PD54-6](#) [SZ4-6.00-R130-F5PD54-9](#) [SZ4-6.00-R130-F5PD-6](#) [SZ4-6.00-R130-F5PD-9](#) [SZ4-6.00-R130-F5PGN](#) [SZ4-6.00-R130-F5PGN-2](#) [SZ4-6.00-R130-F5PGN-4](#) [SZ4-6.00-R130-F5PGN-5](#) [SZ4-6.00-R130-F5PGN54](#)