


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/23/18	C.E.





#### NOTES:

#### MATERIALS:

1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
2. WASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
3. GASKET = DOW CORNING SILASTIC 250, SILICONE RUBBER 45-55 DUROMETER.
4. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

#### FINISHES:

1. CONTACT = GOLD PLATE PER ASTM B488-01, TYPE II, 50μin MIN, GRADE C, OVER 100 TO 200μin STRESS FREE SULFAMATE NICKEL PER QQ-N-290.
2. ALL OTHER METAL PARTS = NICKEL PLATE PER QQ-N-290, 50μin MIN, GRADE G, EXCEPT 100 TO 200μin THICK OVER 50 TO 100μin THICK COPPER PER MIL-C-14550

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE	 <b>Property of Radiall</b> This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.	
		C.E.	04/23/18		
DECIMAL		CHKD:	DATE	<b>TYPE "N" STRAIGHT PLUG CLAMP TYPE FOR RG-316 &amp; SIMILAR CABLES</b>	
		D.N.	04/23/18		
		APVD:	DATE	<b>SIZE A FSCM NO. 19505 DWG NO. 4000-7051-003 REV A</b>	
		J.M.	04/23/18		
REFERENCE:		MATERIALS & FINISHES:		SCALE 3:1	
ORIGINATED: C.E. DATE: 04/23/18		SEE NOTES		THIRD ANGLE PROJECTION	
				SHEET 1 OF 1	

4000-7051-003

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[4000-7051-003](#)