


ULTRA-LOW PROFILE HEADER & SOCKET

(0.50 mm) .0197" PITCH • SLH/TLH SERIES

28
G b p s



SLH
Mates:
TLH

TLH
Mates:
SLH




SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer
Contact Material:
Copper Alloy
Plating:
Au over 50 μ " (1.27 μ m) Ni
Current Rating:
2.1 A per pin
(2 pins powered)
Operating Temp Range:
-55 °C to +125 °C

PROCESSING




Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.10 mm) .004" max
Board Stacking:
For applications requiring two
or more connectors per board,
contact ipg@samtec.com

SLH	-	NO. OF POSITIONS	-	LEAD STYLE	-	PLATING OPTION	-	D	-	OPTION	-	OPTION
		-010, -020, -030 (Per Row)		-1.50 =1.50 mm		-G = 10 μ " (0.25 μ m) Gold in contact, Gold flash on tail				-A = Alignment Pin		-K = (3.00 mm) .118" DIA Polyimide Film Pick & Place Pad



-A OPTION

TLH	-	NO. OF POSITIONS	-	LEAD STYLE	-	PLATING OPTION	-	D	-	OPTION	-	OPTION
		-010, -020, -030 (Per Row)		-0.50 =0.50 mm		-G = 10 μ " (0.25 μ m) Gold in contact, Gold flash on tail				-A = Alignment Pin		-K = (3.00 mm) .118" DIA Polyimide Film Pick & Place Pad



-A OPTION

Note:
Some lengths, styles and
options are non-standard,
non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TLH-010-0.50-G-D](#) [TLH-010-0.50-G-D-A](#) [TLH-010-0.50-G-D-A-K](#) [TLH-010-0.50-G-D-K](#) [TLH-020-0.50-G-D](#) [TLH-020-0.50-G-D-A](#) [TLH-020-0.50-G-D-A-K](#) [TLH-020-0.50-G-D-K](#) [TLH-030-0.50-G-D](#) [TLH-030-0.50-G-D-A](#) [TLH-030-0.50-G-D-A-K](#) [TLH-030-0.50-G-D-K](#)