



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/19/17	D.N.





#### NOTES:

#### MATERIALS:

1. BODY = STAINLESS STEEL PER ASTM A582, ALLOY 303, CONDITION "A".
2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.

#### FINISHES:

1. BODY = GOLD PLATE PER ASTM B488-11, TYPE II, 30μin MIN, GRADE C, OVER 50 TO 100μin STRESS FREE NICKEL PER AMS-QQ-N-290.
2. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50μin MIN, GRADE C, OVER 100 TO 200μin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE	 <b>Property of Radiall</b> This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.	
		D.N.	05/19/17		
DECIMAL	ANGLE	CHKD:	DATE	SMA STRAIGHT JACK TO STRIPLINE NON-CAPTIVE CONTACT	
		P.H.	05/19/17		
		APVD:	DATE	SIZE <b>A</b>	FSCM NO. 19505
		J.M.	05/19/17		
REFERENCE:		MATERIALS & FINISHES:		DWG NO. <b>9610-1213-003</b>	REV <b>A</b>
ORIGINATED: D.N. DATE: 05/19/17		SEE NOTES			
		SCALE 5:1		THIRD ANGLE PROJECTION	SHEET 1 OF 1

9610-1213-003

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[9610-1213-003](#)