





PAGE 1/2	ISSUE 05-02-19A	SERIES OCTIS	PART NUMBER OCTI957500
----------	-----------------	--------------	------------------------



Packing configuration



All dimensions are in mm. Tolerances according ISO 2768 m-H

DESCRIPTION

REP	COMPONENT	MATERIALS	PLATING
1	Grounding ring	STAINLESS STEEL	-
2	Protective cap	PBT GF	-
3	Interface sealing gasket	SILICONE	-
4	Lever	IXEF	-

PAGE 2/2

ISSUE **05-02-19A**

SERIES **OCTIS**

PART NUMBER **OCTI957500**


### GENERAL CHARACTERISTICS

<b>Mechanical</b> Mating endurance (cycles) Vibration Weight (g)	IEC 61300-2-2 IEC 61300-2-1 -	100 - 6.5100
<b>Environmental</b> Protection class Operating temperature (°C) Storage temperature (°C) Humidity (damp heat) (%RH) Salt Mist  RoHS Flammability UVB Resist (h)	IEC 60529 IEC 61300-2-22 IEC 61300-2-22 IEC 61300-2-19 IEC 61300-2-26 (ISO21207 method B) - UL 94 ASTM G154 cycle 2	IP67 * -40 / +85 -65 / +85 5 / 95 720h *  Compliant V0 Compliant
<b>Others:</b> Installation  Packaging	-  -	For use with standard OCTIS™ panel interface or receptacle **  Unitary in plastic bag

\* Mated condition

\*\* If the interface is to be die casted into the equipment panel, please contact Radiall for license conditions and interface definition

### INSTALLATION



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[OCTI957500](#)