





PAGE 1/2	ISSUE 14-02-19A	SERIES OCTIS	PART NUMBER OCTI957550
----------	-----------------	--------------	------------------------



Packing configuration



All dimensions are in mm. Tolerances according ISO 2768 m-H

DESCRIPTION

REP	COMPONENT	MATERIALS	PLATING
1	Protective cap	PBT GF	-
2	Interface sealing gasket	SILICONE	-
3	Lever	IXEF	-

PAGE 2/2

ISSUE 14-02-19A

SERIES OCTIS

PART NUMBER OCTI957550


GENERAL CHARACTERISTICS

Mechanical Mating endurance (cycles) Vibration Weight (g)	IEC 61300-2-2 IEC 61300-2-1 -	100 - 5.1300
Environmental Protection class Operating temperature (°C) Storage temperature (°C) Humidity (damp heat) (%RH) Salt Mist RoHS Flammability	IEC 60529 IEC 61300-2-22 IEC 61300-2-22 IEC 61300-2-19 BS 720H according to Telcordia GR-950 - UL 94	IP67 * -40 / +85 -65 / +85 5 / 95 720h * Compliant V0
Others: Installation Packaging	- -	For use with standard OCTIS™ panel interface or receptacle ** Unitary in plastic bag

* Mated condition

** If the interface is to be die casted into the equipment panel, please contact Radiall for license conditions and interface definition

INSTALLATION



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[OCTI957550](#)