

(2.54 mm) .100"

TS, TD, HTS SERIES

PRECISION MACHINED TERMINAL STRIPS

SPECIFICATIONS

For complete specifications see
www.samtec.com?TS,
www.samtec.com?TD or
www.samtec.com?HTS

Insulator Material:

Black G.F. Polyester (TS, TD)
Black Liquid Crystal Polymer
(HTS)

Terminal Material:

Brass, except Style G is
Phosphor Bronze

Plating:

Au over 50 μ " (1.27 μ m) Ni or
Sn over 100 μ " (2.54 μ m) Cu
or 50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

RoHS Compliant:

Yes

Lead-Free Solderable:

HTS: Yes

TS, TD: No, Lead Wave Only

RECOGNITIONS

For complete scope
of recognitions see
www.samtec.com/quality




Mates with:
SS, SD, HSS, SL,
SDL, ESS, ESD

TYPE
STRIP


1

NO. PINS
PER ROWPLATING
OPTIONLEAD
STYLE


TS
= Single
Row Terminal
Strip



HTS
= Single Row
High Temp
Terminal Strip



TD
= Double Row
Terminal Strip



-G
= 20 μ " (0.51 μ m) Gold
Except -J & -L are
10 μ " (0.25 μ m) Gold


-T
= Tin

01 thru 32
= TS Series

01 thru 36
= HTS & TD Series


Note:
Some lengths, styles and options
are non-standard, non-returnable.

-AA



Component No. = T-1R5-


-A, -A-1, -A-2



-A Component No. = T-1R0-
-A-X Component No. = T-1R7

LEAD STYLE	X (DIA)	Y (±.015)
-A	(0.46) .018	(3.96) .156
-A-1	(0.64) .025	(5.33) .210
-A-2	(0.89) .035	


-C, -C-1, -C-2



-C Component No. = T-1R2-
-C-X Component No. = T-1R9-


LEAD STYLE	X (DIA)	Y (±.015)
-C	(0.46) .018	(3.96) .156
-C-1	(0.64) .025	(5.33) .210
-C-2	(0.89) .035	

-G-1




Component No. = T-1R5-

-J



Component No. = S-1P1-

-L-1, -L-2, -L-3



Component No. = S-1W1

LEAD STYLE	Y (DIA)	Y (±.015)
-L-1	(12.95) .510	(17.86) .703
-L-2	(9.14) .360	(14.05) .553
-L-3	(6.60) .260	(11.51) .453

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TS-105-T-A](#)