


## BNC FEMALE - N MALE ADAPTER

**R192.421.000**

Série : ADAPT 75



All dimensions are in mm.



| COMPONENTS     | MATERIALS | PLATINGS (µm)          |
|----------------|-----------|------------------------|
| BODY           | BRASS     | NICKEL 2               |
| CENTER CONTACT | BRASS     | GOLD 0.5 OVER NICKEL 2 |
| OUTER CONTACT  | -         | -                      |
| INSULATOR      | PTFE      | -                      |
| GASKET         | -         | -                      |
| OTHERS PARTS   | -         | -                      |
| -              | -         | -                      |
| -              | -         | -                      |

Issue : 0417 F

In the effort to improve our products, we reserve the rights to make changes judged to be necessary.


**RADIALL**®

**BNC FEMALE - N MALE ADAPTER****R192.421.000**

Série : ADAPT 75

**PACKAGING**

| Standard | Unit | Other             |
|----------|------|-------------------|
| <b>1</b> | -    | <b>Contact us</b> |

**SPECIFICATION****ELECTRICAL CHARACTERISTICS**

|                                 |                  |                                |
|---------------------------------|------------------|--------------------------------|
| Impedance                       | <b>75</b>        | $\Omega$                       |
| Frequency                       | <b>0-1</b>       | GHz                            |
| VSWR                            | - + <b>0.000</b> | x F(GHz) Maxi                  |
| Insertion loss                  | -                | $\sqrt{F}(\text{GHz})$ dB Maxi |
| RF leakage                      | - (              | - F(GHz)) dB Maxi              |
| Voltage rating                  | -                | Veff Maxi                      |
| Dielectric withstanding voltage | <b>1500</b>      | Veff mini                      |
| Insulation resistance           | <b>5000</b>      | M $\Omega$ mini                |

**ENVIRONMENTAL**

|               |                 |                        |
|---------------|-----------------|------------------------|
| Operating     | <b>-55/+155</b> | $^{\circ}\text{C}$     |
| Hermetic seal | -               | Atm.cm <sup>3</sup> /s |
| Panel leakage | -               |                        |

**MECHANICAL CHARACTERISTICS**

|                            |           |           |
|----------------------------|-----------|-----------|
| Center contact retention   |           |           |
| Axial force – Mating end   | <b>27</b> | N mini    |
| Axial force – Opposite end | <b>27</b> | N mini    |
| Torque                     | -         | N.cm mini |

## Recommended torque

|           |            |          |      |
|-----------|------------|----------|------|
| Mating    | <b>N</b>   | <b>0</b> | N.cm |
|           | <b>BNC</b> | <b>0</b> | N.cm |
|           | -          | <b>0</b> | N.cm |
| Panel nut |            | -        | N.cm |

|             |               |             |
|-------------|---------------|-------------|
| Mating life | <b>500</b>    | Cycles mini |
| Weight      | <b>38.000</b> | g           |

**OTHERS CHARACTERISTICS**

Issue : 0417 F

In the effort to improve our products, we reserve the rights to make changes judged to be necessary.

**RADIALL**

®

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

R192421000