





GLASS BEAD
PACKAGING 100

R280.751.080

Series : ACC-COAX



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
BODY	FERRO-NICKEL	GOLD 1.3 OVER NICKEL 2
CENTER CONTACT	FERRO-NICKEL	GOLD 1.3 OVER NICKEL 2
OUTER CONTACT	-	-
INSULATOR	-	-
GASKET	-	-
OTHERS PARTS	-	-

Operating temperature : $-65/+200\text{ }^{\circ}\text{C}$

Weight : 0,1100 g

Others characteristics :

Issue : 0839 A



In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 


GLASS BEAD
PACKAGING 100

R280.751.080

Series : ACC-COAX

MOUNTING INSTRUCTIONS**FLANGE****RECEPTACLE SCREW****ASSEMBLY**

Introduce the glass bead into its housing.
Weld the ring by putting a welding ring in the groove.
Weld the glass bead pin on the track.
(Beware there is not too much welding).
(For maximum RF characteristics the link track/pin must be as thin as possible. We advise therefore to follow the A dimension rigorously, by welding accurately the glass bead pin on the track).



Issue : 0839 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R280751080](#)