



GLASS BEAD

R280.755.000**SERIES ACC-COAX**

PERCAGE PANNEAU

MOUNTING HOLE

According to customer application
(Selon application client)

NOMINAL IMPEDANCE	50	Ω
FREQUENCY RANGE	0-26.5	GHz
TEMPERATURE RATING	-65/+200	$^{\circ}\text{C}$
V.S.W.R	+	x F(GHz)Maxi
RF INSERTION LOSS	\sqrt{F} (GHz)	dB Maxi
VOLTAGE RATING	335	Veff Maxi
DIELECTRIC WITHSTANDING VOLTAGE	1000	Veff Mini
INSULATION RESISTANCE	NA	M Ω Mini
HERMETIC SEAL	1*10⁻⁸	Atm.cm ³ /s
LEAKAGE (pressurized only)		
MECHANICAL DURABILITY		Cycles
WEIGHT		gr
SPECIFICATION		

CABLES :

OTHERS CHARACTERISTICS

CABLE RETENTION	NA	N Mini
CENTER CONTACT RETENTION		
Axial force - mating end	30	N Mini
Axial force - opposite end	30	N Mini
Torque		cm.N Mini
RECOMMENDED TORQUES		
Mating		cm.N
Panel nut	NA	cm.N
Clamp nut	NA	cm.N

CONNECTOR PARTS MATERIALS

BODY	DILVER P
OUTER CONTACT	
CENTER CONTACT	
INSULATOR	GLASS
GASKET	
OTHERS PIECES	

FINISH (all values are given in micrometers)

GOLD 1.3 OVER NICKEL 2
GOLD 1.3 OVER NICKEL 2
-
-

ISSUE

9910C00

CREATION DATE

29/08/1989

FILE PART-NUMBER

**RADIALL®**The information given here is subject to change without notice.
Design changes may be in order to improve the product.

Connect to the future

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R280755000](#)