




**SMA ATTENUATOR****7 DB 4GHZ 2W****R413.807.115**

Series : ATTENUATOR



SCALE 1:1

All dimensions are in mm.



| COMPONENTS                   | MATERIALS               | PLATING(μm)                   |
|------------------------------|-------------------------|-------------------------------|
| <b>BODY</b>                  | <b>STAINLESS STEEL</b>  |                               |
| <b>MALE CENTER CONTACT</b>   | <b>BERYLLIUM COPPER</b> | <b>GOLD 2.5 OVER NICKEL 1</b> |
| <b>FEMALE CENTER CONTACT</b> | <b>BERYLLIUM COPPER</b> | <b>GOLD 2.5 OVER NICKEL 1</b> |
| <b>OUTER CONTACT</b>         |                         |                               |
| <b>INSULATOR</b>             | <b>PTFE</b>             |                               |
| <b>GASKET</b>                | <b>SILICONE RUBBER</b>  |                               |
| <b>SUBSTRATE</b>             | <b>ALUMINA</b>          |                               |
| <b>RESISTOR</b>              | <b>THIN FILM</b>        |                               |
| <b>OTHERS PARTS</b>          |                         |                               |

**Issue : 0838 A**

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

**RADIAL**

**SMA ATTENUATOR****7 DB 4GHZ 2W****R413.807.115**

Series : ATTENUATOR

**ELECTRICAL CHARACTERISTICS**

|                      |        |
|----------------------|--------|
| Frequency (GHz)      | DC - 4 |
| V.S.W.R ( $\leq$ )   | 1.15   |
| Deviation( $\pm$ dB) | 0.4    |


|                                    |        |                       |
|------------------------------------|--------|-----------------------|
| Operating Frequency Range          | DC - 4 | GHz                   |
| Impedance                          | 50     | $\Omega$              |
| Nominal Attenuation                | 7      | dB                    |
| Peak power at 25°C (1 $\mu$ s, 1%) | 100    | W                     |
| Average power at 25°C              | 2      | W (Free Air Cooled)   |
|                                    |        | W (Conduction Cooled) |

**MECHANICAL CHARACTERISTICS**

|            |          |             |             |
|------------|----------|-------------|-------------|
| Connectors | SMA      | Male Female | MIL-C 39012 |
| Weight     | 5,1470 g |             |             |

**ENVIRONMENTAL CHARACTERISTICS**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55 /+125 °C |
| Storage temperature range   | -55 /+125 °C |

**SPECIFICATION****OTHER CHARACTERISTICS****Issue : 0838 A**

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

**RADIALL** 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R413807115](#)