

RF CHARACTERISTICS

Number of ways	: 3
Frequency range	: 0 - 40 GHz
Impedance	: 50 Ohms

Frequency (GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40
VSWR max	1.30	1.40	1.50	1.70	2.20
Insertion loss max	0.20 dB	0.40 dB	0.50 dB	0.70 dB	1.10 dB
Isolation min	70 dB	60 dB	60 dB	55 dB	50 dB
Average power (*)	40 W	30 W	25 W	15 W	5 W

ELECTRICAL CHARACTERISTICS

Actuator	:	NORMALLY OPEN
Nominal current **	:	102 mA
Actuator voltage (Vcc)	:	28V (24 to 30V)
Terminals	:	25 pins D-SUB male connector
TTL inputs (E)	- High level	2.2 to 5.5 V / 800µA at 5.5 V
	- Low level	0 to 0.8 V / 20µA at 0.8 V

MECHANICAL CHARACTERISTICS

Connectors	: SMA 2.9 female per MIL-C 39012
Life	: 2 million cycles per position
Switching Time***	: < 15 ms
Construction	: Splashproof
Weight	: < 220 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage ; 25° C)




PAGE 2/2

ISSUE 06-02-18

SERIE : SPnT


PART NUMBER : R573803325

DRAWING




TTL input	RF Continuity
E1 = 1	IN ↔ 1
E2 = 1	IN ↔ 2
E3 = 1	IN ↔ 3

LABEL



SCHEMATIC DIAGRAM



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R573803325](#)