


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/03/11	A.D.M.




NOTES:

MATERIALS:

1. BODY & CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. SLEEVE = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

1. BODY & SLEEVE = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .00010 TO .00020 COPPER STRIKE PER MIL-C-14550.
2. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: A.D.M.	DATE 01/03/11	 Property of Radiall This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.				
		CHKD: D.N.	DATE 01/03/11					
DECIMAL	ANGLE	APVD: J.M.	DATE 01/03/11	SSLB STRAIGHT FEMALE PLUG P.C.B. MOUNT RECEPTACLE				
REFERENCE:		MATERIALS & FINISHES:						
ORIGINATED: A.D.M. DATE: 01/03/11		SEE NOTES		<table border="1"> <tr> <td>SIZE A</td> <td>FSCM NO. 19505</td> <td>DWG NO. 7325-1512-050</td> <td>REV A</td> </tr> </table>	SIZE A	FSCM NO. 19505	DWG NO. 7325-1512-050	REV A
SIZE A	FSCM NO. 19505	DWG NO. 7325-1512-050	REV A					
		SCALE 8:1		THIRD ANGLE PROJECTION  SHEET 1 OF 1				

7325-1512-050

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[7325-1512-050](#)