


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/16/18	D.N.
B	UPDATED FINISHES	10/05/18	D.N.
C	UPDATED FINISHES	10/16/18	D.N.






NOTES: LEAK RATE LESS THAN 1×10^{-8} cc/sec AT A DIFFERENTIAL PRESSURE OF 15 PSI.

MATERIALS:

1. BODY = STAINLESS STEEL PER ASTM A582, ALLOY 303, CONDITION "A".
2. INSULATORS= VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. CONTACT = KOVAR
4. GLASS SEAL = CORNING #9013

FINISHES:

1. BODY & CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 100µin MIN, GRADE C, OVER 50 TO 100µin STRESS FREE NICKEL PER AMS-QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE	<div>Property of Radiall This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.</div> <div></div>			
		D.N.	07/16/18				
DECIMAL	ANGLE	CHKD:	DATE	SMC STRAIGHT MALE JACK BULKHEAD FRONT MOUNT HERMETICALLY SEALED RECEPTACLE			
		J.S.	07/16/18				
		APVD:	DATE				
		J.M.	07/16/18				
REFERENCE: H.P. 1250-1618-1 (A) ORIGINATED: D.N. DATE: 07/16/18		MATERIALS & FINISHES: SEE NOTES		SIZE	FSCM NO.	DWG NO.	REV
				A	19505	1019-3313-004	C
				SCALE 8:1		THIRD ANGLE PROJECTION 	SHEET 1 OF 1

1019-3313-004

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[1019-3313-004](#)