


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/06/09	A.D.M.



#### NOTES:


#### MATERIALS:

1. BODY & CONTACT = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.
2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".

#### FINISHES:

1. BODY = SILVER PLATE PER QQ-S-365, TYPE III, GRADE A, .0002 TO .0003 THICK OVER COPPER FLASH PER MIL-C-14550, .000010 TO .000030 THICK.
2. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

Property of Radiall Incorporated  
This document cannot be reproduced or  
communicated to a third party without prior  
written permission of RADIALl Incorporated.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: A.D.M.	DATE 04/06/09	 <b>APPLIED ENGINEERING PRODUCTS</b> 104 John W. Murphy Dr. New Haven, CT 06513
		CHKD: D.N.	DATE 04/06/09	
DECIMAL	ANGLE	APVD: J.M.	DATE 04/06/09	<b>SMB STRAIGHT MALE JACK P.C.B. MOUNT RECEPTACLE</b>
REFERENCE:		MATERIALS & FINISHES:  SEE NOTES		
ORIGINATOR: A.D.M. DATE: 04/06/09		SIZE A	FSCM NO. 19505	DWG. NO. <b>2009-6511-000</b> THIRD ANGLE PROJECTION
		SCALE 6:1	REV A SHEET 1 OF 1	

2009-6511-000

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[2009-6511-000](#)