

(4,00 mm) .1575"

IJ5C SERIES

Isolated Edge Rate Contact

IJ5C-08-0600-S-D-NUS-1

IJ5C-04-0400-S-D-NUS-1

50Ω HIGH ISOLATION RF CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?IJ5C

Insulator Material:

Black LCP

Contact Material:

Copper Alloy

Pin Material:

Copper Alloy

Dielectric Material:

Black LCP

Plating:

Au over 50μ" (1,27 μm) Ni

Operating Temp Range:

-40°C to +90°C

RoHS Compliant:

Yes

Cable (-1):**Conductor Size:**

26 AWG,

(0,48 mm) .019" dia.

Conductor Material:

Silver Plated Copper

Insulator Diameter:

(1,27 mm) .050"

Insulator Material:

Foamed FEP

Shield Material:

Silver Plated Copper

Jacket Material:

FEP

Jacket Diameter:

(1,80 mm) .071"

Impedance:

50Ω

Current Rating:

2.5A

RoHS Compliant:

Yes

Cable (-2):**Conductor Size:**

26 AWG,

(0,51 mm) .020" dia.

Conductor Material:

Silver and Copper

Plated Steel Wire

Insulator Diameter:

(1,52 mm) .060"

Insulator Material:

PTFE

Shield Material:

Silver Plated Copper Wire

Jacket Material:

FEP

Jacket Diameter:

(2,54 mm) .100"

Impedance:

50Ω

Current Rating:

5A DC

RoHS Compliant:

Yes

Note:

This Series is non-standard, non-returnable.

Mates with:
IP5



- Edge Rate™ Contacts
- Positive Latching

1 Meter Cable Assembly	Frequency
Insertion Loss = 3 dB	9.5 GHz / 19.0 Gbps
Return Loss = 15 dB	2.2 GHz / 4.4 Gbps
VSWR = 1.4	2.1 GHz / 4.2 Gbps
Isolation = 60 dB	3.1 GHz / 6.2 Gbps

Performance and complete test data available at www.samtec.com?IJ5C or contact sig@samtec.com

Single or
Double Ended


High
performance
26 AWG
coax cable

Positive latching
system

1, 2, 4, 6 or 8
Positions

IJ5C	NO. OF POSITIONS	ASSEMBLED LENGTH	PLATING OPTION	END OPTION	END 2 OPTION	CABLE TYPE
	-01, -02, -04, -06, -08	- "XXXX" = Assembled Length in millimeters -0100 to -1000 (100 mm) 3.94" minimum	-S = 30μ" (0,76 μm) Gold on contact	-S = Single Ended -D = Double Ended	-NUS = Notch up, straight P1 to P1 -NDS = Notch down, straight P1 to PN	-1 = CTB-2650F-1 cable -2 = RG 316 cable

NO. OF POSITIONS	A
-01	(20,87) .822
-02	(24,87) .979
-04	(32,87) 1.294
-06	(40,87) 1.609
-08	(48,87) 1.924



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
 SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
 SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[IJ5C-01-0500-S-D-NUS-1](#) [IJ5C-04-0200-S-D-NDS-1](#) [IJ5C-08-0200-S-D-NUS-1](#) [IJ5C-08-0200-S-D-NDS-1](#) [IJ5C-08-0600-S-D-NUS-1](#) [IJ5C-08-0100-S-D-NUS-2](#) [IJ5C-04-0500-S-D-NUS-1](#) [IJ5C-02-0500-S-D-NUS-1](#) [IJ5C-08-0600-S-D-NUS-2](#) [IJ5C-01-0200-S-D-NUS-1](#) [IJ5C-02-0600-S-D-NDS-1](#) [IJ5C-04-0700-S-D-NUS-1](#) [IJ5C-04-0300-S-D-NDS-1](#) [IJ5C-02-0100-S-D-NDS-2](#) [IJ5C-02-0200-S-D-NUS-1](#) [IJ5C-02-0300-S-D-NDS-1](#) [IJ5C-04-0200-S-D-NUS-1](#) [IJ5C-02-0600-S-D-NUS-1](#) [IJ5C-06-0300-S-D-NDS-2](#) [IJ5C-01-0100-S-D-NUS-2](#) [IJ5C-04-0300-S-D-NUS-1](#) [IJ5C-01-0300-S-D-NUS-1](#) [IJ5C-06-0200-S-D-NUS-1](#) [IJ5C-06-0600-S-D-NDS-1](#) [IJ5C-01-0300-S-D-NUS-2](#) [IJ5C-08-0500-S-D-NUS-1](#) [IJ5C-04-0100-S-D-NDS-2](#) [IJ5C-06-0500-S-D-NUS-1](#) [IJ5C-06-0100-S-D-NUS-2](#)