


THROUGH-HOLE MICRO HEADER

(1.27 mm) .050" PITCH • TMS/HTMS SERIES



TMS/HTMS

Mates:
SMS, SLM, RSM

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Plating:
Au or Sn over
50 μ " (1.27 μ m) Ni
Current Rating (TMS/SMS):
5 A per pin
(2 pins powered)
Operating Temp Range:
-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

PROCESSING

Lead-Free Solderable:
Yes

SERIES	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OPTION
--------	---	------------------	------------	----------------	------------	--------

TMS
= Standard

HTMS
= High Temp

01 thru 50

Specify
**LEAD
STYLE**
from
chart

-L
= 10 μ "
(0.25 μ m)
Gold on post,
Matte Tin
on tail


-G
= 10 μ "
(0.25 μ m)
Gold on post,
Gold flash
on tail

-S
= Single
Row

-D
= Double
Row

-RA
= Right-
angle

-"XXX"
= Polarized
Position
(Specify position
of omitted pin)




T/H LEAD STYLE	A	B	C
-01	(11.43) .450	(5.84) .230	(3.05) .120
-02	(8.13) .320	(2.54) .100	
-21	(12.83) .505	(5.84) .230	(4.45) .175
-51	(10.41) .410	(4.83) .190	
-52	(10.80) .425	(5.21) .205	
-53	(12.83) .505	(7.24) .285	
-54	(14.10) .555	(8.51) .335	
-55	(15.49) .610	(9.91) .390	
-56	(15.88) .625	(10.29) .405	(3.05) .120
-57	(16.51) .650	(10.92) .430	
-58	(17.91) .705	(12.32) .485	
-59	(19.18) .755	(13.59) .535	
-60	(20.96) .825	(15.37) .605	



SINGLE ROW

DOUBLE ROW



**HTMS
-D
BODY
DESIGN**


ALSO AVAILABLE

Other Plating
(MOQ Required)


Important Note:
Style -02 does not mate
with SMS Series.

Note:
Some lengths, styles and
options are non-standard,
non-returnable.

RA LEAD STYLE	D
-01	(5.84) .230
-02	(2.54) .100
-03	(3.18) .125



-S-RA



-D-RA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[TMS-132-01-T-D-RA](#) [TMS-129-01-G-S](#) [TMS-107-02-F-D-RA](#) [TMS-119-53-G-S](#) [TMS-110-21-L-D](#) [TMS-106-53-L-D](#)
[TMS-131-02-G-S](#) [TMS-103-01-H-S](#) [TMS-150-60-L-D](#) [TMS-110-54-F-D](#) [TMS-102-59-G-D](#) [TMS-118-55-F-S](#) [TMS-](#)
[141-54-L-S](#) [TMS-105-56-L-D](#) [TMS-150-02-F-S-RA](#) [TMS-102-51-F-S](#) [TMS-107-52-L-S](#) [TMS-105-54-S-S-004](#) [TMS-](#)
[113-54-L-S](#) [TMS-118-53-F-S](#) [TMS-110-21-G-D-006](#) [TMS-119-02-L-S](#) [TMS-105-60-S-S-004](#) [TMS-103-01-L-S-002](#)
[TMS-104-57-F-S](#) [TMS-110-01-L-D-RA-006](#) [TMS-103-59-S-S](#) [TMS-140-01-L-D-RA](#) [TMS-116-59-G-D](#) [TMS-110-03-L-](#)
[S-RA](#) [TMS-120-60-L-D](#) [TMS-103-02-F-D](#) [TMS-105-58-L-D](#) [TMS-102-51-T-S](#) [TMS-134-53-S-S](#) [TMS-101-01-L-S-RA](#)
[TMS-120-02-L-D](#)