

REVISION C

REVISION

A	GP	T WILD
6/8/2007	ECN-76836	
RELEASE FOR PRODUCTION		
B	JB	T LOZIER
4/1/2008	ECN-88474	
SHEET 1, BOM: CHG ANTI-STATIC PVC TO POLYIMIDE FILM (KAPTON); TOP VIEW: CHG PIN 1 LOCATION TO UPPER LEFT, DEL PIN 2 LOCATION, ADD PIN 19 LOCATION, ADD ROW MARKERS "A","B","C","D","E" & "F".		
SHEET 2, FOOTPRINT - TOP VIEW: ADD POSITION NOTES "01" & "19".		
C	TV	J Hahn
9/29/2009	ECN-117570	
SHT 1, TOP VIEW: CHG POS 1 CALLOUT FROM TOP LEFT TO BOTTOM LEFT & POS 19 FROM TOP RT TO BOTTOM RT; SHT 2, RECOMMENDED PCB LAYOUT: CHG POS 1 CALLOUT FROM TOP LEFT TO BOTTOM LEFT & POS 19 FROM TOP RT TO BOTTOM RT		

DATE: _____

COMPANY: _____

CUSTOMER SIGNATURE: _____

PRINTED NAME: _____







PHONE NO: _____

FAX NO: _____

ACCEPTANCE OF DRAWING
☐ ACCEPTED WITH DEVIATIONS LISTED

- NOTES:
1. ITEMS -1, -2, & -3 NOT AVAILABLE AS STANDARD.
 2. Ⓢ REPRESENTS A CRITICAL DIMENSION.
 3. BURR ALLOWANCE: .0015[.038] MAX.
 4. MAXIMUM CUT FLASH: .010.
 5. MINIMUM PUSHOUT FORCE: .5 LB.
 6. MAXIMUM ALLOWABLE BOW; TOP/BOTTOM: .004, SIDE/SIDE: .003[.08].
 7. PARTS TO BE PACKAGED IN TUBES.

ANY REV. MADE TO THIS PRINT MUST HAVE AN UPDATED MKTG. PRINT



ITEM NO.	PART NUMBER	QUANTITY	MATERIAL
1	ASP-103598-01-B	1.0000	VECTRA E130i, COLOR: BLACK, UL RATING 94V-0
2	ASP-103599-01-B	1.0000	VECTRA E130i, COLOR: BLACK
3	ASP-104554-02-P-H	114.00	BRASS ALLOY 260, 3/4 HARD
4	SBD-030-6337	114.00	63% TIN /37% LEAD
5	K-850-650	1.0000	POLYIMIDE FILM (KAPTON)
6	PT-1-24-01-08	.05000	ANTI-STATIC PVC
7	TP-13	.01000	THERMOPLASTIC RUBBER

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES

.XX: ±.01 2°

.XXX: ±.005

.XXXX: ±.0020

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING SHEET SCALE: 1:0.3333

PLATING: CONTACT AREA: .000030 GOLD OVER .000050 NICKEL



REMAINDER: .000003 GOLD OVER .000050 NICKEL

520 PARK EAST BLVD, NEW ALBANY, IN 47150
 PHONE: 812-944-6733 FAX: 812-948-5047
 e-Mail: info@SAMTEC.com code: 55322


DESCRIPTION: FLEX, Y, Z, .050 TERMINAL ASSEMBLY

DWG. NO. ASP-103614-08

BY: G. PURVIS 6/8/2007 SHEET 1 OF 2



DETAIL 'B'



PACKAGING VIEW

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

SHEET SCALE: 3:1

DESCRIPTION: FLEX, Y, Z, .050 TERMINAL ASSEMBLY

DWG. NO. ASP-103614-08

BY: G. PURVIS 6/8/2007

SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ASP-103614-08](#)