

REVISION

☐ ACCEPTANCE OF DRAWING ☐ ACCEPTED WITH DEVIATIONS LISTED	
DATE: _____	_____
COMPANY: _____	_____
CUSTOMER SIGNATURE _____	_____
PRINTED NAME _____	_____
PHONE No: _____	_____
FAX No: _____	_____

5	K-850-650	1.0000	POLYIMIDE FILM	
---	-----------	--------	----------------	---

Technical drawing of a mechanical component, showing three views: Top View, Front View, and Side View. Dimensions are provided in millimeters (mm) and inches (in).

Top View:

- Overall length: 23.50 [.925] REF
- Overall width: 5.60 [.220] REF
- Distance from left edge to center of circular feature: 20.32 [.800] REF
- Distance from center of circular feature to right edge: 40
- Radius of circular feature: $\phi 6.00 [.236]$ REF
- Distance from left edge to center of circular feature: 02
- Distance from center of circular feature to right edge: 39
- Distance from left edge to center of circular feature: 0.800 [.0315] (TYP) (TOL NON-ACCUM)
- Distance from center of circular feature to right edge: 15.20 [.598]
- Distance from left edge to right edge: 19.13 [.753]
- Distance from left edge to center of circular feature: 01
- Distance from center of circular feature to right edge: 0.20 [.008]
- Distance from center of circular feature to right edge: 3.36 [.132] REF

Front View:

- Overall length: 8.75 ± 0.50 [.344 $\pm .020$]
- Overall width: 5.46 [.215]
- Distance from left edge to center of circular feature: 3.35 [.132] REF
- Distance from center of circular feature to right edge: 21.80 [.858]
- Distance from left edge to center of circular feature: 0.25 [.010] REF (TYP)
- Distance from center of circular feature to right edge: $\phi 1.32 [.052]$ REF (TYP)
- Distance from left edge to center of circular feature: "B"
- Distance from center of circular feature to right edge: "B"
- Distance from left edge to center of circular feature: 5
- Distance from center of circular feature to right edge: 1

Side View:

- Overall length: 18.80 [.740] REF
- Overall width: 1.10 [.04] REF
- Distance from left edge to center of circular feature: 15.20 [.598]
- Distance from center of circular feature to right edge: 3° MAX SWAY (TYP)
- Distance from left edge to center of circular feature: 0.800 [.0315]
- Distance from center of circular feature to right edge: 0.50 [.059] REF
- Distance from left edge to center of circular feature: "C"

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.









F:\dwa\sw\asp\130000\asp-130367-01.slddrw

SHEET SCALE: 1:0.33

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

BY: D FRALEY	03/22/2007	SHEET 1 OF 2
--------------	------------	--------------

DETAIL 'G'
SCALE 6:1DETAIL 'H'
SCALE 6:1

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

SHEET SCALE: 3:1

DESCRIPTION:
ERF8 ASSEMBLYDWG. NO.
ASP-130367-01

BY: D FRALEY 03/22/2007 SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ASP-130367-01](#)