


# TIGER CLAW™ PASS-THROUGH SOCKET

(2.54 mm) .100" PITCH • BCS SERIES



## BCS

### Mates:

TSW, MTSW, HTSW,  
HMTSW, TSS, ZSS, DW, EW,  
ZW, HW, TSM, MTLW, PHT

## SPECIFICATIONS

### Insulator Material:

Black Liquid Crystal Polymer

### Contact Material:

Phosphor Bronze

### Plating:

Au or Sn over  
50 μ" (1.27 μm) Ni

### Voltage Rating:

495 VAC/700 VDC

(-TE/-DE/-PE mated with TSM)

450 VAC/636 VDC

(-HE mated with TSW)

### Operating Temp Range:

-55 °C to +125 °C

### Insertion Depth:

(4.34 mm) .171" to  
(7.24 mm) .285" from top,  
(5.64 mm) .222" plus board  
thickness minimum from bottom.  
-HE is (4.34 mm) .171"  
to (6.35 mm) .250"

## PROCESSING

### Lead-Free Solderable:

Yes

MATES	CURRENT RATING (PER PIN)
BCS/TSW	4.6 A
BCS/TSM	5.0 A

2 POSITIONS POWERED

## ALSO AVAILABLE

Contact Samtec

Other Platings

BCS	1	NO. PINS PER ROW	PLATING OPTION	ROW OPTION	ENTRY OPTION	OTHER OPTION
-----	---	---------------------	-------------------	---------------	-----------------	-----------------

01 thru 50

**-F**  
= Gold flash  
on contact,  
Matte Tin on tail

**-L**  
= 10 μ" (0.25 μm)  
Gold on contact,  
Matte Tin on tail

**-S**  
= Single

**-D**  
= Double








**-TE**  
= Top Entry

**-DE**  
= Top Entry  
(For Bottom Entry  
specify -DE-BE)  
Cannot be used with  
plated through-holes

**-PE**  
= Pass-through Entry  
(For Bottom Entry  
specify -PE-BE)

**-HE**  
= Horizontal Entry

**-"XXX"**  
= Polarized Position  
(-BE not available)



## Note:

Some lengths, styles and  
options are non-standard,  
non-returnable.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[BCS-116-H-D-DE](#) [BCS-132-H-D-DE](#) [BCS-125-H-D-DE](#)