


# FLEXIBLE ELEVATED & SELF-NESTING SOCKETS

(2.00 mm) .0787" PITCH • ESQT/ESQT (-368)/PTHF SERIES



## ESQT

### Board Mates:

TMMH, TMM, MTMM,  
MMT, TW, LTMM, ZLTMM,  
ESQT, PTT, TSH, TMMS

### Cable Mates:

TCMD

## SPECIFICATIONS

### Insulator Material:

Black Liquid Crystal Polymer

### Contact Material:

Phosphor Bronze

### Plating:

Sn or Au over

50  $\mu$ " (1.27  $\mu$ m) Ni

### Current Rating (ESQT/TMMH):

4.5 A per pin

(2 pins powered)

### Operating Temp Range:

-55 °C to +125 °C

### Insertion Depth:

(2.62 mm) .103" to

(5.03 mm) .198" with

(0.38 mm) .015" wipe

### Max Cycles:



100 with 10  $\mu$ " (0.25  $\mu$ m) Au

### Lead-Free Solderable:


Yes, for -S, -D & -Q

(Wave only for -T, -5 & -6)

| ESQT | 1 | NO. PINS PER ROW | LEAD STYLE                    | PLATING OPTION                                                                                                                 | ROW OPTION         | BODY HEIGHT                            | OTHER OPTION                                               |
|------|---|------------------|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------|--------------------|----------------------------------------|------------------------------------------------------------|
|      |   | 02 thru 50       | Specify LEAD STYLE from chart | -F<br>= Gold flash on contact, Matte Tin on tail                                                                               | -S<br>= Single Row | - "XXX"<br>= Body Height (inches)      | - "XXX"<br>= Polarized Position (Indicate position number) |
|      |   |                  |                               | -L<br>= 10 $\mu$ " (0.25 $\mu$ m)<br>Gold on contact, Matte Tin on tail                                                        | -D<br>= Double Row | (7.87 mm) .310" minimum for -S, -D, -Q |                                                            |
|      |   |                  |                               | -M<br>= 20 $\mu$ " (0.51 $\mu$ m)<br>Gold on contact, Matte Tin on tail                                                        | -T<br>= Triple Row | (9.53 mm) .375" minimum for -T, -S, -6 |                                                            |
|      |   |                  |                               | -GF<br>= 15 $\mu$ " (0.38 $\mu$ m)<br>Gold on contact, Gold flash on tail (Recommended for self-nesting) (-02 lead style only) | -Q<br>= Quad Row   |                                        |                                                            |
|      |   |                  |                               |                                                                                                                                | -5<br>= Five Row   |                                        |                                                            |
|      |   |                  |                               |                                                                                                                                | -6<br>= Six Row    |                                        |                                                            |



| LEAD STYLE | A            | MAX TAIL     | MAX BODY HEIGHT |
|------------|--------------|--------------|-----------------|
| -02        | (21.59) .850 | (13.72) .540 | (20.32) .800    |
| -03        | (11.63) .458 | (3.76) .148  | (10.36) .408    |



## ESQT (-368)/PTHF

### Mates:

ESQT, PTHF

## SPECIFICATIONS

### Insulator Material:

Black Liquid Crystal Polymer (ESQT-368)

Black High Temp Nylon (PTHF)

### Contact Material:

Phosphor Bronze

### Plating:

Au or Sn over

50  $\mu$ " (1.27  $\mu$ m) Ni

### Operating Temp Range:

-55 °C to +125 °C

### Normal Force:

60 grams (0.59 N) average




### Max Cycles:

100 with 10  $\mu$ " (0.25  $\mu$ m) Au

### Lead-Free Solderable:

Yes (ESQT-368)

| SERIES | 1 | NO. PINS PER ROW | LEAD STYLE                    | PLATING OPTION                                                                                  | Q | 368 |
|--------|---|------------------|-------------------------------|-------------------------------------------------------------------------------------------------|---|-----|
| ESQT   |   | 30               | Specify LEAD STYLE from chart | -GF<br>= 15 $\mu$ " (0.38 $\mu$ m)<br>Gold on contact, Gold flash on tail (-02 Lead Style only) |   |     |
| PTHF   |   |                  |                               | -M<br>= 20 $\mu$ " (0.51 $\mu$ m)<br>Gold on contact, Matte Tin on tail (-03 Lead Style only)   |   |     |



| LEAD STYLE | ESQT         | PTHF         |
|------------|--------------|--------------|
|            | A            | B            |
| -02        | (21.59) .850 | (12.24) .482 |
| -03        | (11.63) .458 | (3.00) .118  |

## TOOLING

Press-Fit  
CAT-PT-130-A-4

For more information, visit  
[www.samtec.com/tooling](http://www.samtec.com/tooling)

### Note:

This Series is non-standard,  
non-returnable.

ESQT (-368) SERIES

PTHF SERIES

[samtec.com?ESQT](http://samtec.com?ESQT) or [samtec.com?PTHF](http://samtec.com?PTHF)

F-221 (Rev 28APR21)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ESQT-105-02-L-D-438](#)