


# FLAT FLEXIBLE CABLE (FCC) JUMPER & SOCKET

(1.00 mm) .0394" PITCH • FJ/ZF1/FC1 SERIES



## FJ

**Mates:**  
FC1, ZF1

## ZF1/FC1

**Mates:**  
FJ

### SPECIFICATIONS

#### FJ



**Conductor:**  
Tin Plated Copper  
**Conductor Resistance:**  
300  $\Omega$ /km max  
**Operating Temp Range:**  
-30 °C to +80 °C  
**Voltage Rating:**  
300 VAC

#### ZF1

**Insulator Material:**  
Liquid Crystal Polymer  
**Contact Material:**  
Phosphor Bronze  
**Plating:**  
Sn over 40  $\mu$ " (1.02  $\mu$ m) Ni  
**Weld Tab:** Phosphor Bronze  
**Operating Temp Range:**  
-55 °C to +105 °C

#### FC1


**Insulator Material:**  
Liquid Crystal Polymer  
**Contact Material:**  
Phosphor Bronze  
**Plating:**  
Sn over 50  $\mu$ " (1.27  $\mu$ m) Ni  
**Operating Temp Range:**  
-55 °C to +105 °C  
**Max Cycles:**  
25 with FJ



### PROCESSING

#### ZF1/FC1

**Lead-Free Solderable:**  
Yes  
**SMT Lead Coplanarity:**  
(0.10 mm) .004" max



**Notes:**  
FJ Stiffener color will be blue or black at Samtec's discretion.

Some sizes, styles and options are non-standard, non-returnable.

[samtec.com?FJ](http://samtec.com?FJ), [samtec.com?ZF1](http://samtec.com?ZF1) or [samtec.com?FC1](http://samtec.com?FC1)

F-224 WEB

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Samtec:

[FC1-15-01-T-LC](#) [FC1-05-01-T](#) [FC1-05-01-T-K-TR](#) [FC1-10-01-T-LC](#) [FC1-20-01-T-LC](#) [FC1-05-02-T-WT-TR](#) [FC1-05-01-T-LC](#) [FC1-05-02-T-WT](#) [FC1-15-02-T-WT](#) [FC1-10-01-T](#) [FC1-05-02-T](#) [FC1-20-01-T](#) [FC1-10-02-T-WT](#) [FC1-20-02-T-WT](#) [FC1-10-01-T-K-TR](#) [FC1-15-01-T](#) [FC1-15-02-T](#) [FC1-15-02-T-WT-TR](#) [FC1-25-01-T-LC-K](#) [FC1-25-02-T-WT](#) [FC1-15-L2-T](#) [FC1-20-L1-T-LC](#) [FC1-05-L1-T](#) [FC1-05-L1-T-K](#) [FC1-05-L1-T-LC](#) [FC1-15-L1-T](#) [FC1-25-01-T-LC](#) [FC1-25-02-T](#) [FC1-25-L2-T](#) [FC1-15-L1-T-LC](#) [FC1-25-L2-T-WT](#) [FC1-05-L1-T-K-TR](#) [FC1-08-L1-T-K](#) [FC1-10-L2-T](#) [FC1-16-02-T-WT](#) [FC1-20-L2-T-WT](#) [FC1-25-L1-T](#) [FC1-15-01-T-K](#) [FC1-25-L1-T-LC](#) [FC1-10-L1-T](#) [FC1-20-01-T-LC-TR](#) [FC1-20-02-T](#) [FC1-10-02-T](#) [FC1-10-L1-T-LC](#) [FC1-05-L2-T](#) [FC1-10-L2-T-WT](#) [FC1-16-02-T](#) [FC1-20-L1-T](#) [FC1-20-L2-T](#) [FC1-15-01-T-LC-TR](#) [FC1-20-01-T-TR](#) [FC1-25-L2-T-WT-TR](#) [FC1-06-02-T-WT](#) [FC1-08-01-T-LC-K-TR](#) [FC1-22-L2-T-WT](#) [FC1-06-01-T](#) [FC1-08-02-T-WT](#) [FC1-14-01-T-LC](#) [FC1-22-02-T-WT](#) [FC1-07-L2-T-WT](#) [FC1-08-01-T-K](#) [FC1-08-01-T-K-TR](#) [FC1-12-01-T](#) [FC1-15-L2-T-WT-TR](#) [FC1-25-01-T-K-TR](#) [FC1-10-L1-T-K](#) [FC1-05-01-T-LC-K](#) [FC1-06-L2-T](#) [FC1-12-01-T-LC](#) [FC1-25-01-T-TR](#) [FC1-12-02-T-WT-TR](#) [FC1-15-L1-T-LC-TR](#) [FC1-18-02-T](#) [FC1-05-01-T-TR](#) [FC1-15-01-T-LC-K-TR](#) [FC1-20-02-T-TR](#) [FC1-10-01-T-K](#) [FC1-15-02-T-TR](#) [FC1-18-01-T-K-TR](#) [FC1-20-01-T-K](#) [FC1-20-L2-T-WT-TR](#) [FC1-05-02-T-TR](#) [FC1-10-01-T-LC-K](#) [FC1-10-01-T-LC-TR](#) [FC1-15-L2-T-TR](#) [FC1-18-01-T-LC](#) [FC1-06-01-T-LC](#) [FC1-15-01-T-K-TR](#) [FC1-06-L1-T-K](#) [FC1-07-02-T-WT](#) [FC1-15-01-T-TR](#) [FC1-15-L1-T-K](#) [FC1-10-01-T-LC-K-TR](#) [FC1-16-01-T](#) [FC1-20-01-T-LC-K-TR](#) [FC1-10-L1-T-TR](#) [FC1-12-02-T-WT](#) [FC1-16-01-T-K-TR](#) [FC1-16-L1-T](#) [FC1-16-L1-T-K](#)