


POWER HEADERS, STACKERS & SOCKETS

(5.08 mm) .200" PITCH • HPM, HPW, HPF SERIES

MAX
16.1
A m p s



HPM, HPW
Board Mates:
HPF

HPF
Board Mates:
HPM, HPW

SPECIFICATIONS

Insulator Material:
HPW/HPM = Glass Filled Polyester (Through-hole), Natural Liquid Crystal Polymer (Surface Mount)
HPF = Black LCP
Terminal Material (HPM/HPW):
Copper Alloy
Contact Material (HPF):
BeCu
Plating:
Sn over 50 μ " (1.27 μ m) Ni
Operating Temp Range:
-55 °C to +105 °C
Voltage Rating:
HPM/HPF = 850 VAC/1200 VDC
Insertion Depth (HPF):
(3.68 mm) .145" to (8.26 mm) .325" (.368" (9.35 mm) plus board thickness minimum for bottom entry)
Wiping Distance (HPF):
(0.38 mm) .015"

PROCESSING

Lead-Free Solderable:
HPW-VS, HPM-VS, HPF = Yes
HPM -TH, HPM -RA & HPW -TH = No, Lead Wave only
SMT Lead Coplanarity:
HPM = (0.20 mm) .008" max (02-15)*
HPM = (0.25 mm) .010" max (16-20)*
HPW = (0.20 mm) .008" max*
HPF = (0.15 mm) .006" max (02-10)*
(0.20 mm) .008" max (11-20)*
*(.004" stencil solution may be available; contact IPG@samtec.com)

Note:
Some lengths, styles and options are non-standard, non-returnable.

HPM	NO. OF PINS	LEAD STYLE	PLATING OPTION	S	TAIL OPTION	OTHER OPTION
-----	-------------	------------	----------------	---	-------------	--------------

High Temp
High Power
Header


01 thru 20

Specify
LEAD
STYLE
from
chart
below

-T
= Matte Tin

Leave blank for
Through-hole
-RA
= Right-angle
(-02 & -04 lead style only)
-VS
= Surface Mount
(2 pins/row minimum)
(-01 & -02 lead style only)

-P
= Pick & Place
Pad (3 Pos. min.)
(-VS only)
(Not Available
with -05
lead style)



LEAD STYLE	A	B	C	D	E	F	G
-01	(4.57) .180	(11.94) .470	-	-	-	(10.72) .422	(8.64) .340
-02	(4.57) .180	(13.21) .520	(2.54) .100	(4.57) .180	(8.08) .318	(12.24) .482	(8.38) .330
-04	(4.09) .161	(21.06) .829	(4.95) .195	(3.96) .156	(13.82) .544	-	-
-05	(4.57) .180	(3.81) .150	-	-	-	-	-

HPW	NO. OF PINS	04	PLATING OPTION	S	STACK HEIGHT	POST HEIGHT	OTHER OPTIONS
-----	-------------	----	----------------	---	--------------	-------------	---------------

High Temp
High Power

02 thru 20


-T
= Matte Tin

- "XXX"
= Stacker
Height (in
inches)
(0.13 mm) .005"
increments

- "XXX"
= Post Height
(in inches)

Leave blank for
Through-hole
-VS
= Surface Mount
(2 pins/row minimum)

-P
= Pick & Place Pad
(3 Pos. min.) (6.98 mm)
.275" min. post height
(-VS only)



HPF	NO. OF PINS	LEAD STYLE	PLATING OPTION	S	OTHER OPTIONS
-----	-------------	------------	----------------	---	---------------

02 thru 20

-01
= Through-hole
-02
= Surface Mount


-T
= Matte Tin

-LC
= Locking Clip
(Manual
placement
required)
(-02 lead
style only)

-TR
= Tape & Reel
Packaging
(14 positions max.)
(Style -02 only)

-K
= (6.50 mm)
.256" DIA
Polyimide
film Pick
& Place Pad

-FR
= Full Reel
Tape & Reel
(must order max.
quantity per reel;
contact Samtec
for quantity
breaks)
(14 positions max.)
(Style -02 only)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[HPW-02-04-T-S-645-275](#) [HPW-03-04-T-S-375-090](#) [HPW-03-04-T-S-419-300](#) [HPW-04-04-T-S-200-235](#) [HPW-10-04-T-S-630-110-VS](#) [HPW-10-04-T-S-630-250-VS](#) [HPW-06-04-T-S-400-310](#) [HPW-12-04-T-S-400-325](#) [HPW-05-04-T-S-350-250](#) [HPW-05-04-T-S-650-300](#) [HPW-06-04-T-S-420-275](#) [HPW-04-04-T-S-200-100](#) [HPW-04-04-T-S-380-110-VS](#) [HPW-04-04-T-S-655-110](#) [HPW-14-04-T-S-225-235](#) [HPW-07-04-T-S-500-150](#) [HPW-08-04-T-S-635-236](#) [HPW-06-04-T-S-500-150](#) [HPW-08-04-T-S-419-300](#) [HPW-12-04-T-S-650-300](#) [HPW-03-04-T-S-450-300](#) [HPW-10-04-T-S-262-217](#) [HPW-10-04-T-S-380-300](#) [HPW-04-04-T-S-420-275](#) [HPW-04-04-T-S-655-110-VS](#) [HPW-20-04-T-S-650-250](#) [HPW-04-04-T-S-650-250](#) [HPW-06-04-T-S-250-285](#) [HPW-08-04-T-S-380-250](#) [HPW-02-04-T-S-755-235](#) [HPW-04-04-T-S-416-275](#) [HPW-06-04-T-S-265-270](#) [HPW-08-04-T-S-375-300](#) [HPW-08-04-T-S-650-300](#) [HPW-12-04-T-S-200-250](#) [HPW-20-04-T-S-300-300-VS](#) [HPW-02-04-T-S-750-100](#) [HPW-04-04-T-S-380-250](#) [HPW-04-04-T-S-655-275](#) [HPW-10-04-T-S-820-250](#) [HPW-04-04-T-S-550-215-VS](#) [HPW-04-04-T-S-635-236](#) [HPW-02-04-T-S-625-090](#) [HPW-02-04-T-S-630-190](#) [HPW-04-04-T-S-630-190](#) [HPW-06-04-T-S-400-150](#) [HPW-07-04-T-S-650-170](#) [HPW-14-04-T-S-250-300](#) [HPW-15-04-T-S-800-200](#) [HPW-03-04-T-S-635-110](#) [HPW-10-04-T-S-500-250](#) [HPW-10-04-T-S-540-250](#) [HPW-10-04-T-S-550-250](#) [HPW-03-04-T-S-295-090](#) [HPW-03-04-T-S-505-470](#) [HPW-04-04-T-S-312-150](#) [HPW-05-04-T-S-650-270](#) [HPW-05-04-T-S-750-225](#) [HPW-04-04-T-S-275-275](#) [HPW-05-04-T-S-750-300](#) [HPW-05-04-T-S-750-350](#) [HPW-09-04-T-S-420-150-VS](#) [HPW-02-04-T-S-240-250](#) [HPW-03-04-T-S-200-315](#) [HPW-04-04-T-S-420-150-VS](#) [HPW-06-04-T-S-380-250](#) [HPW-08-04-T-S-295-090](#) [HPW-12-04-T-S-225-300](#) [HPW-20-04-T-S-200-200](#) [HPW-03-04-T-S-205-250](#) [HPW-04-04-T-S-470-275](#) [HPW-04-04-T-S-650-150](#) [HPW-04-04-T-S-650-300](#) [HPW-06-04-T-S-385-285](#) [HPW-10-04-T-S-800-200](#) [HPW-02-04-T-S-250-090](#) [HPW-02-04-T-S-720-235](#) [HPW-04-04-T-S-550-250](#) [HPW-06-04-T-S-400-110](#) [HPW-06-04-T-S-472-512](#) [HPW-07-04-T-S-750-300](#) [HPW-12-04-T-S-250-090](#) [HPW-14-04-T-S-600-100](#) [HPW-04-04-T-S-280-240](#) [HPW-04-04-T-S-332-225-VS](#) [HPW-06-04-T-S-500-000](#) [HPW-20-04-T-S-820-200](#) [HPW-03-04-T-S-510-620](#) [HPW-04-04-T-S-390-150](#) [HPW-04-04-T-S-725-450](#) [HPW-07-04-T-S-380-325](#) [HPW-08-04-T-S-820-000](#) [HPW-02-04-TM-S-750-100](#) [HPW-02-04-T-S-500-500](#) [HPW-03-04-T-S-515-465](#) [HPW-04-04-T-S-375-175](#) [HPW-04-04-T-S-755-245](#) [HPW-05-04-T-S-400-250](#) [HPW-05-04-T-S-785-315](#) [HPW-07-04-T-S-380-245](#)