


ISOLATED POWER SYSTEMS


FEATURES & BENEFITS

- Individually shrouded contacts for electrical and mechanical protection
- .100" (2.54 mm) and .165" (4.19 mm) pitch
- Surface mount or through-hole
- Vertical and right-angle for parallel, perpendicular and coplanar applications
- Locking clip, key polarization and guide post options
- Discrete wire assemblies with 16-30 AWG PVC or Teflon™ fluoropolymer wire (see pages 243-245).
- Metal or plastic rugged latching system

*Teflon™ is a trademark of The Chemours Company FC, LLC used under license by Samtec



Selectively loading contacts achieves customer specific creepage and clearance requirements.



Flexible standard or high-power stacking systems with Power Eye three-finger BeCu contacts for reliable connection. For available series, visit samtec.com/flexiblestrips

CREEPAGE & CLEARANCE

	CREEPAGE	CLEARANCE
IPT1/IPBS MMSS(T)/MMSD(T)	2.54 mm	1.91 mm
IPBT/IPBS PMSS(T)/PMSD(T)	4.27 mm	3.05 mm



Selectively loading contacts achieves customer specific creepage and clearance requirements.

KEY SPECIFICATIONS

SERIES	PITCH	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	VOLTAGE RATING	LEAD-FREE SOLDERABLE
IPT1/IPBS1	.100" (2.54 mm)	Black LCP	Phosphor Bronze	Sn or Au over 50 μ" (1.27 μm) Nickel	-55 °C to +125 °C	5.9 A (1 pin power)	775 VAC	Yes
IPBT/IPBS	.165" (4.19 mm)	Black LCP	High Copper Alloy (IPBT) Phosphor Bronze (IPBS)	Sn over 50 μ" (1.27 μm) Nickel	-55 °C to +105 °C	10.3 A (2 pins power)	400 VAC	Yes

IPBT	1	NO. OF POSITIONS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OPTIONS
		02, 03, 04, 05, 08, 10	-H1 = Through-hole	-T = Matte Tin	-S = Single Row	-RA = Right-angle (Lead Style -H1 only)
		15 (-D Only) (Standard Sizes)	-H2 = Surface Mount		-D = Double Row	-GP = Guide Post Holes (Not available with -K)
						-K = Keyed Polarization (Not available with -GP option, is required callout if -GP not called out)




IPBT
Board Mates:
IPBS
Cable Mates:
PMSSD, PMSS



IPBT/IPBS	
PINS POWERED	CURRENT RATING (PER CONTACT)
2	10.3 A
4	8.4 A
6	7.6 A
8	7.1 A
30	6.0 A

IPBS	1	NO. OF POSITIONS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OPTION
		02, 03, 04, 05, 08, 10	-01 = Standard Power	-T = Matte Tin	-S = Single Row	-GP = Guide Post
		15 (-D Only) (Standard Sizes)	-02 = Standard Power Surface Mount		-D = Double Row	

IPBS
Board Mates:
IPBT



IPBT/IPBS LEAD STYLE	MATED HEIGHT*
H1/-01	(15.25) .600
-H2/-02	(16.84) .663

*Processing conditions will affect mated height.

Note:
Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: samtec.com?IPBT & samtec.com?IPBS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[IPBS-102-02-T-D-GP](#) [IPBS-104-02-T-D](#) [IPBS-110-01-T-D-GP](#) [IPBS-108-01-T-D](#) [IPBS-104-01-T-S](#) [IPBS-102-02-T-D](#)
[IPBS-102-01-T-D](#) [IPBS-104-01-T-D-GP](#) [IPBS-115-01-T-D](#) [IPBS-105-01-T-D](#) [IPBS-110-01-T-D](#) [IPBS-103-01-T-D](#)
[IPBS-102-01-T-S](#) [IPBS-105-02-T-D](#) [IPBS-102-01-T-D-GP](#) [IPBS-105-01-T-S](#) [IPBS-103-01-T-S-GP](#) [IPBS-105-01-T-D-](#)
[GP](#) [IPBS-104-01-T-D](#) [IPBS-115-01-T-D-GP](#) [IPBS-104-01-T-S-GP](#) [IPBS-108-01-T-D-GP](#) [IPBS-103-01-T-D-GP](#) [IPBS-](#)
[105-01-T-S-GP](#) [IPBS-107-02-T-S](#) [IPBS-114-01-T-D](#) [IPBS-106-01-T-D](#) [IPBS-112-02-T-D](#) [IPBS-112-02-T-D-GP](#) [IPBS-](#)
[113-01-T-D](#) [IPBS-113-01-T-D-GP](#) [IPBS-109-01-T-D-GP](#) [IPBS-111-01-T-D-GP](#) [IPBS-112-01-T-D-GP](#) [IPBS-109-01-T-](#)
[D](#) [IPBS-111-01-T-D](#) [IPBS-110-02-T-D-GP](#) [IPBS-107-01-T-D](#) [IPBS-115-02-T-D-GP](#) [IPBS-106-01-T-D-GP](#) [IPBS-107-](#)
[01-T-D-GP](#) [IPBS-108-02-T-D-GP](#) [IPBS-103-02-T-D-GP](#) [IPBS-105-02-T-D-GP](#) [IPBS-109-02-T-D-GP](#) [IPBS-112-01-T-D](#)
[IPBS-115-02-T-D](#) [IPBS-110-02-T-D](#) [IPBS-114-01-T-D-GP](#) [IPBS-104-02-T-D-GP](#) [IPBS-105-01-TM-D](#) [IPBS-106-02-](#)
[T-D](#) [IPBS-108-02-T-D](#) [IPBS-110-01-T-S-GP](#) [IPBS-104-01-TM-D-GP](#) [IPBS-115-01-TM-D](#) [IPBS-106-02-T-D-GP](#) [IPBS-](#)
[103-02-T-D](#) [IPBS-115-01-TM-D-GP](#) [IPBS-115-02-TM-D](#) [IPBS-102-01-T-S-GP](#) [IPBS-102-02-T-S](#) [IPBS-106-01-T-S](#)
[IPBS-106-01-T-S-GP](#) [IPBS-103-01-T-S](#) [IPBS-107-01-T-S](#) [IPBS-108-01-T-S](#) [IPBS-103-02-T-S](#) [IPBS-102-02-T-S-GP](#)
[IPBS-105-02-T-S-GP](#) [IPBS-104-02-T-S](#) [IPBS-104-02-T-S-GP](#) [IPBS-105-02-T-S](#) [IPBS-108-02-T-S](#) [IPBS-103-01-TM-D](#)
[IPBS-112-01-TM-D-GP](#) [IPBS-108-01-TM-D](#) [IPBS-110-01-TM-D](#) [IPBS-102-01-TM-S](#) [IPBS-103-02-T-S-GP](#) [IPBS-](#)
[104-01-TM-D](#) [IPBS-110-01-TM-D-GP](#) [IPBS-107-01-TM-D-GP](#) [IPBS-108-01-T-S-GP](#) [IPBS-104-02-TM-D](#) [IPBS-110-](#)
[02-T-S](#) [IPBS-108-02-T-S-GP](#) [IPBT-102-H1-S-D-RA-K](#) [IPBT-109-H4-S-D-K](#) [IPBT-102-H2-TM-S-K](#) [IPBT-105-H1-TM-S-](#)
[K](#) [IPBT-110-H1-L-S-K](#) [IPBS-110-02-T-S-GP](#) [IPBT-110-H1-S-S-K](#) [IPBT-115-H1-L-D-K](#) [IPBS-105-01-TM-S](#) [IPBT-115-](#)
[H1-S-D-K](#) [IPBT-110-H1-TM-D-K](#) [IPBT-103-H1-S-D-K](#) [IPBT-103-H1-S-D-RA-K](#)