


ISOLATED POWER SYSTEMS


FEATURES & BENEFITS

- Individually shrouded contacts for electrical and mechanical protection
- .100" (2.54 mm) and .165" (4.19 mm) pitch
- Surface mount or through-hole
- Vertical and right-angle for parallel, perpendicular and coplanar applications
- Locking clip, key polarization and guide post options
- Discrete wire assemblies with 16-30 AWG PVC or Teflon™ fluoropolymer wire.
- Metal or plastic rugged latching system

*Teflon™ is a trademark of The Chemours Company FC, LLC used under license by Samtec



Selectively loading contacts achieves customer specific creepage and clearance requirements.



Flexible standard or high-power stacking systems with Power Eye three-finger BeCu contacts for reliable connection. For available series, visit samtec.com/flexiblestrips

CREEPAGE & CLEARANCE

	CREEPAGE	CLEARANCE
IPT1/IPBS MMSS(T)/MMSD(T)	2.54 mm	1.91 mm
IPBT/IPBS PMSS(T)/PMSD(T)	4.27 mm	3.05 mm

Selectively loading contacts achieves customer specific creepage and clearance requirements.



KEY SPECIFICATIONS

SERIES	PITCH	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	VOLTAGE RATING	LEAD-FREE SOLDERABLE
IPT1/IPBS1	.100" (2.54 mm)	Black LCP	Phosphor Bronze	Sn or Au over 50 μ" (1.27 μm) Nickel	-55 °C to +125 °C	5.9 A (2 pin power)	775 VAC	Yes
IPBT/IPBS	.165" (4.19 mm)	Black LCP	High Copper Alloy (IPBT) Phosphor Bronze (IPBS)	Sn over 50 μ" (1.27 μm) Nickel	-55 °C to +105 °C	10.3 A (2 pins power)	400 VAC	Yes

(2.54 mm) .100" PITCH • SHROUDED POWER CONNECTOR SET

IPT1	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	TAIL OPTION	OTHER OPTIONS
		05	Specify LEAD STYLE from chart	-L = 10 μ " (0.25 μ m) Gold on contact, Matte Tin on tail		Requires -01 Lead Style (Leave blank for Through-hole)	-A = Alignment Pin (-VS only) (N/A with -LC)
		10					
		15					
		20					
		25 (Standard Sizes)					
						-RA = Right-angle	-LC = Locking Clip (Manual placement required) (-VS only) (N/A with -A)
						-VS = Surface Mount	-K = (6.00 mm) .236" DIA Polyimide film Pick & Place Pad (-VS only)
							-TR = Tape & Reel (-VS only)
							-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-VS only)

IPT1 Board Mates: IPS1





IPT1/IPS1	
PINS	CURRENT RATING (PER CONTACT)
2	5.9 A
4	4.8 A
6	4.1 A
8	3.6 A
50	2.3 A

LEAD STYLE	MATED HEIGHT	A	B
-01	(11.05) .435	(6.35) .250	(2.16) .085
-01-VS	(13.59) .535	(6.35) .250	N/A
-02	(14.00) .551	(9.30) .366	(2.64) .104
-03	(16.00) .630	(11.30) .445	(2.16) .085
-04	(17.00) .669	(12.30) .484	(2.69) .106
-05	(19.00) .748	(14.30) .563	(2.46) .097
-06	(20.00) .787	(15.30) .602	(2.35) .093
-07	(25.00) .984	(20.30) .799	(2.31) .091
-08	(30.00) 1.181	(25.30) .996	(2.39) .094
-09	(35.00) 1.378	(30.30) 1.193	(2.46) .097

IPS1	1	NO. PINS PER ROW	01	PLATING OPTION	D	TAIL OPTION	OTHER OPTIONS
		05		-L = 10 μ " (0.25 μ m) Gold on contact, Matte Tin on tail		Leave blank for Through-hole	-LC = Locking Clip (Manual placement required) (-VS only)
		10					
		15					
		20					
		25 (Standard Sizes)					
						-RA = Right-angle	-K = (5.50 mm) .217" DIA Polyimide film Pick & Place Pad (-VS only)
						-VS = Surface Mount	
							-TR = Tape & Reel (-VS only)
							-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-VS only)

IPS1 Board Mates: IPT1



Note:
Some lengths, styles and
options are non-standard,
non-returnable.

View complete specifications at: samtec.com?IPT1 & samtec.com?IPS1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[IPT1-115-01-S-D-RA](#) [IPT1-125-01-S-D](#) [IPT1-120-01-S-D](#) [IPT1-105-01-S-D](#) [IPT1-105-01-S-D-RA](#) [IPT1-110-01-S-D-RA](#) [IPT1-106-01-S-D-RA](#) [IPT1-120-01-L-D](#) [IPT1-105-01-L-D](#) [IPT1-125-01-L-D-RA](#) [IPT1-120-01-L-D-RA](#) [IPT1-115-01-L-D](#) [IPT1-120-01-S-D-RA](#) [IPT1-115-01-L-D-RA](#) [IPT1-105-02-L-D](#) [IPT1-115-01-S-D](#) [IPT1-110-01-L-D-VS](#) [IPT1-110-05-L-D](#) [IPT1-110-03-L-D](#) [IPT1-110-01-S-D-PL](#) [IPT1-110-01-L-D](#) [IPT1-110-01-S-D](#) [IPT1-110-01-L-D-RA](#) [IPT1-110-04-L-D](#) [IPT1-105-06-L-D](#) [IPT1-120-01-L-D-VS](#) [IPT1-110-06-L-D](#) [IPT1-105-01-L-D-VS](#) [IPT1-115-01-L-D-VS](#) [IPT1-125-01-L-D](#) [IPT1-105-07-L-D](#) [IPT1-105-01-L-D-RA](#) [IPT1-105-04-L-D](#) [IPT1-105-03-L-D](#) [IPT1-107-01-L-D-RA](#) [IPT1-108-01-L-D](#) [IPT1-104-01-L-D-VS](#) [IPT1-115-01-L-D-VS-K-TR](#) [IPT1-117-01-L-D-VS](#) [IPT1-109-01-S-D](#) [IPT1-110-01-S-D-VS](#) [IPT1-103-01-S-D](#) [IPT1-118-01-S-D-RA](#) [IPT1-150-01-S-D-VS](#) [IPT1-111-01-S-D-VS-A](#) [IPT1-117-01-S-D](#) [IPT1-110-01-S-D-VS-A-K](#) [IPT1-105-01-S-D-VS](#) [IPT1-113-01-S-D](#) [IPT1-105-01-S-D-VS-A](#) [IPT1-107-01-S-D](#) [IPT1-125-01-S-D-RA](#) [IPT1-111-01-S-D-VS](#) [IPT1-150-01-S-D](#) [IPT1-120-01-S-D-VS](#) [IPT1-120-01-S-D-VS-LC](#) [IPT1-125-01-S-D-VS](#) [IPT1-108-01-S-D](#) [IPT1-111-01-S-D-RA](#) [IPT1-115-01-S-D-VS-A](#) [IPT1-125-01-S-D-VS-A](#) [IPT1-105-01-S-D-VS-LC](#) [IPT1-106-01-S-D-VS](#) [IPT1-115-01-S-D-VS](#) [IPT1-105-01-S-D-FL](#) [IPT1-125-01-S-D-VS-FL](#) [IPT1-120-01-S-D-VS-K](#) [IPT1-112-01-S-D](#) [IPT1-112-01-S-D-RA](#) [IPT1-115-01-S-D-DH-A](#) [IPT1-125-01-S-D-VS-LC](#) [IPT1-110-01-S-D-VS-LC](#) [IPT1-115-01-S-D-VS-LC](#) [IPT1-125-01-S-D-DH-A](#) [IPT1-105-01-SM-D-VS](#) [IPT1-116-01-S-D-VS-LC-K](#) [IPT1-104-01-S-D-DH-A](#) [IPT1-105-01-S-D-VS-FL](#) [IPT1-110-01-S-D-VS-A](#) [IPT1-106-01-S-D](#) [IPT1-106-01-S-D-VS-LC](#) [IPT1-103-01-SM-D](#) [IPT1-110-01-S-D-VS-A-K-TR](#) [IPT1-102-01-S-D](#) [IPT1-108-01-S-D-VS-LC](#) [IPT1-125-01-S-D-FL](#) [IPT1-111-01-S-D](#) [IPT1-105-01-S-D-VS-A-K](#) [IPT1-107-01-SM-D](#) [IPT1-112-01-S-D-VS](#) [IPT1-110-01-SM-D](#) [IPT1-104-01-S-D](#) [IPT1-120-01-S-D-VS-A](#) [IPT1-110-01-S-D-FL](#) [IPT1-105-01-S-D-DH-A](#) [IPT1-110-01-SM-D-VS](#) [IPT1-105-01-SM-D](#) [IPT1-111-01-S-D-VS-A-K](#) [IPT1-102-01-S-D-VS](#) [IPT1-110-01-S-D-VS-FL](#)