



SERIES	PINS PER ROW	WIRE GAUGE	PLATING OPTION	ASSEMBLY LENGTH	END OPTION	K	LATCH OPTION				
MMSD = Double Row PVC Cable	-02, -03, -04, -05, -06, -08, -10, -12, -15, -16, -20, -25 (Standard sizes)	-20 = Color Coded Cable (MMSD & MMSS only)	-L = 10 μ" (0.25 μm) Gold on contact, Tin on tail	-"XX.XX" = Assembly Length in Inches (82.55 mm) 03.25" min.	-S = Single Ended -D = Double Ended (Latch Required)	-K = Keyed Polarization	(Metal latches for more rugged environments; -02, -05 & -10 positions only) -M = Single Ended, Metal Latches (Leave blank for plastic) Double Ended (-D) Crossed requires MMSD/MMSDT				
MMSDT = Double Row Blue *Teflon™ Fluoropolymer Cable (20, 24, 28, 30 AWG only)		-24C = Color Coded Cable (MMSD & MMSS only)									
MMSS = Single Row PVC Cable		-22, -24									
MMSST = Single Row Blue *Teflon™ Fluoropolymer Cable (20, 24, 28, 30 AWG)		-26, -28 -28C = Color Coded Cable (MMSD & MMSS only)									
MMSD, MMSDT, MMSS, MMSST Board Mates: IPL1 (Does not mate with IPT1) Cable Mates: MMTD(T), MMTS(T)		-30									
SPECIFICATIONS											
Insulator Material: Nylon 66 Contact Material: Phosphor Bronze Plating: Au or Sn over 50 μ" (1.27 μm) Ni Operating Temp Range: -10 °C to +80 °C (PVC) -40 °C to +125 °C (*Teflon™) Current Rating: 4.8 A (2 pins powered) Voltage Rating: 275 VAC/389 VDC											
*Teflon™ is a trademark of The Chemours Company FC, LLC used under license by Samtec. Teflon™ Fluoropolymer cable is intended for crimp only. Contact Samtec for solderable cable applications.											
<table><tr><td colspan="2">No. of positions x (2.54) .100 + (1.40) .055</td></tr><tr><td>(8.97) .353</td><td></td></tr></table>				No. of positions x (2.54) .100 + (1.40) .055		(8.97) .353					
No. of positions x (2.54) .100 + (1.40) .055											
(8.97) .353											

View complete specifications at: samtec.com?MMSD, samtec.com?MMSDT, samtec.com?MMSS & samtec.com?MMSST

IPD1	POSITIONS PER ROW	ROW OPTION	K	LATCH OPTION	SERIES	WIRE GAUGE	01	PLATING OPTION
	-02, -03, -04, -05, -06, -08, -10, -12, -15, -16, -20, -25 (Standard sizes)	-S = Single Row -D = Double Row	-K = Keyed Polarization	-M = Metal Latch (Metal for more rugged environments) (-02, -05 & -10 positions only) (Leave blank for plastic latch)	CC79L = Contact, Loose CC79R = Contact, Full Reel (12,000 Parts per Reel)	-2630 = 26 to 30 AWG -2024 = 20 to 24 AWG		-L = 10 μ" (0.25 μm) Gold on contact, Tin on tail

TOOLING

Note:
Some lengths, styles and options are non-standard, non-returnable.

Hand Tool: CAT-HT-179-2030-13 (20-30 AWG)

Mini Applicator: CAT-MC-179-2024-XX-01 (20-24 AWG)
Mini Applicator: CAT-MC-179-2630 XX-01 (26-30 AWG)
Extraction Tool: CAT-EX-179-01

View complete specifications at: samtec.com?IPD1, samtec.com?CC79L & samtec.com?CC79R

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[MMSDT-05-24-L-05.00-D-P-MUS](#) [MMSDT-10-24-L-12.00-D-P-MUS](#) [MMSDT-06-20-S-05.5-D-K-LDX](#)