


# SMT & THROUGH-HOLE BOARD STACKERS

(2.00 mm) .0787" PITCH • TW SERIES

CLT or MMS	SQT
8	4
G b p s	G b p s



## TW

### Board Mates:

CLT, SQT, SQW, ESQT,  
TLE, SMM, MMS

### Cable Mates:

TCSD

## SPECIFICATIONS

### Insulator Material:

Black Liquid Crystal Polymer  
**Terminal Material:**  
Phosphor Bronze

### Plating:

Sn or Au over  
50  $\mu$ " (1.27  $\mu$ m) Ni

### Current Rating:

TW-SM = 4.9 A per pin  
(2 pins powered)  
TW-TH = 5.2 A per pin  
(2 pins powered)

### Operating Temp Range:

-55 °C to +105 °C with Tin;  
-55 °C to +125 °C with Gold

## PROCESSING



### Lead-Free Solderable:

Yes

### SMT Lead Coplanarity:

(0.15 mm) .006" max\*  
\*(.004" stencil solution  
may be available; contact  
ipg@samtec.com)

TW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	SM	OTHER OPTION																				
	02 thru 36	Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail  -L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail  -T = Matte Tin	-S = Single Row  -D = Double Row	-“XXX” = Stacker Height in inches (0.13 mm) .005" increments  Example: -250 = (6.35 mm) .250"		-“XXX” = Polarized Position  -A = Alignment Pin (Metal or plastic at Samtec discretion) (4.83 mm) .190" min. board space (-D only)  -P = Pick & Place Pad (1.91 mm) .075" min. post height (04-36 only)																				
		<table><tr><th>LEAD STYLE</th><th>OAL</th></tr><tr><td>-02</td><td>(7.85) .309</td></tr><tr><td>-03</td><td>(11.86) .467</td></tr><tr><td>-04</td><td>(12.37) .487</td></tr><tr><td>-06</td><td>(15.37) .605</td></tr><tr><td>-07</td><td>(17.35) .683</td></tr><tr><td>-09</td><td>(9.86) .388</td></tr></table>		LEAD STYLE	OAL	-02	(7.85) .309	-03	(11.86) .467	-04	(12.37) .487	-06	(15.37) .605	-07	(17.35) .683	-09	(9.86) .388	<table><tr><th>ROW OPTION</th><th>A</th></tr><tr><td>-S</td><td>(5.08) .200</td></tr><tr><td>-D</td><td>(6.35) .250</td></tr></table>		ROW OPTION	A	-S	(5.08) .200	-D	(6.35) .250		
LEAD STYLE	OAL																										
-02	(7.85) .309																										
-03	(11.86) .467																										
-04	(12.37) .487																										
-06	(15.37) .605																										
-07	(17.35) .683																										
-09	(9.86) .388																										
ROW OPTION	A																										
-S	(5.08) .200																										
-D	(6.35) .250																										

TW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	TAIL SPEC																										
	02 thru 50	Specify LEAD STYLE from chart	<p>-F = Gold flash on post, Matte Tin on tail</p> <p>-L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail</p> <p>-T = Matte Tin</p>	<p>-S = Single Row</p> <p>-D = Double Row</p> <p>-T = Triple Row</p> <p>-Q = Four Row</p> <p>-5 = Five Row</p> <p>-6 = Six Row</p>	<p>-“XXX” = Stacker Height in inches (0.13 mm) .005" increments</p> <p>Example: -250 = (6.35 mm) .250"</p> <table><thead><tr><th>LEAD STYLE</th><th>OAL</th></tr></thead><tbody><tr><td>-01</td><td>(8.20) .323</td></tr><tr><td>-02</td><td>(9.60) .377</td></tr><tr><td>-03</td><td>(13.60) .535</td></tr><tr><td>-04</td><td>(14.10) .555</td></tr><tr><td>-05</td><td>(15.10) .594</td></tr><tr><td>-06</td><td>(17.10) .673</td></tr><tr><td>-07</td><td>(19.10) .751</td></tr><tr><td>-08*</td><td>(21.10) .830</td></tr><tr><td>-09</td><td>(11.60) .456</td></tr><tr><td>-10</td><td>(15.60) .614</td></tr><tr><td>-11</td><td>(10.08) .397</td></tr><tr><td>-12*</td><td>(28.19) 1.110</td></tr></tbody></table>	LEAD STYLE	OAL	-01	(8.20) .323	-02	(9.60) .377	-03	(13.60) .535	-04	(14.10) .555	-05	(15.10) .594	-06	(17.10) .673	-07	(19.10) .751	-08*	(21.10) .830	-09	(11.60) .456	-10	(15.60) .614	-11	(10.08) .397	-12*	(28.19) 1.110	<p>-“XXX” = Tail Length in inches (0.13 mm) .005" increments</p> <p>Example: -150 = (3.81 mm) .150"</p> <p>-“XXX” = Polarized Position (Specify position to be removed)</p>
LEAD STYLE	OAL																															
-01	(8.20) .323																															
-02	(9.60) .377																															
-03	(13.60) .535																															
-04	(14.10) .555																															
-05	(15.10) .594																															
-06	(17.10) .673																															
-07	(19.10) .751																															
-08*	(21.10) .830																															
-09	(11.60) .456																															
-10	(15.60) .614																															
-11	(10.08) .397																															
-12*	(28.19) 1.110																															
		<p>-S, -D*, -Q</p> <p>-T, -5, -6</p>																														
		<p>-S, -D*, -Q</p> <p>-T, -5, -6</p>																														
		<table><thead><tr><th>ROW OPTION</th><th>STACKER HEIGHT</th></tr></thead><tbody><tr><td>-S, -D*, -Q</td><td>(3.05) .120 MIN</td></tr><tr><td>-T, -5, -6</td><td>(4.06) .160 MIN</td></tr></tbody></table>		ROW OPTION	STACKER HEIGHT	-S, -D*, -Q	(3.05) .120 MIN	-T, -5, -6	(4.06) .160 MIN	<p>*-D with stacker height greater than (4.06 mm) .160" will not have standoffs.</p>																						
ROW OPTION	STACKER HEIGHT																															
-S, -D*, -Q	(3.05) .120 MIN																															
-T, -5, -6	(4.06) .160 MIN																															
		<p>*Style -08 &amp; -12 = S &amp; D only</p>																														

## Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TW-09-09-G-D-250-SM-009](#) [TW-10-04-T-D-300-SM-003](#) [TW-10-04-T-D-300-SM-007](#) [TW-10-06-T-D-500-SM-007](#)  
[TW-07-06-G-D-350-SM-003-M](#) [TW-07-09-G-D-170-SM-011](#) [TW-07-03-F-D-200-SM-130-P-TR](#) [TW-10-04-T-D-190-SM-](#)  
[001-M-TR](#) [TW-31-03-G-D-260-SM-062](#) [TW-31-03-G-D-339-SM-062](#) [TW-34-02-S-S-175-SM-005-P](#) [TW-34-02-S-S-](#)  
[175-SM-005-P-TR](#) [TW-35-04-F-D-250-SM-001](#) [TW-12-03-L-D-190-SM-001-P](#) [TW-20-06-T-D-190-SM-001-A-P-TR](#)  
[TW-20-09-F-D-223-SM-036](#) [TW-20-09-F-D-223-SM-036-P-TR](#) [TW-20-09-L-D-223-SM-036](#) [TW-21-03-F-D-200-SM-](#)  
[130-P-TR](#) [TW-31-02-G-D-190-SM-062](#) [TW-20-04-L-D-361-SM-036-P](#) [TW-20-04-T-D-285-SM-001](#) [TW-20-04-T-D-285-](#)  
[SM-001-P](#) [TW-20-04-T-D-285-SM-001-P-TR](#) [TW-20-04-T-D-285-SM-004-P-TR](#) [TW-20-04-T-D-285-SM-010-P-TR](#) [TW-](#)  
[20-03-L-D-272-SM-020](#) [TW-20-03-L-D-272-SM-020-P](#) [TW-20-04-F-D-322-SM-020-P-TR](#) [TW-20-04-F-D-361-SM-036](#)  
[TW-20-04-F-D-361-SM-036-P](#) [TW-20-04-L-D-361-SM-036](#) [TW-13-07-L-D-295-SM-140](#) [TW-14-03-L-D-170-SM-135-P-](#)  
[TR](#) [TW-14-06-L-D-400-SM-090-TR](#) [TW-20-03-F-D-272-SM-020](#) [TW-20-03-F-D-272-SM-020-P](#) [TW-20-03-F-D-272-](#)  
[SM-020-P-TR](#) [TW-230-07-T-T-480-120](#) [TW-6-12-G-D-787-161](#) [TW-02-03-T-D-285-SM-001](#) [TW-02-03-T-D-285-SM-](#)  
[001-TR](#) [TW-12-03-F-D-190-SM-001](#) [TW-12-03-L-D-260-SM-100](#) [TW-02-04-S-D-310-SM-A](#) [TW-10-02-SM-D-SM-K-TR](#)  
[TW-106-02-G-D-142-110](#) [TW-120-06-L-D-395-080](#) [TW-10-02-SM-D-170-P-TR](#) [TW-19-07-L-D-SM-P-TR](#) [TW-10-04-](#)  
[L-D-275-SM-001](#) [TW-12-04-L-S-170-SM-002](#) [TW-12-04-L-S-250-SM-002](#) [TW-13-02-T-D-SM-500](#) [TW-17-03-T-D-290-](#)  
[SM-027](#) [TW-13-06-G-D-SM-335-TR](#) [TW-12-03-S-S-320-SM-001](#) [TW-13-03-L-S-330-SM-001-P-TR](#) [TW-13-06-S-D-](#)  
[450-SM-007-P-TR](#) [TW-13-06-T-D-450-SM-007](#) [TW-13-06-T-D-450-SM-007-P](#) [TW-29-02-G-D-170-SM-058](#) [TW-08-02-](#)  
[S-D-170-SM-002](#) [TW-10-04-L-S-240-SM-005](#) [TW-10-07-S-D-600-SM-003](#) [TW-11-03-G-D-268-SM-001](#) [TW-11-04-G-](#)  
[D-300-SM-013-M](#) [TW-11-06-G-D-480-SM-013](#) [TW-08-02-L-D-190-SM-A-P](#) [TW-03-02-T-S-200-088](#) [TW-02-07-L-D-](#)  
[472-SM](#) [TW-04-03-F-D-250-SM](#) [TW-10-07-L-D-450-SM](#) [TW-15-07-T-D-487-SM-A](#) [TW-05-07-T-D-520-SM-A](#) [TW-20-](#)  
[09-G-D-236-SM-A](#) [TW-10-03-L-D-330-SM-A-P-TR](#) [TW-20-03-F-D-305-SM-P-TR](#) [TW-13-09-L-D-315-SM](#) [TW-06-04-L-](#)  
[D-360-SM](#) [TW-12-03-F-D-325-SM-P](#) [TW-02-06-L-D-295-SM](#) [TW-10-03-L-D-170-SM-TR](#) [TW-13-09-L-D-190-SM-A-P-](#)  
[TR](#) [TW-07-03-G-D-300-SM-A](#) [TW-03-02-F-D-170-SM-TR](#) [TW-07-06-S-D-375-SM-A](#)