

DO NOT
SCALE FROM
THIS PRINT

DESIGNED & DIMENSIONED
IN INCHES[MILLIMETERS]

PRF35-J-C-EP-402-SS

SERIES
-35: 3.5MM

GENDER
-J: JACK





TYPE
-C: CABLE

TERMINATION
-S: SOLDER CLAMP

ORIENTATION
-S: STRAIGHT

CABLE TYPE
-402: RG-402 SEMI-RIGID

FINISH
-EP: 50µ" EXTRA HEAVY GOLD
CENTER CONTACT,
PASSIVATED OUTER CONTACT





EXPLODED VIEW
NOT TO SCALE
(FOR CLARITY ONLY)

NOTES:

1. MATERIAL:
BODY, BUSHING: STAINLESS STEEL
CONTACT: BERYLLIUM COPPER
CLAMP NUT: BRASS ALLOY
BEAD: PCTFE
2. FINISH:
BODY, BUSHING: PASSIVATED
CLAMP NUT, CONTACT: 50µ" MIN. GOLD OVER 50µ" MIN. NICKEL PLATE
3. PCI P/N: 3887


F:\DWG\MISC\MKTG\PRF35-J-C-EP-402-SS-MKT.SLDDRW

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE: DECIMALS ANGLES .XX: ±.01 [0.3] 1 ° .XXX: ±.005 [0.13] .XXXX: ±.0005 [0.013]	<div>PROPRIETARY NOTE</div> <div>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</div>	<div></div> <div>520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322</div>	
		DO NOT SCALE DRAWING SHEET SCALE: 3.5:1	
		DESCRIPTION: 3.5MM JACK SOLDER CLAMP NUT FOR RG-402 CABLE	
		DWG. NO. PRF35-J-C-EP-402-SS	
BY: CANDY W 4/13/2019		SHEET 1 OF 2	




IN-PROCESS VIEW 1

1. TRIM CABLE JACKET TO EXPOSE DIELECTRIC CORE AS SHOWN.



IN-PROCESS VIEW 2

2A. SOLDER CLAMP NUT TO CABLE AS SHOWN.
 2B. TRIM CABLE DIELECTRIC FLUSH WITH FACE OF CLAMP NUT AS SHOWN.
 2C. POINT CABLE CENTER CONDUCTOR AS SHOWN.



DISTANCE FROM END OF CABLE CENTER COND. TO REF. PL. IS .370 (REF.)

3A. INSERT CABLE SUB-ASSEMBLY INTO CONNECTOR UNTIL SEATED AND TORQUE TO 25-30 IN. LBS.
 3B. GAGE CONTACT RECESSON FROM CONNECTOR INTERFACE. (.000/.0033 SUB-FLUSH).

IN-PROCESS VIEW 3

• PROPRIETARY NOTE •
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3.5:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
 PHONE: 812-944-6733 FAX: 812-948-5047
 e-Mail info@SAMTEC.com code 55322

DESCRIPTION: 3.5MM JACK SOLDER CLAMP NUT FOR RG-402 CABLE

DWG. NO. PRF35-J-C-EP-402-SS

BY: CANDY W 4/13/2019 SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[PRF35-J-C-EP-402-SS](#)