

(2.00 mm) .0787"

TW-20-03-L-Q-400-085

TW-08-09-F-T-165-100

TW-16-06-T-D-500-100

TW SERIES

THROUGH-HOLE BOARD STACKERS

SPECIFICATIONS

For complete specifications see www.samtec.com?TW-TH

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over

50 μ " (1.27 μ m) Ni

Current Rating:

5.2 A per pin

(2 pins powered)

Operating Temp Range:

-55 °C to +105 °C with Tin;

-55 °C to +125 °C with Gold

RoHS Compliant:

Yes

Lead-Free Solderable:

Yes


Board Mates:

CLT, SQT, SQW, ESQT,
TLE, SMM, MMS

Cable Mates:

TCSD

OTHER SOLUTIONS



Paste In Hole (PIH) processing.
Contact Samtec ASP Group.

ALSO AVAILABLE (MOQ Required)

- Other platings

Specify stacker height in (0.13 mm) .005" increments

(2.00 mm) .0787 pitch

Choice of one through six rows

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.

Other Solutions


2 mm Shunt

See 2SN Series.




Surface Mount

See previous page.



Low Profile

See TMM Series.




Right-angle

See TMM Series.



Shrouded Double Row

See ZLTMM Series.



TW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	TAIL SPEC
02 thru 50	Specify LEAD STYLE from chart below.	<p>—F = Gold flash on post, Matte Tin on tail</p> <p>—L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail</p> <p>—T = Matte Tin</p>	<p>—S = Single Row</p> <p>—D = Double Row</p> <p>—T = Triple Row</p> <p>—Q = Four Row</p> <p>—5 = Five Row</p> <p>—6 = Six Row</p>	<p>—"XXX" = Stacker Height in inches (0.13 mm) .005" increments</p> <p>Example: -250 = (6.35 mm) .250"</p>	<p>—"XXX" = Tail Length in inches (0.13 mm) .005" increments</p> <p>Example: -150 = (3.81 mm) .150"</p> <p>—"XXX" = Polarized Position (Specify position to be removed)</p>	

04
01
(2.00) .0787 TYP
-S, -D*, -Q
300
No. of rows x (2.00) .0787
295
-T, -5, -6

(0.51) .020 SQ
POST
TAIL
(0.00) .000 MIN
(2.00) .0787
(1.27) .050 MIN
STACKER HEIGHT See Chart
OAL

LEAD STYLE	OAL
-01	(8.20) .323
-02	(9.60) .377
-03	(13.60) .535
-04	(14.10) .555
-05	(15.10) .594
-06	(17.10) .673
-07	(19.10) .751
-08	(21.10) .830
-09	(11.60) .456
-10	(15.60) .614
-11	(10.08) .397
-12	(28.19) 1.110

ROW OPTION	STACKER HEIGHT
-S, -D*, & -Q	(3.05) .120 MIN
-T, -5, -6	(4.06) .160 MIN

* Style -08 & -12 = S & D only

* -D with stacker height greater than (4.06 mm) .160" will not have standoffs.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[TW-02-06-G-D-395-120](#) [TW-02-01-L-S-130-090](#) [TW-02-06-S-D-500-050](#) [TW-01-01-T-S-120-101](#) [TW-02-01-L-D-120-095](#) [TW-02-01-T-S-120-100](#) [TW-02-06-G-D-472-100](#) [TW-50-12-L-D-755-210](#) [TW-01-02-T-S-210-085](#) [TW-02-01-T-S-120-101](#) [TW-02-01-L-S-120-150](#) [TW-02-06-S-S-500-050](#) [TW-02-06-G-S-375-080](#) [TW-02-01-L-S-147-125](#)