


FLAT FLEXIBLE CABLE (FCC) JUMPER & SOCKET

(1.00 mm) .0394" PITCH • FJ/ZF1/FC1 SERIES



FJ

Mates:
FC1, ZF1

ZF1/FC1

Mates:
FJ

SPECIFICATIONS

FJ



Conductor:
Tin Plated Copper
Conductor Resistance:
300 Ω/km max
Insulation Resistance:
10 MΩ/km min
(conductor-to-conductor)
Dielectric Test:
400 VAC during 1 minute
(conductor-to-conductor)
Temperature Rating:
-30 °C to +80 °C
Voltage Rating:
300 VAC

ZF1

Insulator Material:
Liquid Crystal Polymer
Contact Material:
Phosphor Bronze
Plating:
Sn over 40 μ" (1.02 μm) Ni
Weld Tab: Phosphor Bronze
Operating Temp Range:
-55 °C to +105 °C

FC1

Insulator Material:
Liquid Crystal Polymer
Contact Material:
Phosphor Bronze
Plating:
Sn over 50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +105 °C
Max Cycles:
25 with FJ




PROCESSING

ZF1/FC1

Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.10 mm) .004" max

Notes:
FJ Stiffener color will be blue or black at Samtec's discretion.

Some sizes, styles and options are non-standard, non-returnable.



samtec.com?FJ, samtec.com?ZF1 or samtec.com?FC1

F-221

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[ZF1-04-01-T-WT-TR](#) [ZF1-15-02-T-WT-TR](#) [ZF1-22-02-T-WT](#) [ZF1-24-01-T-WT](#) [ZF1-06-02-T-WT](#) [ZF1-22-01-T-WT](#)
[ZF1-06-01-T-WT](#) [ZF1-18-01-T-WT](#) [ZF1-20-02-T-WT](#) [ZF1-30-02-T-WT](#) [ZF1-09-01-T-WT](#) [ZF1-25-02-T-WT](#) [ZF1-06-01-T-WT-TR](#) [ZF1-05-02-T-WT](#) [ZF1-18-02-T-WT](#) [ZF1-06-02-T-WT-TR](#) [ZF1-11-01-T-WT](#) [ZF1-13-01-T-WT-TR](#) [ZF1-18-01-T-WT-TR](#) [ZF1-20-01-TM-WT](#) [ZF1-24-01-T-WT-TR](#) [ZF1-30-01-TM-WT](#) [ZF1-05-02-T-WT-TR](#) [ZF1-07-01-T-WT](#) [ZF1-16-02-TM-WT](#) [ZF1-16-02-T-WT-TR](#) [ZF1-25-02-T-WT-TR](#) [ZF1-22-02-T-WT-TR](#) [ZF1-28-01-T-WT](#) [ZF1-04-01-T-WT](#) [ZF1-04-02-TM-WT-TR](#) [ZF1-08-02-T-WT](#) [ZF1-10-01-TM-WT](#) [ZF1-15-02-TM-WT-TR](#) [ZF1-20-02-T-WT-TR](#) [ZF1-22-01-T-WT-TR](#) [ZF1-06-01-TM-WT-TR](#) [ZF1-07-02-TM-WT](#) [ZF1-11-02-T-WT-TR](#) [ZF1-12-02-T-WT-TR](#) [ZF1-17-01-T-WT](#) [ZF1-25-01-TM-WT](#) [ZF1-25-02-TM-WT-TR](#) [ZF1-26-01-T-WT](#) [ZF1-04-02-T-WT](#) [ZF1-14-02-T-WT](#) [ZF1-15-01-TM-WT](#) [ZF1-07-02-T-WT](#) [ZF1-08-01-T-WT-TR](#) [ZF1-14-01-T-WT](#) [ZF1-24-02-T-WT-TR](#) [ZF1-26-02-T-WT](#) [ZF1-11-02-T-WT](#)
[ZF1-24-02-T-WT](#) [ZF1-05-01-TM-WT-TR](#) [ZF1-08-02-TM-WT](#) [ZF1-10-02-TM-WT-TR](#) [ZF1-16-01-T-WT-TR](#) [ZF1-17-02-T-WT](#) [ZF1-18-02-T-WT-TR](#) [ZF1-30-01-TM-WT-TR](#) [ZF1-04-02-TM-WT](#) [ZF1-08-02-T-WT-TR](#) [ZF1-09-01-T-WT-TR](#) [ZF1-20-02-TM-WT](#) [ZF1-21-01-T-WT](#) [ZF1-04-02-T-WT-TR](#) [ZF1-08-01-TM-WT-TR](#) [ZF1-10-01-TM-WT-TR](#) [ZF1-13-01-T-WT](#) [ZF1-14-01-TM-WT](#) [ZF1-16-01-TM-WT-TR](#) [ZF1-12-01-T-WT-TR](#) [ZF1-12-02-T-WT](#) [ZF1-16-02-T-WT](#) [ZF1-20-01-TM-WT-TR](#) [ZF1-04-01-TM-WT-TR](#) [ZF1-05-01-TM-WT](#) [ZF1-10-02-TM-WT](#) [ZF1-16-01-TM-WT](#) [ZF1-12-01-TM-WT](#) [ZF1-08-02-TM-WT-TR](#) [ZF1-09-02-TM-WT](#) [ZF1-23-01-TM-WT](#) [ZF1-09-02-TM-WT-TR](#) [ZF1-11-02-TM-WT](#) [ZF1-27-01-TM-WT-TR](#) [ZF1-04-01-TM-WT](#) [ZF1-07-02-TM-WT-TR](#) [ZF1-05-02-TM-WT](#) [ZF1-15-01-TM-WT-TR](#) [ZF1-15-02-TM-WT](#) [ZF1-17-02-TM-WT](#) [ZF1-12-01-TM-WT-TR](#) [ZF1-06-01-TM-WT](#) [ZF1-17-01-TM-WT](#) [ZF1-09-01-TM-WT](#) [ZF1-13-02-TM-WT](#) [ZF1-13-02-TM-WT-TR](#) [ZF1-18-01-TM-WT](#)