


# SHROUDED HEADER & STACKER

(2.00 mm) .0787" PITCH • LTMM/ZLTMM SERIES



## LTMM/ZLTMM

### Mates:

SQT, SQW, ESQT, SMM

### SPECIFICATIONS

#### Insulator Material:

Black Liquid Crystal Polymer

#### Terminal Material:

Phosphor Bronze

#### Plating:

Sn or Au over

50  $\mu$ " (1.27  $\mu$ m) Ni

#### Operating Temp Range:

-55 °C to +105 °C with Tin;

-55 °C to +125 °C with Gold

### PROCESSING

#### Lead-Free Solderable:

Yes

#### SMT Lead Coplanarity:

(0.10 mm) .004" max

| LTMM | 1 | NO. PINS PER ROW                                                                   | 02 | PLATING OPTION                                                                                                                                              | D | TAIL OPTION                                                                               | OTHER OPTION                                                                                                                                                                                                                                                                                                                                                                                 |
|------|---|------------------------------------------------------------------------------------|----|-------------------------------------------------------------------------------------------------------------------------------------------------------------|---|-------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|      |   | 04, 05,<br>06, 07,<br>08, 10, 12,<br>13, 15, 17,<br>20, 22, 25<br>(Standard sizes) |    | -F<br>= Gold flash<br>on post,<br>Matte Tin on tail<br><br>-L<br>= 10 $\mu$ " (0.25 $\mu$ m)<br>Gold on post,<br>Matte Tin on tail<br><br>-T<br>= Matte Tin |   | Leave blank for<br>Through-hole<br><br>-RA<br>= Right-angle<br><br>-SM<br>= Surface Mount | - "XX"<br>= Polarized<br>Position<br><br>-LC<br>= Locking Clip<br>(-SM only)<br>(Manual<br>placement<br>required)<br><br>-K<br>= (7.50 mm)<br>.295" DIA Film<br>Pick &<br>Place Pad<br>(-SM only)<br><br>-TR<br>= Tape & Reel<br>(-SM only)<br><br>-FR<br>= Full Reel<br>Tape & Reel<br>(must order<br>max. quantity<br>per reel;<br>contact Samtec<br>for quantity<br>breaks)<br>(-SM only) |

| ZLTMM | 1 | NO. PINS PER ROW                                                                   | LEAD STYLE                                | PLATING OPTION                                                                                                                                              | D | BODY HEIGHT                 | OTHER OPTION                      |
|-------|---|------------------------------------------------------------------------------------|-------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|---|-----------------------------|-----------------------------------|
|       |   | 04, 05,<br>06, 07,<br>08, 10, 12,<br>13, 15, 17,<br>20, 22, 25<br>(Standard sizes) | Specify<br>LEAD<br>STYLE<br>from<br>chart | -F<br>= Gold flash<br>on post,<br>Matte Tin on tail<br><br>-L<br>= 10 $\mu$ " (0.25 $\mu$ m)<br>Gold on post,<br>Matte Tin on tail<br><br>-T<br>= Matte Tin |   | - "XXX"<br>= Body<br>Height | - "XX"<br>= Polarized<br>Position |

| LEAD STYLE | B (OAL)       | MAX BODY HEIGHT |
|------------|---------------|-----------------|
| -75        | (9.58) 0.377  | (7.42) 0.292    |
| -62        | (10.08) 0.397 | (7.92) 0.312    |
| -65        | (10.49) 0.413 | (8.33) 0.328    |
| -73        | (12.09) 0.476 | (9.93) 0.391    |
| -63        | (14.10) 0.555 | (11.94) 0.470   |
| -66        | (15.09) 0.594 | (12.93) 0.509   |
| -69        | (15.60) 0.614 | (13.44) 0.529   |
| -74        | (17.09) 0.673 | (14.94) 0.588   |
| -70        | (17.60) 0.693 | (15.44) 0.608   |
| -71        | (21.08) 0.830 | (18.92) 0.745   |
| -72        | (21.62) 0.851 | (19.46) 0.766   |

### Note:

This Series is non-standard, non-returnable.

### Note:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ZLTMM-112-63-G-D-420](#) [ZLTMM-113-69-G-D-470](#) [ZLTMM-125-69-G-D-470](#) [ZLTMM-113-75-G-D-250](#) [ZLTMM-125-75-G-D-250](#) [ZLTMM-117-03-T-D-440](#) [ZLTMM-125-73-L-D-389](#) [ZLTMM-117-72-L-D-573](#) [ZLTMM-120-72-G-D-766-10](#) [ZLTMM-120-75-L-D-250](#) [ZLTMM-123-73-L-D-353](#) [ZLTMM-125-62-L-D-250](#) [ZLTMM-115-70-G-D-608](#) [ZLTMM-115-73-G-D-370](#) [ZLTMM-117-63-S-D-470](#) [ZLTMM-117-69-G-D-512](#) [ZLTMM-120-71-G-D-620](#) [ZLTMM-122-71-G-D-662](#) [ZLTMM-122-70-S-D-608](#) [ZLTMM-125-71-L-D-690](#) [ZLTMM-125-74-S-D-533](#) [ZLTMM-125-75-G-D-272](#) [ZLTMM-103-70-L-D-581](#) [ZLTMM-105-70-G-D-579](#) [ZLTMM-105-70-L-D-600](#) [ZLTMM-106-73-G-D-360](#) [ZLTMM-106-73-L-D-375](#) [ZLTMM-109-69-G-D-484](#) [ZLTMM-110-70-G-D-576](#) [ZLTMM-110-75-L-D-250](#) [ZLTMM-113-72-S-D-765](#) [ZLTMM-120-70-L-D-608](#) [ZLTMM-120-71-L-D-690](#) [ZLTMM-122-63-L-D-400](#) [ZLTMM-122-69-G-D-512](#) [ZLTMM-125-66-S-D-484](#) [ZLTMM-125-69-G-D-525](#) [ZLTMM-125-73-S-D-330-36](#) [ZLTMM-115-66-S-D-483](#) [ZLTMM-117-69-G-D-445](#) [ZLTMM-120-69-G-D-512](#) [ZLTMM-120-71-G-D-642](#) [ZLTMM-122-69-G-D-506](#) [ZLTMM-125-66-G-D-480](#) [ZLTMM-125-69-S-D-529](#) [ZLTMM-115-70-S-D-550](#) [ZLTMM-105-63-L-D-450](#) [ZLTMM-105-73-F-D-313](#) [ZLTMM-105-73-L-D-315](#) [ZLTMM-107-62-L-D-250](#) [ZLTMM-108-73-F-D-313](#) [ZLTMM-109-73-L-D-328](#) [ZLTMM-110-63-F-D-375](#) [ZLTMM-110-63-F-D-470](#) [ZLTMM-110-74-F-D-501](#) [ZLTMM-110-74-L-D-550](#) [ZLTMM-113-66-L-D-504](#) [ZLTMM-115-63-L-D-429](#) [ZLTMM-115-65-F-D-323](#) [ZLTMM-115-73-G-D-380](#) [ZLTMM-115-73-L-D-382](#) [ZLTMM-117-71-F-D-625](#) [ZLTMM-120-74-L-D-575](#) [ZLTMM-105-66-F-D-505](#) [ZLTMM-105-66-F-D-509](#) [ZLTMM-105-66-L-D-460](#) [ZLTMM-105-74-G-D-259](#) [ZLTMM-106-63-L-D-415](#) [ZLTMM-107-71-F-D-551](#) [ZLTMM-107-72-L-D-766](#) [ZLTMM-108-73-L-D-320](#) [ZLTMM-108-73-L-D-382](#) [ZLTMM-108-74-L-D-535](#) [ZLTMM-110-73-S-D-352](#) [ZLTMM-112-66-H-D-495](#) [ZLTMM-112-74-F-D-575](#) [ZLTMM-115-62-L-D-295](#) [ZLTMM-115-63-F-D-402](#) [ZLTMM-104-63-F-D-466](#) [ZLTMM-104-71-F-D-625](#) [ZLTMM-105-66-G-D-430](#) [ZLTMM-106-63-L-D-312](#) [ZLTMM-107-73-L-D-391](#) [ZLTMM-110-63-S-D-465](#) [ZLTMM-110-73-L-D-345](#) [ZLTMM-112-69-L-D-350](#) [ZLTMM-113-75-F-D-250](#) [ZLTMM-120-63-F-D-330](#) [ZLTMM-125-63-L-D-420](#) [ZLTMM-105-63-L-D-425](#) [ZLTMM-105-70-G-D-576](#) [ZLTMM-105-71-F-D-630](#) [ZLTMM-104-73-S-D-364](#) [ZLTMM-104-75-L-D-254](#) [ZLTMM-105-66-F-D-487](#) [ZLTMM-105-69-G-D-470](#) [ZLTMM-108-02-L-D-285](#) [ZLTMM-108-63-F-D-375](#) [ZLTMM-108-72-F-D-766](#) [ZLTMM-110-66-F-D-505](#)