


SHROUDED HEADERS & STACKERS

(1.27 mm) .050" PITCH • TML/ZML SERIES



TML/ZML

Mates:

SMS, RSM

SPECIFICATIONS

TML

Insulator Material:
Black Liquid Crystal Polymer

Insulation Resistance:

5000 MΩ min

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin;

-55 °C to +125 °C with Gold

ZML

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin;

-55 °C to +125 °C with Gold

PROCESSING

TML

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (05-20)

(0.15 mm) .006" max (32)*

*(.004" stencil solution

may be available; contact

IPG@samtec.com)

ZML

Same as TML except:

SMT Lead Coplanarity:

(0.15 mm) .006" max*

*(.004" stencil solution

may be available; contact

ipg@samtec.com)

ALSO AVAILABLE

MOQ Required

Other sizes

Other platings

Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Some sizes, styles and options are non-standard, non-returnable.

TML	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	D	-	TAIL OPTION	-	OTHER OPTION
-----	---	---	------------------	---	------------	---	----------------	---	---	---	-------------	---	--------------

05, 08,
10, 20, 32
(Standard sizes)

Specify
LEAD
STYLE
from
chart

-L
= 10 μ"
(0.25 μm)
Gold on post,
Matte Tin
on tail


-G
= 10 μ"
(0.25 μm)
Gold on post,
Gold flash
on tail

(Leave blank for
Through-hole)

-RA
= Right-angle

-SM
= Surface Mount
(For locking clip
add -LC)

-“XXX”
= Polarized
position
(Specify position
of omitted pin)



RIGHT-ANGLE

ZML	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	D	-	BODY HEIGHT	-	TAIL OPTION
-----	---	---	------------------	---	------------	---	----------------	---	---	---	-------------	---	-------------

05, 08,
10, 20, 32
(Standard sizes)

Specify
LEAD
STYLE
from
chart

-L
= 10 μ"
(0.25 μm)
Gold on post,
Matte Tin
on tail


-G
= 10 μ"
(0.25 μm)
Gold on post,
Gold flash
on tail

(Leave blank for
Through-hole)

-“XXX”
= -SM Body Height
(Specify board space
“B” in inches from
lead style charts.)

(Leave blank for
Through-hole)

-SM
= Surface
Mount



THROUGH-HOLE

LEAD STYLE	BODY HEIGHT (C)
-01	(12.83) .505
-02	(14.22) .560
-03	(16.64) .655
-04	(19.69) .775

SURFACE MOUNT

LEAD STYLE	POST HEIGHT (A)	BODY HEIGHT (B)
-53	(3.05) .120	(13.46) .530 to (20.19) .795
-54	(5.84) .230	(13.46) .530 to (17.40) .685

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ZML-108-01-L-D](#) [ZML-110-54-S-D-685-SM](#) [ZML-125-53-S-D-787-SM](#) [ZML-108-03-L-D](#) [ZML-125-54-S-D-760-SM](#)
[ZML-132-04-L-D](#) [ZML-120-54-G-D-685-SM](#) [ZML-120-54-L-D-560-SM](#) [ZML-108-54-G-D-650-SM](#) [ZML-110-01-L-D](#)
[ZML-110-03-L-D](#) [ZML-136-03-L-D](#) [ZML-105-54-L-D-600-SM](#) [ZML-120-04-L-D](#) [ZML-111-04-S-D](#) [ZML-113-54-S-D-](#)
[685-SM](#) [ZML-115-54-G-D-700-SM](#) [ZML-118-54-G-D-530-SM](#) [ZML-107-54-S-D-685-SM](#) [ZML-136-53-G-D-750-SM](#)
[ZML-110-02-L-D](#) [ZML-110-04-L-D](#) [ZML-135-01-L-D](#) [ZML-140-02-L-D](#) [ZML-140-54-S-D-685-SM](#) [ZML-110-54-S-D-](#)
[620-SM](#) [ZML-105-53-G-D-530-SM](#) [ZML-136-04-G-D](#) [ZML-105-03-L-D](#) [ZML-105-54-S-D-685-SM](#) [ZML-130-54-G-D-](#)
[551-SM](#) [ZML-115-54-G-D-537-SM](#) [ZML-115-01-L-D](#) [ZML-130-04-L-D](#) [ZML-110-54-L-D-650-SM](#) [ZML-132-54-L-D-](#)
[570-SM](#) [ZML-108-54-L-D-665-SM](#) [ZML-112-54-L-D-570-SM](#) [ZML-108-54-G-D-615-SM](#) [ZML-110-54-G-D-795-SM](#)
[ZML-108-54-G-D-670-SM](#) [ZML-106-03-L-D](#) [ZML-115-54-G-D-530-SM](#) [ZML-113-54-G-D-685-SM](#) [ZML-120-54-L-D-](#)
[685-SM](#) [ZML-105-54-G-D-670-SM](#) [ZML-117-54-G-D-615-SM](#) [ZML-117-54-L-D-680-SM](#) [ZML-105-54-S-D-610-SM](#)
[ZML-107-03-S-D](#) [ZML-108-01-G-D](#) [ZML-110-02-G-D](#) [ZML-114-01-G-D](#) [ZML-115-02-S-D](#) [ZML-115-54-S-D-530-SM](#)
[ZML-130-54-T-D-795-SM](#) [ZML-132-02-S-D](#) [ZML-136-54-S-D-685-SM](#) [ZML-136-54-T-D-685-SM](#) [ZML-140-01-G-D](#)
[ZML-140-54-T-D-685-SM](#) [ZML-108-02-S-D](#) [ZML-110-01-S-D](#) [ZML-110-53-S-D-795-SM](#) [ZML-115-54-S-D-685-SM](#)
[ZML-120-04-G-D](#) [ZML-130-03-G-D](#) [ZML-130-54-S-D-795-SM](#) [ZML-132-54-G-D-530-SM](#) [ZML-136-54-S-D-560-SM](#)
[ZML-140-03-G-D](#) [ZML-140-53-S-D-795-SM](#) [ZML-136-54-S-D-550-SM](#) [ZML-140-01-S-D](#) [ZML-140-54-S-D-550-SM](#)
[ZML-120-54-S-D-685-SM](#) [ZML-124-04-G-D](#) [ZML-125-03-S-D](#) [ZML-136-54-S-D-590-SM](#) [ZML-140-02-S-D](#) [ZML-140-](#)
[54-G-D-530-SM](#) [ZML-130-02-G-D](#) [ZML-130-02-S-D](#) [ZML-136-02-G-D](#) [ZML-140-02-G-D](#) [ZML-108-54-G-D-530-SM](#)
[ZML-110-54-S-D-625-SM](#) [ZML-110-54-S-D-635-SM](#) [ZML-117-03-G-D](#) [ZML-117-03-S-D](#) [ZML-120-54-G-D-530-SM](#)
[ZML-125-53-S-D-795-SM](#) [ZML-136-54-G-D-650-SM](#) [ZML-140-04-S-D](#) [ZML-140-53-S-D-530-SM](#) [ZML-124-02-G-D](#)
[ZML-125-04-G-D](#) [ZML-125-54-S-D-530-SM](#) [ZML-130-04-G-D](#) [ZML-136-54-S-D-540-SM](#)