




IPS1-1XX-XX-XX-D-VS-XX-XX

No OF POS PER ROW
-02 THRU -25

LEAD STYLE
-01

PLATING SPECIFICATION
-S: SELECTIVE GOLD, MATTE TIN TAIL (USE C-17-02-S)
-SM: SELECTIVE GOLD, MATTE TIN TAIL (USE C-17-02-S)
-L: LIGHT SELECTIVE GOLD, MATTE TIN TAIL (USE C-17-02-L)

ROW SPECIFICATION
-D: DOUBLE (USE IPS1-XX-D)

OPTION


-PL: POSITION #1 REMOVED (USE IPS1-XX-D-P) (SEE NOTE 11)
-K: POLYIMIDE FILM PAD [4 POS MIN] (USE K-DOT-217-.313-.005)
-TR: TAPE & REEL PACKAGING

OPTION



-LC: LOCKING CLIP (USE LC-07-TM) (SEE NOTE 10)
-FL: FRICTION LOCK (USE IPS1-XX-D-FL-X) [POSITIONS -05 THRU -25]

TAIL OPTION

-VS: VERTICAL SURFACE MOUNT



DO NOT
SCALE FROM
THIS PRINT



NOTES:

SECTION "A"- "A"

1. $\odot$ REPRESENTS A CRITICAL DIMENSION.
2. MAXIMUM ALLOWABLE CUT FLASH: $.010 [.25]$.
3. MINIMUM CONTACT PUSH OUT FORCE: 1.5 lbs.
4. MAXIMUM ALLOWABLE BOW: $.003 [.08]$ INCH/INCH AFTER ASSEMBLY.
5. MAXIMUM VARIATION BETWEEN PIN ROWS: $.010 [.25]$.
6. SHEAR TAILS TO ACHIEVE DIMENSION SHOWN.
7. SHEAR BURR ALLOWED ON TOP SIDE (MOLD SIDE) TO $.005 [.13]$ MAX.
8. "END WALLS" AFTER CUTTING SHOULD BE $.015 \pm .003 [.38 \pm .08]$.
9. AFTER REVISION N OF COMPONENT IPS1-XX-D-XX-X, SAMTEC LOGO TO APPEAR ON #1 POSITION.
10. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
11. FOR EXISTING CUSTOMERS ONLY, -POL CAN BE SUBSTITUTED FOR -PL.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: $\pm .01 [.3]$ $\pm 2^\circ$
.XXX: $\pm .005 [.13]$
.XXXX: $\pm .0020 [.051]$

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322


MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2.5:1
INSULATOR: VECTRA E130i, COLOR: BLACK
CONTACT: PHOS BRONZE, 510 SPRING TEMPER

DESCRIPTION:
.100 DOUBLE ROW SHROUDED SOCKET ASSEMBLY

DWG. NO.
IPS1-1XX-XX-XX-D-VS-XX-XX

BY: DEAN P 10-30-2002 SHEET 1 OF 2

PACKAGING VIEW




TUBE: ASP-90528-01-S
PLUG: TP-03


TABLE 1

POSITION	COPLANARITY
-04 THRU -10	.005 [.13]
-11 THRU -25	.006 [.15]


INPROCESS




-FL: FRICTION LOCK OPTION
IPS1-110-01-X-D-VS-FL SHOWN



-PL: POLARIZED OPTION
IPS1-110-01-X-D-VS-PL SHOWN




-K: POLYAMIDE FILM PAD OPTION



NOTE: "R" = USE MEASURED DIMENSION
"S" = $((\text{"R"} - .2165[5.499]) / 2) \pm .020[.51]$

-LC: LOCKING CLIP OPTION
IPS1-110-01-X-D-VS-LC-FL SHOWN



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
.100 DOUBLE ROW SHROUDED SOCKET ASSEMBLY

DWG. NO.
IPS1-1XX-XX-XX-D-VS-XX-XX

BY: DEAN P 10-30-2002 SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[IPS1-125-01-L-D-VS-PL](#) [IPS1-125-01-S-D-VS-LC-PL](#)