


MTMM-108-07-F-D-350



(2.00 mm) .0787"

MTMM SERIES

# MODIFIED THROUGH-HOLE HEADER

## SPECIFICATIONS

For complete specifications see [www.samtec.com?MTMM](http://www.samtec.com?MTMM)

**Insulator Material:** Black Liquid Crystal Polymer

**Terminal Material:** Phosphor Bronze

**Plating:** Sn or Au over 50 μm (1.27 μm) Ni

**Operating Temp Range:** -55 °C to +105 °C with Tin; -55 °C to +125 °C with Gold

**RoHS Compliant:** Yes

**Lead-Free Solderable:** Yes

**Lead-Free Solderable:** Yes


**Board Mates:**

CLT, SQT, SQW, ESQT, TLE, SMM, MMS

**Cable Mates:**


TCSD

Choice of single, double or quad row



Specify post height in (0.13 mm) .005" increments

(2.00 mm) .0787" pitch



## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)



FILE NO. E111594

## ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.



01 thru 50


Specify LEAD STYLE from chart.

- F = Gold flash on post, Matte Tin on tail
- L = 10 μm (0.25 μm) Gold post, Matte Tin on tail
- T = Matte Tin

- S = Single Row
- D = Double Row
- Q = Quad Row

- "XXX" = Post Height in inches (0.13 mm) .005" increments  
Example: -070 = (1.78 mm) .070"

- "XXX" = Polarized Position Specify position of omitted pin



LEAD STYLE	OAL
-02	(6.48) .255
-03	(7.67) .302
-04	(8.20) .323
-05	(9.58) .377
-06	(10.08) .397
-07	(11.58) .456
-08	(12.09) .476
-09	(13.59) .535
-10	(14.10) .555
-11	(15.09) .594
-12	(15.60) .614
-13	(17.09) .673
-14	(19.08) .751
-15	(21.08) .830

**Note:** This Series is non-standard, non-returnable.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Samtec:

[MTMM-106-14-T-D-350](#) [MTMM-105-12-T-D-070](#) [MTMM-102-02-L-S-070](#) [MTMM-103-03-T-Q-070](#) [MTMM-105-05-L-D-070](#) [MTMM-106-04-T-D-070](#) [MTMM-106-07-F-D-350](#) [MTMM-106-10-F-S-350](#) [MTMM-106-10-L-S-070](#) [MTMM-108-06-L-S-235](#) [MTMM-110-15-T-S-070](#) [MTMM-112-02-T-S-070](#) [MTMM-103-06-L-D-235](#) [MTMM-150-02-F-S-070](#)