

DO NOT
SCALE FROM
THIS PRINT





FIG 1
-S: SINGLE END
SFSD-10-28-XX-XX.XX-S SHOWN



ASSEMBLED LENGTH:
(SEE NOTE 8)

SECTION "A"- "A"

DWCX-XX-XX-300

POLARIZATION KEY

SFSDX-XX-XXX-XX-XX.XX-XX-XXX

FEP CABLE OPTION
-T: FEP (LEAVE BLANK FOR
STANDARD PVC INSULATION)

No OF POSITIONS
-02 THRU -50
(PER ROW)

WIRE GAUGE (AWG)
-28, -30

COLOR CODE:

LEAVE BLANK FOR ALL BLACK WIRE
C: COLOR CODED WIRE
(SEE TABLE 4, SHT 3)
(NOT AVAILABLE WITH FEP OPTION)

PLATING SPECIFICATION

-H: 30μ" HEAVY GOLD IN CONTACT AREA,
3μ" GOLD ON TAIL
-G: 10μ" LIGHT GOLD IN CONTACT AREA,
3μ" GOLD ON TAIL
-F: 3μ" FLASH GOLD IN CONTACT AREA,
3μ" GOLD ON TAIL
-GF: 3μ" FLASH SELECTIVE IN CONTACT AREA,
3μ" GOLD ON TAIL
(ONLY AVAILABLE TO EXISTING
CUSTOMERS; SEE -F PLATING)
(SEE TABLE 3, SHEET 1)

ASSEMBLED LENGTH

SPECIFY IN INCHES
(SINGLE END: 03.00 INCH [76.2mm]
MINIMUM,
DOUBLE END: 03.25 INCH [82.6mm]
MINIMUM)

-NXX OPTION (END 2)
(ONLY AVAILABLE WITH -D, -DL, -DR & -DS)
-NUS: NOTCH UP, STRAIGHT
(PIN 1 TO PIN N-1)
-NDS: NOTCH DOWN, STRAIGHT
(PIN 1 TO PIN 2)
-NUX: NOTCH UP, CROSSED
(PIN 1 TO PIN N)
-NDX: NOTCH DOWN, CROSSED
(PIN 1 TO PIN 1)

END OPTION
(END OPTION COMBINATIONS NOT AVAILABLE)

-S: SINGLE END
-D: DOUBLE END
(MUST CHOOSE FROM -NXX OPTIONS)
-SL: SINGLE ENDED WITH FRICTION LOCK
(SEE SHEET 2, FIG 3)(ONLY AVAILABLE ON
*5,*7, 10 THRU 50 POSITION)
-DL: DOUBLE ENDED WITH FRICTION LOCK
(SEE SHEET 2, FIG 4) (ONLY AVAILABLE
ON *5,*7, 10 THRU 50 POSITION)
(MUST CHOOSE FROM -NXX OPTIONS)
-SR: SINGLE ENDED WITH RETENTION LATCH
(SEE SHEET 3, FIG 5)
(ONLY AVAILABLE ON -02 THRU -50 POS)
-DR: DOUBLE ENDED WITH RETENTION LATCH
(SEE SHEET 3, FIG 6)
(ONLY AVAILABLE ON -02 THRU -50 POS)
(MUST CHOOSE FROM -NXX OPTIONS)
-SS: DUAL SCREW DOWN, SINGLE ENDED CABLE
(SEE SHT 4, FIG 7)
(NOT AVAILABLE WITH OPTIONS SL, DL, SR & DR
USES ISDF-XX-D-DS, CPS-RR-XX-XX-X & ACCRT-01)
-DS: DUAL SCREW DOWN, DOUBLE ENDED CABLE
(SEE SHT 4, FIG 8)
(NOT AVAILABLE WITH OPTIONS SL, DL, SR & DR
USES ISDF-XX-D-DS, CPS-RR-XX-XX-X & ACCRT-01,
MUST CHOOSE FROM NXXX OPTIONS)

TABLE 3: PLATING	
PLATING	CONTACT
-H	C-203-2830-H or CC03X-2830-01-H
-GF	C-203-2830-GF or CC03X-2830-01-GF
-G	C-203-2830-G or CC03X-2830-01-G
-F	C-203-2830-GF or CC03X-2830-01-GF

NOTES:

1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
2. MINIMUM PULLOUT FORCE: 3.0 LBS [13.3 N].
3. Ⓢ CONTACT MUST BE INSERTED UNTIL RETENTION FEATURE LOCKS INTO PLACE.
4. Ⓢ ALL FINISHED GOODS ARE TO BE ELECTRICAL TESTED INCLUDING HI-POT TEST AT 1000 VOLTS DC. AFTER FINAL ELECTRICAL TEST, LABEL EACH ASSEMBLY WITH 1 LABEL-ET STAMP ON THE BODY.
5. TINNED COPPER WIRE IS RoHS COMPLIANT.
6. PARTS TO BE LAYER PACKAGED.
7. NOTE DELETED.
8. FOR LENGTHS LESS THAN 12 in, TOLERANCE SHALL BE +/- .125.
9. FOR OTHER LENGTHS, TOLERANCE SHALL BE +/- 2%.
9. NOTE DELETED.
10. REFER TO CRIMP SPECIFICATIONS PRINT FOR CRIMP AND STRIP DIMENSIONS, TOLERANCES, TOOLING AND ITS REQUIREMENTS.
11. 3LB MIN WIRE CRIMP STRENGTH FOR -30 AWG AND 4.5LB MIN WIRE CRIMP STRENGTH FOR -28 AWG.
12. NOTE DELETED.
13. -TC TEFLON USE FOR DOUBLE ENDED ASSEMBLIES ONLY,
ALL SINGLE ENDED ASSEMBLIES USE SILVER PLATED DWCT-XX-01.
14. CUT LENGTH IS ASSEMBLY LENGTH MINUS OVERALL LENGTH SUBTRACTOR.

TABLE 1		
SERIES	WIRE GAUGE	CABLE
SFSD	28 AWG	DWC-28-XX-300
SFSD	30 AWG	DWC-30-XX-300
SFSDT (SEE NOTE 13)	28 AWG	DWCT-28-XX-TC
SFSDT (SEE NOTE 13)	30 AWG	DWCT-30-XX-TC

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1

INSULATOR: LCP UL 94V-0, COLOR: BLACK
CONTACT: BeCu
CABLE INSULATION: PVC OR FEP
WIRE: DWCT: TINNED COPPER.

(* = NOT AVAILABLE WITH POLARIZATION KEY)




FIG 2

-D: DOUBLE END
SFSD-10-28-XX-XX.XX-D-NUS SHOWN
(SAME AS FIG 1, UNLESS OTHERWISE STATED)

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
.050 [1.27] SOCKET DISCRETE CABLE ASSEMBLY

DWG. NO.
SFSDX-XX-XXX-XX-XX.XX-XX-XXX

BY: BRATCHER 5/5/2005 SHEET 1 OF 5









Table 5- Pin Mapping		
End Option (Double)	END 1	END 2
-NUS	01	N-1
-NUX	01	N
NDS	01	2
-NDX	01	1



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING
SHEET SCALE: 1:0.571429

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
.050[1.27] SOCKET DISCRETE CABLE ASSEMBLY

DWG. NO.
SFSDX-XX-XXX-XX-XX.XX-XX-XXX

BY: BRATCHER 5/5/2005 SHEET 2 OF 5





FIG 5
-SR: SINGLE END WITH RETENTION LATCH
SFSDX-05-28-XX-XX.XX-SR SHOWN
(ONLY AVAILABLE ON -02 THRU -50 POS)
(SAME AS FIG 1, UNLESS OTHERWISE STATED)




TABLE 4

SFSD color coded wire sequence

	COLOR									
	brown	red	orange	yellow	green	violet	gray	white	black	blue
	DWC-XX-01-300	DWC-XX-02-300	DWC-XX-03-300	DWC-XX-04-300	DWC-XX-05-300	DWC-XX-07-300	DWC-XX-08-300	DWC-XX-09-300	DWC-XX-10-300	DWC-XX-13-300
pin #	1	2	3	4	5	6	7	8	9	10
	11	12	13	14	15	16	17	18	19	20
	21	22	23	24	25	26	27	28	29	30
	31	32	33	34	35	36	37	38	39	40
	41	42	43	44	45	46	47	48	49	50
	51	52	53	54	55	56	57	58	59	60
	61	62	63	64	65	66	67	68	69	70
	71	72	73	74	75	76	77	78	79	80
	81	82	83	84	85	86	87	88	89	90
	91	92	93	94	95	96	97	98	99	100

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 4:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
.050[1.27] SOCKET DISCRETE CABLE ASSEMBLY

DWG. NO.
SFSDX-XX-XXX-XX-XX.XX-XX-XXX

BY: BRATCHER 5/5/2005 SHEET 3 OF 5






FIG 7
-SS: SINGLE END WITH SCREW DOWN
SFSDX-10-XXX-XX-XX.XX-SS SHOWN
(SAME AS FIG 1, UNLESS OTHERWISE STATED)



F:\DWG\MISC\Mktg\SFSDX-XX-XXX-XX-XX-XX-MKT.SLDDRW




FIG 8
-DS: DOUBLE END WITH SCREW DOWN
SFSDX-10-XXX-XX-XX.XX-DS-ND SHOWN
MUST CHOOSE FROM -NXXX OPTIONS
(SAME AS FIG 1, UNLESS OTHERWISE STATED)

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
.050[1.27] SOCKET DISCRETE CABLE ASSEMBLY

DWG. NO.
SFSDX-XX-XXX-XX-XX.XX-XX-XXX

BY: BRATCHER 5/5/2005

SHEET 4 OF 5

CABLE CUT IN-PROCESS




TABLE 6 (OVERALL LENGTH SUBTRACTORS) (SEE NOTE 14)	
	LENGTH
-S: SINGLE END	.249 [6.325]
-D: DOUBLE END	.448 [11.379]

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

SHEET SCALE: 2:1

DESCRIPTION:
.050[1.27] SOCKET DISCRETE CABLE ASSEMBLY

DWG. NO.
SFSDX-XX-XXX-XX-XX.XX-XX-XXX

BY:BRATCHER 5/5/2005 SHEET 5 OF 5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[SFSD-06-28-H-10.00-SR](#) [SFSD-20-30-H-03.25-DR-NUS](#) [SFSD-05-28-H-16.00-DR-NDX](#) [SFSD-06-28-G-04.00-DR-NDX](#) [SFSD-06-30-H-10.00-S](#) [SFSD-07-28-G-14.00-S](#) [SFSD-50-28-G-10.00-D-NDX](#) [SFSD-50-28-G-22.00-SR](#) [SFSD-50-28-G-39.37-D-NUS](#) [SFSD-50-28-G-50.00-S](#) [SFSD-25-30-G-20.00-S](#) [SFSD-25-30-G-24.00-SR](#) [SFSD-30-28-F-06.00-S](#) [SFSD-30-28-G-12.00-SL](#) [SFSD-30-28-G-16.00-SL](#) [SFSD-35-28C-G-15.74-S](#) [SFSD-15-30-H-18.00-SR](#) [SFSD-20-28C-G-20.00-SR](#) [SFSD-20-28-G-24.00-DR-NUS](#) [SFSD-25-28-G-04.00-DR-NDS](#) [SFSD-25-28-G-16.00-DR-NDX](#) [SFSD-25-30-G-10.00-D-NUS](#) [SFSD-10-28-G-30.00-D-NDX](#) [SFSD-15-28-G-08.00-DL-NUS](#) [SFSD-15-28-G-09.00-DR-NDX](#) [SFSD-15-28-G-24.00-DR-NDX](#) [SFSD-15-28-G-39.37-D-NDX](#) [SFSD-15-30-G-39.37-S](#) [SFSD-05-28-G-03.30-D-NUS](#) [SFSD-05-28-G-48.00-SR](#) [SFSD-07-28-G-24.00-DL-NDX](#) [SFSD-10-28-G-03.50-SR](#) [SFSD-10-28-G-04.00-DR-NUX](#) [SFSD-10-28-G-24.00-SL](#) [SFSD-08-28-G-05.00-D-NUS](#) [SFSD-08-28-H-06.00-S](#) [SFSD-10-30-H-20.00-SR](#) [SFSD-15-28-H-07.00-D-NDX](#) [SFSD-25-28-G-08.00-DR-NUS](#) [SFSD-02-28-G-05.00-S](#) [SFSD-20-28-G-04.00-D-NDS](#) [SFSD-50-28-G-18.00-S](#) [SFSD-08-28-G-07.00-S](#) [SFSD-35-28-G-06.00-D-NUS](#) [SFSD-10-28-G-06.00-DL-NDX](#) [SFSD-05-30-G-20.00-DR-NUS](#) [SFSD-05-30-G-16.00-D-NUS](#) [SFSD-15-28-G-25.00-SR](#) [SFSD-30-28-G-03.25-S](#) [SFSD-07-28-G-06.00-D-NDS](#) [SFSD-17-28-G-06.00-D-NUS](#) [SFSD-50-28-G-10.00-DR-NUX](#) [SFSD-15-28-G-03.25-S](#) [SFSD-20-28-G-06.50-D-NDX](#) [SFSD-05-28-G-16.00-S](#) [SFSD-07-28-G-08.00-SL](#) [SFSD-07-28-G-11.81-D-NDS](#) [SFSD-20-28-H-04.00-S](#) [SFSD-15-28-G-03.25-SL](#) [SFSD-25-28-G-30.00-S](#) [SFSD-07-28-G-12.00-D-NUX](#) [SFSD-30-28-G-15.78-DR-NDX](#) [SFSD-05-28-H-36.00-DR-NUS](#) [SFSD-40-28-H-03.25-S](#) [SFSD-02-28-G-05.00-DR-NUS](#) [SFSD-15-28-G-08.00-DR-NUX](#)