

DO NOT
SCALE FROM
THIS PRINT




TABLE 1 (BOARD TO BOARD)	
STYLE	"A"
-19	0.75 [19.0]
-25	0.98 [25.0]
-30	1.18 [30.0]

RU8-1XX-XX-XX-XX-DV-XX-X-XX

No OF POSITIONS
-40, -50, & -60

STACK HEIGHT
-19, -25, -30
(SEE TABLE 1)

SIGNAL ROUTING
-SE: SINGLE ENDED
-DP: DIFFERENTIAL PAIRS

CONNECTOR PLATING
SPECIFICATION
(VALUES GIVEN ARE IN MICRO-INCHES)
-SM: SELECTIVE, 30 AU / 50 NI MIN
ON CONTACT, MATTE TIN TAIL
-H: HEAVY GOLD, 30 AU / 50 NI MIN
ON CONTACT, 3 AU / 50 NI MIN ON TAIL
-S: SELECTIVE, 30 AU / 50 NI MIN
ON CONTACT, MATTE TIN TAIL
-L: LIGHT SELECTIVE, 10 AU / 50 NI MIN
ON CONTACT, MATTE TIN TAIL

CONNECTOR PACKAGING
-TR: TAPE & REEL
(LEAVE BLANK FOR TRAYS)

OPTION
-K: POLYAMIDE FILM PAD
(SEE NOTE 3)

OPTION
-BL: BOARD LOCK
(FIG. 2, SHT. 2)(AVAILABLE
ON -25 & -30 STACK HEIGHTS ONLY)

ROW SPECIFICATION
-DV: DUAL VERTICAL




FIG 1
RU8-160-19-SE-XX-DV SHOWN

TABLE 2		
No OF POS	"B"	"C"
-40	1.567 [39.80]	2.010 [51.05]
-50	1.882 [47.80]	2.325 [59.05]
-60	2.197 [55.80]	2.640 [67.05]

- NOTES:
- ⊗ REPRESENTS A CRITICAL DIMENSION.
 - BOTH HSEC8 CONNECTORS WILL BE SHIPPED WITH THE SAME OPTIONS EXCEPT FOR -BL OPTION.
 - REFERENCE HSEC8 DRAWING FOR ALL OTHER DIMENSIONS AND OPTIONS.
 - HSEC8 ASSEMBLIES WILL BE TRAY PACKAGED AND PCBs WILL BE PACKAGED IN BUBBLE BAGS. THE TRAY STACK SHOULD BE PLACED IN A TRAY BOX FIRST WITH THE PCBs PLACED ON TOP AND THEN VOID FILLED

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 1:1

INSULATOR: LCP, UL 94 VO, COLOR: BLACK
CONTACT: BRUSH ALLOY, 390 HT
LATCH ARM: LCP

DESCRIPTION:
.8mm BOARD TO BOARD KIT

DWG. NO.
RU8-1XX-XX-XX-XX-DV-XX-X-XX

BY: ELS 8/17/04 SHEET 1 OF 2

TABLE 3	
PART NUMBER	PCB-100256-RU8X-XXX-XX-XX
RU8-140-19-SE-XX-DV-XX	PCB-100256-RU8-040-19-SE
RU8-140-19-DP-XX-DV-XX	PCB-100256-RU8-040-19-DP
RU8-140-25-SE-XX-DV-XX	PCB-100256-RU8-040-25-SE
RU8-140-25-DP-XX-DV-XX	PCB-100256-RU8-040-25-DP
RU8-140-25-SE-XX-DV-BL-XX	PCB-100256-RU8L-040-25-SE
RU8-140-25-DP-XX-DV-BL-XX	PCB-100256-RU8L-040-25-DP
RU8-140-30-SE-XX-DV-XX	PCB-100256-RU8-040-30-SE
RU8-140-30-DP-XX-DV-XX	PCB-100256-RU8-040-30-DP
RU8-140-30-SE-XX-DV-BL-XX	PCB-100256-RU8L-040-30-SE
RU8-140-30-DP-XX-DV-BL-XX	PCB-100256-RU8L-040-30-DP
RU8-150-19-SE-XX-DV-XX	PCB-100256-RU8-050-19-SE
RU8-150-19-DP-XX-DV-XX	PCB-100256-RU8-050-19-DP
RU8-150-25-SE-XX-DV-XX	PCB-100256-RU8-050-25-SE
RU8-150-25-DP-XX-DV-XX	PCB-100256-RU8-050-25-DP
RU8-150-25-SE-XX-DV-BL-XX	PCB-100256-RU8L-050-25-SE
RU8-150-25-DP-XX-DV-BL-XX	PCB-100256-RU8L-050-25-DP
RU8-150-30-SE-XX-DV-XX	PCB-100256-RU8-050-30-SE
RU8-150-30-DP-XX-DV-XX	PCB-100256-RU8-050-30-DP
RU8-150-30-SE-XX-DV-BL-XX	PCB-100256-RU8L-050-30-SE
RU8-150-30-DP-XX-DV-BL-XX	PCB-100256-RU8L-050-30-DP
RU8-160-19-SE-XX-DV-XX	PCB-100256-RU8-060-19-SE
RU8-160-19-DP-XX-DV-XX	PCB-100256-RU8-060-19-DP
RU8-160-25-SE-XX-DV-XX	PCB-100256-RU8-060-25-SE
RU8-160-25-DP-XX-DV-XX	PCB-100256-RU8-060-25-DP
RU8-160-25-SE-XX-DV-BL-XX	PCB-100256-RU8L-060-25-SE
RU8-160-25-DP-XX-DV-BL-XX	PCB-100256-RU8L-060-25-DP
RU8-160-30-SE-XX-DV-XX	PCB-100256-RU8-060-30-SE
RU8-160-30-DP-XX-DV-XX	PCB-100256-RU8-060-30-DP
RU8-160-30-SE-XX-DV-BL-XX	PCB-100256-RU8L-060-30-SE
RU8-160-30-DP-XX-DV-BL-XX	PCB-100256-RU8L-060-30-DP




FIG 2
RU8-160-25-SE-XX-DV-BL SHOWN
(AVAILABLE IN -25 & -30 STACKER HEIGHTS ONLY)

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC. DO NOT SCALE DRAWING SHEET SCALE: 2:1	samtec 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code 55322 DESCRIPTION: .8mm BOARD TO BOARD KIT DWG. NO. RU8-1XX-XX-XX-XX-DV-XX-X-XX BY: ELS 8/17/04 SHEET 2 OF 2
---	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[RU8-140-25-SE-S-DV-BL-K-TR](#) [RU8-150-25-DP-S-DV-BL-K-TR](#) [RU8-140-25-SE-S-DV-K-TR](#) [RU8-160-19-DP-S-DV-](#)
[K-TR](#) [RU8-160-25-SE-S-DV-K-TR](#) [RU8-160-19-SE-S-DV-K-TR](#)