


SHROUDED .025" SQ POST IDC HEADERS

(2.54 mm) .100" PITCH • TST/HTST/ZST SERIES



TST/HTST/ZST

Mates:
IDSD, HCSD

SPECIFICATIONS

Insulator Material:
TST, ZST=Black Glass
Filled Polyester
HTST=Natural LCP
Insulation Resistance:
5000 MΩ min
Terminal Material:
Phosphor Bronze
Plating:
Au or Sn over
50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +125 °C with Gold
-55 °C to +105 °C with Tin
Voltage Rating:
425 VAC/600 VDC

PROCESSING

Lead-Free Solderable:
HTST=Yes
TST, ZST= No, Lead Wave only
SMT Lead Coplanarity:
(0.10 mm) .004" max (05-15)
(0.15 mm) .006" max (17-36)*
*(.004" stencil solution
may be available; contact
ipg@samtec.com)

SERIES	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
--------	---	------------------	------------	----------------	------------	--------------

TST
= Cable Strip

HTST
= High Temp
Cable Strip

**05, 07, 08, 10,
12, 13, 15, 17,
20, 25, 32, 36**
(Standard sizes)

**Specify
LEAD
STYLE
from
chart**

-F
= Gold flash
on post,
Matte Tin
on tail
(Not available
on -DV)

-L
= 10 μ" (0.25 μm)
Gold on post,
Matte Tin
on tail

-T
= Matte Tin

-D
= Double Row
Through-hole
(lead style -01,
-02 & -03 only)

-DV
= Double Row
Surface Mount
(lead style
-01 only)
(HTST only)

-D-RA
= Double Row
Right-angle
(lead style -04
& -05 only)


Surface Mount
(lead style
-01 only)
(HTST only)

-P
= Pick &
Place Pad




-TR
= Tape & Reel

-FR
= Full Reel
Tape & Reel
(must order max.
quantity per reel;
contact Samtec
for quantity
breaks)


LEAD STYLE	THROUGH-HOLE (A)
-01	(2.92) .115
-02	(4.19) .165
-03	(14.35) .565



-D -DV -D-RA



-DV (HTST ONLY)



LEAD STYLE	RIGHT-ANGLE (B)
-04	(3.30) .130
-05	(5.84) .230

ALSO AVAILABLE MOQ Required

Other platings & sizes
Alignment Pins
Single Row
Locking Leads
Polarized

ZST	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	BODY HEIGHT
-----	---	------------------	------------	----------------	---	-------------

**05, 07, 08, 10,
12, 13, 15, 17,
20, 25, 32, 36**
(Standard sizes)




**Specify
LEAD
STYLE
from
chart**

-F
= Gold flash on post,
Matte Tin on tail

-L
= 10 μ" (0.25 μm)
Gold on post,
Matte Tin on tail

-T
= Matte Tin

-"XXXX"
= Body Height



LEAD STYLE	C (OAL)	MAX BODY HEIGHT
-01	(16.00) .630	(13.72) .540
-02	(18.54) .730	(16.26) .640
-03	(21.08) .830	(18.80) .740
-04	(23.62) .930	(21.34) .840
-05	(26.16) 1.030	(23.88) .940
-06	(28.70) 1.130	(26.42) 1.040
-07	(31.24) 1.230	(28.96) 1.140
-08	(33.78) 1.330	(31.50) 1.240
-09	(36.32) 1.430	(34.04) 1.340

Note:
Some lengths, styles and
options are non-standard,
non-returnable. ZST is
non-standard, non-returnable.

Note:
For added mechanical stability, Samtec
recommends mechanical board spacers
be used in applications with gold or
selective gold plated connectors. Contact
ipg@samtec.com for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ZST-105-02-L-D-640](#) [ZST-107-01-L-D-540](#) [ZST-110-04-L-D-840](#) [ZST-107-06-G-D-1040](#) [ZST-117-01-G-D-480](#) [ZST-108-02-L-D-640](#) [ZST-105-01-L-D-540](#) [ZST-112-01-L-D-540](#) [ZST-113-05-G-D-665](#) [ZST-110-01-L-D-540](#) [ZST-110-03-S-D-690](#) [ZST-105-06-L-D-1040](#) [ZST-117-01-L-D-450](#) [ZST-117-01-G-D-540](#) [ZST-120-06-L-D-1030](#) [ZST-125-04-G-D-760](#) [ZST-130-02-G-D-640](#) [ZST-136-06-L-D-1040](#) [ZST-110-06-L-D-1040](#) [ZST-117-07-T-D-815](#) [ZST-125-01-G-D-530](#) [ZST-125-06-G-D-610](#) [ZST-132-06-G-D-515](#) [ZST-107-01-G-D-540](#) [ZST-108-03-L-D-715](#) [ZST-125-02-S-D-615](#) [ZST-125-01-L-D-515](#) [ZST-110-05-G-D-940-LL](#) [ZST-110-01-T-D-540](#) [ZST-105-03-L-D-715](#) [ZST-105-07-G-D-1140](#) [ZST-105-08-G-D-1215](#) [ZST-105-09-G-D-1340](#) [ZST-110-01-G-D-530](#) [ZST-112-03-G-D-550](#) [ZST-108-01-S-D-515](#) [ZST-110-01-S-D-540](#) [ZST-103-01-G-D-515](#) [ZST-105-02-G-D-640](#) [ZST-107-01-S-D-540](#) [ZST-105-05-G-D-825](#) [ZST-105-02-T-D-640](#) [ZST-105-06-T-D-812](#) [ZST-125-01-G-D-520](#) [ZST-110-01-T-D-511](#) [ZST-108-02-S-D-640](#) [ZST-120-03-G-D-700](#) [ZST-105-05-T-D-885](#) [ZST-108-09-S-D-1340](#) [ZST-120-01-G-D-540-20](#) [ZST-105-09-S-D-1340](#) [ZST-120-05-S-D-940](#) [ZST-105-05-L-D-900](#) [ZST-120-01-G-D-500](#) [ZST-105-06-T-D-1000](#) [ZST-108-01-S-D-514](#) [ZST-113-06-L-D-1040](#) [ZST-120-05-G-D-450](#) [ZST-108-06-G-D-600](#) [ZST-112-07-L-D-1106](#) [ZST-115-05-G-D-940](#) [ZST-105-04-L-D-800](#) [ZST-105-05-L-D-897](#) [ZST-108-06-L-D-1040](#) [ZST-108-09-G-D-1296](#) [ZST-113-03-L-D-740](#) [ZST-115-05-G-D-840](#) [ZST-105-09-S-D-1250](#) [ZST-108-07-L-D-1140](#) [ZST-110-02-S-D-578](#) [ZST-112-01-T-D-450](#) [ZST-120-03-S-D-735](#) [ZST-120-05-F-D-940-LL](#) [ZST-105-09-L-D-1340](#) [ZST-108-02-G-D-600](#) [ZST-110-01-G-D-450](#) [ZST-115-03-T-D-535](#) [ZST-106-01-L-D-450](#) [ZST-108-02-L-D-600](#) [ZST-108-05-G-D-920](#) [ZST-110-04-T-D-810](#) [ZST-117-06-G-D-600](#) [ZST-125-07-G-D-650](#) [ZST-108-02-L-D-550](#) [ZST-110-03-L-D-705](#) [ZST-105-07-S-D-1100](#) [ZST-110-02-G-D-600](#) [ZST-110-05-L-D-930](#) [ZST-117-02-L-D-550](#) [ZST-113-03-S-D-680](#) [ZST-117-02-L-D-600](#) [ZST-125-04-L-D-840](#) [ZST-125-08-G-D-1200](#) [ZST-105-08-G-D-1240](#) [ZST-115-01-L-D-465](#) [ZST-130-03-T-D-535](#) [ZST-105-01-S-D-480](#) [ZST-108-01-S-D-465](#) [ZST-120-01-S-D-480](#) [ZST-136-02-F-D-520](#)